Engineering Specification

Job Name	Contractor
Job Location	Approval
Engineer	Contractor's P.O. No.
Approval	Representative

FD-100-FC

Floor Drain with Surface Membrane Clamp

Specification

Watts FD-100-FC epoxy coated cast iron floor drain with anchor flange, reversible clamping collar with primary & secondary weepholes, adjustable heel proof nickel bronze strainer with surface membrane clamp, and no hub (standard) outlet.

Call customer service if you need assistance with technical details.


Pipe Sizing			
Suffix	Description		
2	2"(51) Pipe Size		
3	3"(76) Pipe Size		
4	4"(102) Pipe Size		
6	6"(152) Pipe Size		
	(No Hub Only)		

Outlet Type			
Suffix	Description		
NH	No Hub (MJ)		
P	Push On		
Т	Threaded Outlet		
Х	Inside Caulk		

Options			
Suffix	Description		
-5	Sediment Bucket		
-6	Vandal Proof		
-7	Trap Primer Tapping		
-8	Backwater Valve		
	(2, 3, 4" Only)		
-13	Galvanized Body		
-15	Strainer Extension (DD-50)		
-F4-50	4" Round Cast Iron Funnel		
-F4-1	4" Round Nickel Bronze Funnel		
-F6-1	6" Round Nickel Bronze Funnel		
-G-50	4" x 9" Oval Cast Iron Funnel		
-G-1	4" x 9" Oval Nickel Bronze Funnel		
-S0	Side Outlet		

Optional Body Material			
Suffix	Description		
-60	PVC Body w/Socket Outlet		
-61	ABS Body w/Socket Outlet		





Strainer Size

Str. Dia.	Min.	Max.	Load Rating	Free Area Sq. In.
7"(178)	1 3/8"(35)	3 3/8"(86)	MD	12
9"(229)	1 3/8"(35)	3 3/8"(86)	MD	15

Chart B

Pipe Size	Std. No Hub	P Push On	T Female Thread	X Inside Caulk	60/61 PVC/ ABS
2"(51)	3 5/8"(92)	4 1/4"(108)	4 1/4"(108)	4 1/2"(114)	4"(102)
3"(76)	3 5/8"(92)	4 1/4"(108)	4 1/4"(108)	4 1/2"(114)	4"(102)
4"(102)	3 5/8"(92)	4 1/4"(108)	4 1/4"(108)	4 1/2"(114)	4"(102)
6"(152)	3 1/2"(89)	-	-	-	-

NOTICE

The information contained herein is not intended to replace the full product installation and safety information available or the experience of a trained product installer. You are required to thoroughly read all installation instructions and product safety information before beginning the installation of this product.

Watts product specifications in U.S. customary units and metric are approximate and are provided for reference only. For precise measurements, please contact Watts Technical Service. Watts reserves the right to change or modify product design, construction, specifications, or materials without prior notice and without incurring any obligation to make such changes and modifications on Watts products previously or subsequently sold.

WATTS

USA: T: (800) 338-2581 • Watts.com **Canada:** T: (888) 208-8927 • Watts.ca

Latin America: T: (52) 55-4122-0138 • Watts.com

ES-WD-FD-100-FC 2412 © 2024 Watts