




FD9

Tag: _____

Drain for Wooden Floors

PROLINE

SPECIFICATION: Watts ProLine FD9 PVC, ABS, or cast iron drain for wooden floors with heel proof nickel bronze strainer and countersunk steel mounting flange.



Pipe Sizing (Select One)		
Suffix	Description	
-2PVC	2" (51) PVC	☐
-2ABS	2" (51) ABS	☐
-2NH	2" (51) No Hub	☐
-3PVC	3" (76) PVC	☐
-3ABS	3" (76) ABS	☐
-3NH	3" (76) No Hub	☐
-4PVC	4" (102) PVC	☐
-4ABS	4" (102) ABS	☐
-4NH	4" (102) No Hub	☐
Options (Select One or More)		
-B	Sediment Bucket	☐
-BV	Backwater Valve	☐
-G	CI Round Funnel	☐
-GNB	NB Round Funnel	☐
-H	CI Oval Funnel	☐
-HNB	NB Oval Funnel	☐
-VP	Vandal Proof Screws	☐

Job Name _____ Contractor _____

Job Location _____ Contractor's P.O. No. _____

Engineer _____ Representative _____

WATTS Drainage reserves the right to modify or change product design or construction without prior notice and without incurring any obligation to make similar changes and modifications to products previously or subsequently sold. See your WATTS Drainage representative for any clarification. Dimensions are subject to manufacturing tolerances.



Specification Drainage Products

USA: 100 Watts Road, Spindale, NC, 28160-2298; TEL: 828-288-2179 TOLL-FREE: 1-800-338-2581 www.watts.com
Canada: 5435 North Service Rd., Burlington, ONT. L7L 5H7; www.wattscanada.ca