Installation Instructions

IntelliStation Jr Control Module Upgrade Kit for IoT capabilities

Control and manage your domestic hot water system remotely with the Watts OnSite App.





How to Replace the Control Head

DANGER




Before attempting to open the control module, a certified and qualified electrician MUST disconnect all electrical power and fully de-energize the IntelliStation Jr. system.


Note: This kit is supplied with the complete enclosure, control head and hardware. Only the control head is required for IoT upgrade or controller repair.




1. Disconnect power and fully de-energize the system.




Press down at the fingertip grips on top of the front cover and pull out and down.




3. Lift the front cover up and away from the control.




 Using a screwdriver, loosen the 2 screws at the front of the wiring cover.




5. Pull the wiring cover straight out from the wiring chamber.




 Remove the 2 safety dividers from the wiring chamber by pulling them straight out of their grooves.




7. Disconnect the actuator, sensor, BAS (if installed) and power wires by pulling the plugs straight down.




8. Press and hold the control release clip on the base inside the wiring chamber, then slide the control upward to release it.




9. Lift the control up and away from the base.




10. Place the new control head onto the base, aligning its 4 tabs with the 4 openings on the base, then slide it downward until it clicks in place.




11. Reconnect the sensor, actuator, BAS (if used) and power wires.




12. Slide the 2 safety dividers back into their grooves.



13. Put the wiring cover back on and tighten the 2 screws.



14. Position the front cover onto the unit, then snap it in place.



 Turn power on and reprogram the system. Refer to original product User Guide and Instruction Manual: IOM-P-INTELLISTATIONJR.

Technical Data

Color	Blue
Туре	NEMA 1
Material	PVC or PPO plastic
Dimensions (inches)	6 ⁵ / ₈ x 7 ⁹ / ₁₆ x 2 ¹³ / ₁₆
H x W x D (mm)	170 x 193 x 72

Note: For use on the following models

LFIS075VL LFIS100VL LFIS150VL LFIS200VL

LIMITED WARRANTY / LIMITATION OF REMEDY:

What is covered? Powers warrants to the original purchaser only, that the product it manufactured when used as intended and instructed, is free from defects in materials or workmanship for five year warranty from date of shipment to the original purchaser.

What is not covered? This Limited Warranty does not cover or is voided by (a) any product, components or parts not manufactured by Powers, (b) faulty or improper installation or unsuitable installation environment, (c) failure to follow instructions or warnings, (d) problems caused by unauthorized attachments, modification, repairs or parts, (e) negligence or vandalism, (f) problems due to foreign material, adverse or improper water conditions, chemicals, contamination, improper pH, water treatment activities or products, mineral deposits, or decomposition by galvanic action, (g) shipping defects or damage, (h) normal wear and tear, (i) any abuse, misuse, unintended use, failure to maintain or inspect, (j) any circumstances over which Powers has no control.

IN NO EVENT SHALL POWERS BE LIABLE TO BUYER OR THIRD PARTIES FOR ANY GENERAL, SPECIAL, INCIDENTAL, OR CONSEQUENTIAL DAMAGES INCLUDING, BUT NOT LIMITED TO, PROPERTY DAMAGE, PERSONAL INJURIES, LOST PROFITS, LOSS OF SAVINGS OR REVENUE, LOSS OF THE USE OF THE PRODUCT OR ANY ASSOCIATED PRODUCTS, COST OF REPAIR, COST OF ANY SUBSTITUTE PRODUCTS OR SERVICES, DELAY DAMAGES, LABOR CHARGES, FINES/ PENALTIES, ECONOMIC OR NON-ECONOMIC LOSSES, ARISING DIRECTLY OR INDIRECTLY FROM THE SALE/PURCHASE, OWNERSHIP, INSTALLATION, OR USE OF THE PRODUCT, WHETHER BASED ON BREACH OF WARRANTY, BREACH OF CONTRACT, NEGLIGENCE, STRICT LIABILITY, OR ANY OTHER LEGAL THEORY.

What will Powers do? THE SOLE AND EXCLUSIVE REMEDY UNDER THIS LIMITED WARRANTY OR ANY IMPLIED WARRANTIES, is: Within a reasonable period of time after receiving a timely and bona fide claim, Powers will at its sole option (a) repair the product, or (b) replace the product (or component) with a same or similar product. A replaced product is warranted for 90 days from the date of return shipment, or for the balance of the original Limited Warranty period, whichever is longer. IN NO EVENT SHALL POWERS LIABILITY EXCEED AN AMOUNT EQUAL TO THE SALES PRICE OF THE PRODUCT.

To obtain warranty service: Contact Powers at 1-800-669-5430 with description of the problem and proof of the date of original purchase. Cost of shipping and insuring returned product must be paid by purchaser. Powers is not responsible for any loss of damage to the product incurred during shipping.

DISCIAIMER OF OTHER WARRANTY IS IN LIEU OF ALL OTHER WARRANTIES, EXPRESS OR IMPLIED. ALL IMPLIED WARRANTIES, INCLUDING THE IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE, ARE DISCLAIMED.



A WATTS Brand

USA: T: 888-432-8932 • PowersControls.com

Canada: T: 888-208-8927 • PowersControls.ca
Latin America: T: (52) 55-4122-0138 • PowersControls.com