Engineering Specification

Job Name	Contractor
Job Location	Approval
Engineer	Contractor's P.O. No.
Approval	Representative


RD-290

Scupper Drain with Flat Grate Specification

Watts RD-290 epoxy coated cast iron scupper drain with flashing clamp, secured flat grate, and no hub (standard) outlet.

Suffix	Pipe Sizing Description	
2	2"(51) Pipe Size	
3	3"(76) Pipe Size	
4	4"(102) Pipe Size	
6	6"(152) Pipe Size	





Options Suffix Description				
-1	Nickel Bronze Grate & Frame			
-6	Vandal Proof Grate			
-13	Galvanized			
-A	45 Degree Outlet (NH Only)			
-T	Threaded Outlet			



Pipe	No Hub		Threaded	
Size	Α	В	Α	В
2"(51)	5 1/8"(130)	6 1/2"(165)	2 3/4"(70)	6"(152)
3"(76)	4 1/2"(114)	5 3/4"(146)	2 3/4"(70)	5 3/8"(137)
4"(102)	4"(102)	5 1/8"(130)	2 3/4"(70)	4 7/8"(124)
6"(152)	3 1/2"(90)	4 13/16"(122)	N/A	N/A

4 3/4" (121) 6 1/4" (158) Pipe Size

NOTICE

The information contained herein is not intended to replace the full product installation and safety information available or the experience of a trained product installer. You are required to thoroughly read all installation instructions and product safety information before beginning the installation of this product.

Watts product specifications in U.S. customary units and metric are approximate and are provided for reference only. For precise measurements, please contact Watts Technical Service. Watts reserves the right to change or modify product design, construction, specifications, or materials without prior notice and without incurring any obligation to make such changes and modifications on Watts products previously or subsequently sold.

