Engineering Specification

Job Name	Contractor
Job Location	Approval
Engineer	Contractor's P.O. No.
Approval	Representative

FS-850

16" Square x 12" Deep Sanitary

Floor Sink

Specification

Watts FS-850 16"(406) square x 12"(305) deep flanged sanitary floor sink with white acid resistant porcelain enamel coated interior, loose set porcelain enamel coated cast iron grate, polypropylene dome bottom strainer, and no hub outlet.


Pipe Sizing			
Suffix Description			
4	4"(102) Pipe Size		
6	6"(152) Pipe Size		

Options			
Suffix Description			
-FC	Flange w/Weepholes & Flashing Clamp		
-1	Nickel Bronze Top		
-5	Sediment Bucket		
-6	Vandal Proof (-1, -3 Only)		
-7	Trap Primer Tapping		
-9	Hinged Grate (-1 Only)		
-33	Less Grate		
-150	1/2 Grate		
-175	3/4 Grate		
-F4-1	4" Round Nickel Bronze Funnel		
-F6-1	6" Round Nickel Bronze Funnel		
-G-1	4x9" Oval Nickel Bronze Funnel		

Free Area Sq. In.		
Standard Grate	With -1 Rim & Grate	
52	90	

Please refer to watts.com for BAA information on specific models.





*Add 3/4"(19) for -1 Nickel Bronze Rim & Grate

NOTICE

The information contained herein is not intended to replace the full product installation and safety information available or the experience of a trained product installer. You are required to thoroughly read all installation instructions and product safety information before beginning the installation of this product.

Watts product specifications in U.S. customary units and metric are approximate and are provided for reference only. For precise measurements, please contact Watts Technical Service. Watts reserves the right to change or modify product design, construction, specifications, or materials without prior notice and without incurring any obligation to make such changes and modifications on Watts products previously or subsequently sold.



USA: T: (800) 338-2581 • F: (828) 248-3929 • Watts.com **Canada:** T: (888) 208-8927 • F: (905) 481-2316 • Watts.ca

Latin America: T: (52) 55-4122-0138 ◆ Watts.com

ES-WD-FS-850 2128 © 2021 Watts