

Engineering Specification

Job Name _____

Contractor _____

Job Location _____

Approval _____

Engineer _____

Contractor's P.O. No. _____

Approval _____

Representative _____

Tag _____

RD-100-CP-85

IRMA Roof Drain with 12"x12"

Promenade Top

Specification

Watts RD-100-CP-85 epoxy coated cast iron IRMA roof drain with flashing clamp, 4"(102) high stainless steel perforated extension, 12 3/4"x12 3/4"(324x324) square epoxy coated ductile iron heel proof promenade top, and no hub (standard) outlet.

| Pipe Size | | |
|-----------|-----------------------------|--------------------------|
| Suffix | Description | |
| 2 | 2"(51) Pipe Size | <input type="checkbox"/> |
| 3 | 3"(76) Pipe Size | <input type="checkbox"/> |
| 4 | 4"(102) Pipe Size | <input type="checkbox"/> |
| 5 | 5"(127) Pipe Size (NH Only) | <input type="checkbox"/> |
| 6 | 6"(152) Pipe Size | <input type="checkbox"/> |




| Outlet Type | | |
|-------------|-----------------|--------------------------|
| Suffix | Description | |
| NH | No Hub (M.J) | <input type="checkbox"/> |
| P | Push On | <input type="checkbox"/> |
| T | Threaded Outlet | <input type="checkbox"/> |
| X | Inside Caulk | <input type="checkbox"/> |

| Options | | |
|---------|-------------------------------|--------------------------|
| Suffix | Description | |
| -1 | All Nickel Bronze Top | <input type="checkbox"/> |
| -5 | Sediment Bucket | <input type="checkbox"/> |
| -6 | Vandal Proof Top | <input type="checkbox"/> |
| -9 | Hinged Grate | <input type="checkbox"/> |
| -13 | Galvanized | <input type="checkbox"/> |
| -B | Sump Receiver | <input type="checkbox"/> |
| -D | Underdeck Clamp | <input type="checkbox"/> |
| -F | Deck Flange/Adj. Extension | <input type="checkbox"/> |
| -SO | Side Outlet (2", 3", 4" Only) | <input type="checkbox"/> |

| Optional Body Material | | |
|------------------------|--------------------------|--------------------------|
| Suffix | Description | |
| -60 | PVC Body w/Socket Outlet | <input type="checkbox"/> |
| -61 | ABS Body w/Socket Outlet | <input type="checkbox"/> |

| Load Rating | Free Area Sq. In. |
|-------------|-------------------|
| HD* | 41 |

Deck Opening 10"(254)
with sump receiver 13 1/4"(337)



NOTICE

The load classifications are in accordance with the American National Standards ASME A112.6.3 ASME Ratings are as follows:
*HD - Safe Live Load 5000-7499 lbs.(2250-3375 kg.)
The above categories are given as a guide only. Please consult factory.

NOTICE

The information contained herein is not intended to replace the full product installation and safety information available or the experience of a trained product installer. You are required to thoroughly read all installation instructions and product safety information before beginning the installation of this product.

Watts product specifications in U.S. customary units and metric are approximate and are provided for reference only. For precise measurements, please contact Watts Technical Service. Watts reserves the right to change or modify product design, construction, specifications, or materials without prior notice and without incurring any obligation to make such changes and modifications on Watts products previously or subsequently sold.



USA: T: (800) 338-2581 • F: (828) 248-3929 • Watts.com

Canada: T: (888) 208-8927 • F: (905) 481-2316 • Watts.ca

Latin America: T: (52) 55-4122-0138 • Watts.com

ES-WD-RD-100-CP-85 2139

© 2021 Watts