For Commercial Applications

Job Name	Contractor
Job Location	Approval
Engineer	Contractor's P.O. No.
Approval	Representative


RD-200-W Overflow Roof Drain with 4" Internal Water Dam

Specification

Taq

Watts RD-200-W epoxy coated cast iron overflow roof drain with flashing clamp with integral 4"(102) high internal standpipe, self-locking polyethylene dome (standard), and no hub (standard) outlet.

Suffix	Pipe Size (Select One)					
2	2"(51) Pipe Size					
3	3"(76) Pipe Size					
4	4"(102) Pipe Size (NH Only)					
C Suffix	outlet Type (Select One)					
NH	No Hub (MJ)					
Р	Push On					
Т	Threaded Outlet					
х	Inside Caulk					
Ont	iona (Calaat One ar Mar		1			
Suffix	ions (Select One or Mor Description	e)				
-13	Galvanized Body & Flashing Clamp					
-В	Sump Receiver					
-D	Underdeck Clamp					
-F	Deck Flange/Adj. Extension					
-GSS	Stainless Steel Ballast Guard					
-K	Ductile Iron Dome					
-K13	Galvanized Dome					
-K80	Aluminum Dome					
-K81	Rough Bronze Dome					
-K83	SS Mesh Covered					
	Aluminum Dome					onal Body Materia
-L	Vandal Proof Dome			Suffix		Description
-SO	Side Outlet		•	-60	PV	C Body w/Socket Outle
-US	Buy American Compliant		•	-61	AB	S Body w/Socket Outle
-W	Adj. Internal Water Dam					
- VV			1			Free Area
- • •	Deck Opening:		1			Sq. In.



NOTICE

Side Outlet (-S0) option only available in 2"(51), 3"(76), 4"(102) pipe sizes. Underdeck Clamp (-D) options are not available when -S0 is selected.

NOTICE

The information contained herein is not intended to replace the full product installation and safety information available or the experience of a trained product installer. You are required to thoroughly read all installation instructions and product safety information before beginning the installation of this product.

	Std.	Р	Т	х	60/61
Pipe	No	Push	Female	Inside	PVC/
Size	Hub	On	Thread	Caulk	ABS
2"(51)	3 5/8"(92)	4 1/4"(108)	4 1/4"(108)	4 1/4"(108)	3 3/4"(95)
3"(76)	3 5/8"(92)	4 1/4"(108)	4 1/4"(108)	4 1/4"(108)	3 5/8"(92)
4"(102)	3 5/8"(92)	4 1/4"(108)	4 1/4"(108)	4 1/4"(108)	3 7/8"(94)

Watts product specifications in U.S. customary units and metric are approximate and are provided for reference only. For precise measurements, please contact Watts Technical Service. Watts reserves the right to change or modify product design, construction, specifications, or materials without prior notice and without incurring any obligation to make such changes and modifications on Watts products previously or subsequently sold.



USA: T: (800) 338-2581 • F: (828) 248-3929 • Watts.com **Canada:** T: (905) 332-4090 • F: (905) 332-7068 • Watts.ca **Latin America:** T: (52) 81-1001-8600 • Watts.com