

Price List

Plumbing Solutions for Agriculture & Irrigation Applications



Effective September 15, 2025

All prices supersede previous issues,
are temporary and subject to change
without notice.

Table of Contents

Fittings

ANKA® Series Fittings	
Couplings	3
Reducing Coupling	3
Male Adapters	3
Reducing Male Adaptor	3
Female Adaptor	3
Reducing Female Adaptor	3
Tees	3
Reducing Tees	3
Female Tees	3
Elbows	4
Male Elbows	4
Female Elbows	4
Reducing Female Elbow	4
Pipe Unions	4
Female Pipe Unions	4
Tank Fittings	4
Quick Locks	4

Valves

ANKA® Series Valves	
Foot Valves	5
Check Valves	5

Hose Nozzles

Hose Nozzles and Trigger Guns	5
Repair Kits	5

Floats

APEX® Series Valves	
BigA®	6
PumpBuddy®	6
XtraFlo®	6
Xcess™	6
UltraFlo™	6
AP	6
220P	6
SpaceSaver	6
Visiball®	6
RainAid®	6
Reservoir Valve	6
APEX® Series Fittings	
Floats	7
Float Arms	7
Repair Kits & Parts	7

Terms and Conditions

FREIGHT TERMS: All shipments are F.O.B. shipping point. Shipments from factory less than 1000 lbs. are F.O.B. factory. Factory shipments OF \$5000 and over within the continental U.S.A. will be prepaid and allowed when made at the lowest motor carrier transportation rate.

TERMS OF SALE: All sales are F.O.B. shipping point.

PAYMENT TERMS: The invoices are due and payable 30 days from the date of invoice.

PURCHASE ORDER FORMS: Orders submitted on customer's own purchase order forms will be accepted only with the express understanding that no

statements, clauses, or conditions contained in said order form will be binding on the Seller if they in any way modify the Seller's own terms and conditions of sales.

STOCKING WHOLESALE MINIMUM CHARGE: A minimum billing charge of \$200.00 applies to shipments F.O.B. factory. Stocking Wholesaler Customers are encouraged to order sufficient material to avoid this charge which is necessitated by increased costs of processing small orders.

SPECIAL PRODUCTS: Orders for special or modified products are non-cancelable. In the event that the customer cancels an order for such products, Watts shall charge the customer an amount equal to Watts' costs and expenses incurred in performing the purchase order prior to receipt of notice of cancellation.

LIMITED WARRANTY: Watts Regulator Co. (the "Company") warrants each product to be free from defects in material and workmanship under normal usage for a period of one year from the date of original shipment. In the event of such defects within the warranty period, the Company will, at its option, replace or recondition the product without charge.

THE WARRANTY SET FORTH HEREIN IS GIVEN EXPRESSLY AND IS THE ONLY WARRANTY GIVEN BY THE COMPANY WITH RESPECT TO THE PRODUCT. THE COMPANY MAKES NO OTHER WARRANTIES, EXPRESS OR IMPLIED. THE COMPANY HEREBY SPECIFICALLY DISCLAIMS ALL OTHER WARRANTIES, EXPRESS OR IMPLIED, INCLUDING BUT NOT LIMITED TO THE IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE.

The remedy described in the first paragraph of this warranty shall constitute the sole and exclusive remedy for breach of warranty, and the Company shall not be responsible for any incidental, special or consequential damages, including without limitation, lost profits or the cost of repairing or replacing other property which is damaged if this product does not work properly, other costs resulting from labor charges, delays, vandalism, negligence, fouling caused by foreign material, damage from adverse water conditions, chemical, or any other circumstances over which the Company has no control. This warranty shall be invalidated by any abuse, misuse, misapplication, improper installation or improper maintenance or alteration of the product.

Some States do not allow limitations on how long an implied warranty lasts, and some States do not allow the exclusion or limitation of incidental or consequential damages. Therefore the above limitations may not apply to you. This Limited Warranty gives you specific legal rights, and you may have other rights that vary from State to State. You should consult applicable state laws to determine your rights. **SO FAR AS IS CONSISTENT WITH APPLICABLE STATE LAW, ANY IMPLIED WARRANTIES THAT MAY NOT BE DISCLAIMED, INCLUDING THE IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE, ARE LIMITED IN DURATION TO ONE YEAR FROM THE DATE OF ORIGINAL SHIPMENT.**

SERVICE POLICY: For inoperative products beyond the warranty period, we assume no liability for replacement of valves due to service conditions beyond our control.

RETURNED GOODS: No material shall be returned without authorization. When credit is issued it will be at the price charged, or prevailing price if lower, less handling charges based on costs of reconditioning, boxing, etc. However, a minimum 25% handling charge will apply. A minimum handling charge of \$20.00 is applied whenever the 25% handling deduction does not total \$20.00. Products which are obsolete or made to special order are not returnable.

NOTE: Prices and terms are subject to change without notice and supersede all previous quotations. The right is reserved to change or modify product design or construction without prior notice and without incurring any obligation to make such changes and modifications on products previously or subsequently sold.

*The wetted surface of this product contacted by consumable water contains less than 0.25% of lead by weight.

Consult factory for ordering code numbers of special models/options.

Fittings

Model	Ordering Code	Size (in.)	Description	UPC	# Per Inner	Weight Per Carton (lbs.)	List Price (each)
-------	---------------	------------	-------------	-----	-------------	--------------------------	-------------------

ANKA® Series Fittings

Couplings



ASC12

ASC12 US	88005243	1/2"	Coupling	098268149142	10	1.22	\$ 7.00
ASC34 US	88005244	3/4"	Coupling	098268149913	10	2.01	8.50
ASC1 US	88005245	1"	Coupling	098268149937	5	1.51	9.50
ASC114 US	88005246	1-1/4"	Coupling	098268149975	5	2.33	15.75

Reducing Coupling



ARSC3412

ARSC3412 US	88005247	1/2" x 3/4"	Reducing Coupling	098268149494	10	1.66	8.50
ARSC112 US	88005248	1/2" x 1"	Reducing Coupling	098268150049	5	1.16	9.50
ARSC134 US	88005249	3/4" x 1"	Reducing Coupling	098268150070	5	1.32	9.50
ARSC1141 US	88005250	1" x 1-1/4"	Reducing Coupling	098268150131	5	2.01	11.00

Male Adapters



AMA12

AMA12 US	88005251	1/2"	Male Adaptor	098268149500	10	1.01	6.25
AMA34 US	88005252	3/4"	Male Adaptor	098268150148	10	1.54	7.00
AMA1 US	88005253	1"	Male Adaptor	098268150155	5	1.22	10.25
AMA114 US	88005254	1-1/4"	Male Adaptor	098268150162	5	1.75	11.25

Reducing Male Adaptor



ARMA1234

ARMA1234 US	88005255	1/2" x 3/4"	Reducing Male Adaptor	098268149524	10	1.16	7.00
ARMA121 US	88005256	1/2" x 1"	Reducing Male Adaptor	098268150179	5	0.75	8.50
ARMA1114 US	88005257	1" x 1-1/4"	Reducing Male Adaptor	098268150186	5	1.34	10.75

Female Adaptor



AFA12

AFA12 US	88005258	1/2"	Female Adaptor	098268149548	10	1.08	6.25
AFA34 US	88005259	3/4"	Female Adaptor	098268150193	10	1.62	7.50
AFA1 US	88005260	1"	Female Adaptor	098268150209	5	1.21	9.25
AFA114 US	88005261	1-1/4"	Female Adaptor	098268150216	5	0.76	11.25

Reducing Female Adaptor



ARFA1234

ARFA1234 US	88005262	1/2" x 3/4"	Reducing Female Adaptor	098268149586	10	1.19	6.50
-------------	----------	-------------	-------------------------	--------------	----	------	------

Tees



AT12

AT12 US	88005263	1/2"	Tee	098268149616	10	1.71	9.50
AT34 US	88005264	3/4"	Tee	098268150223	10	2.88	11.50
AT1 US	88005265	1"	Tee	098268150292	5	2.16	15.00
AT114 US	88005266	1-1/4"	Tee	098268150308	5	3.30	18.75

Reducing Tees



ART3412

ART3412 US	88005267	1/2" x 3/4" x 3/4"	Reducing Tee	098268149623	10	2.58	11.00
ART112 US	88005268	1/2" x 1" x 1"	Reducing Tee	098268150346	5	1.85	13.75
ART134 US	88005269	3/4" x 1" x 1"	Reducing Tee	098268150407	5	2.00	15.00
ART1141 US	88005270	1" x 1-1/4" x 1-1/4"	Reducing Tee	098268150438	5	3.03	17.75

Female Tees



AFT12

AFT12 US	88005271	1/2"	Female Tee	098268149630	10	1.55	9.50
AFT34 US	88005273	3/4"	Female Tee	098268150520	10	2.44	11.00
AFT1 US	88005274	1"	Female Tee	098268150629	5	1.88	13.75

*The wetted surface of this product contacted by consumable water contains less than 0.25% of lead by weight.

Consult factory for ordering code numbers of special models/options.

Fittings

Model	Ordering Code	Size (in.)	Description	UPC	# Per Inner	Weight Per Carton (lbs.)	List Price (each)
-------	---------------	------------	-------------	-----	-------------	--------------------------	-------------------

ANKA Series Fittings

Elbows

AE12 US	88005275	1/2"	Elbow	098268149678	10	1.22	\$ 9.50
AE34 US	88005276	3/4"	Elbow	098268150674	10	2.00	11.00
AE1 US	88005277	1"	Elbow	098268150698	5	1.50	13.75
AE114 US	88005278	1-1/4"	Elbow	098268150797	5	2.30	16.50

Male Elbows

AME12 US	88005279	1/2"	Male Elbow	098268149685	10	1.01	7.00
AME34 US	88005280	3/4"	Male Elbow	098268150803	10	1.57	8.50
AME1 US	88005281	1"	Male Elbow	098268150971	5	1.22	11.00
AME114 US	88005282	1-1/4"	Male Elbow	098268150988	5	1.75	13.75

Female Elbows

AFE12 US	88005283	1/2"	Female Elbow	098268149692	10	1.07	7.00
AFE34 US	88005284	3/4"	Female Elbow	098268151015	10	1.60	8.50
AFE1 US	88005285	1"	Female Elbow	098268151176	5	1.27	11.00
AFE114 US	88005286	1-1/4"	Female Elbow	098268151459	5	1.86	13.75

Reducing Female Elbow

ARFE3412 US	88005287	1/2" x 3/4"	Reducing Female Elbow	098268149715	10	1.27	8.50
ARFE112 US	88005288	1/2" x 1"	Reducing Female Elbow	098268151510	10	1.63	8.50
ARFE134 US	88005289	3/4" x 1"	Reducing Female Elbow	098268151824	10	1.91	9.50

Yard Hydrant Elbow

AHF34	88225113	3/4" x 3/4"	Hydrant Elbow	098268513356	3	1.50	8.50
AHF134	88225114	1" x 3/4"	Hydrant Elbow	098268513363	3	1.50	10.25

Pipe Unions

APU34 US	88005290	3/4"	Pipe Union	098268149722	5	1.70	21.75
APU1 US	88005291	1"	Pipe Union	098268151855	5	1.98	23.00
APU114 US	88005292	1-1/4"	Pipe Union	098268151893	5	2.46	24.25

Female Pipe Unions

AFU34 US	88005293	3/4"	Female Union	098268149739	10	3.80	20.25
AFU1 US	88005294	1"	Female Union	098268151916	10	3.30	21.75
AFU114 US	88005295	1-1/4"	Female Union	098268151923	5	3.09	28.25
AFU112 US	88005984	1-1/2"	Female Union	098268162097	5	2.81	46.75
AFU2 US	88005985	2"	Female Union	098268162103	5	3.80	69.50

Tank Fittings

ABTF34 US	88005296	3/4"	Tank Fitting	098268149777	10	0.85	14.25
ABTF1 US	88005297	1"	Tank Fitting	098268151947	10	1.14	15.75
ATF34 US	88005298	3/4"	Tank Fitting	098268151954	5	1.17	19.75
ATF1 US	88005299	1"	Tank Fitting	098268151961	5	1.42	21.50
AMTF34 US	88005300	3/4"	Tank Fitting	098268151978	10	0.99	17.00
AMTF1 US	88005301	1"	Tank Fitting	098268151985	10	1.34	19.75

Quick Locks

AQLCM34 US	88005313	3/4"	Quick Lock	098268152067	10	1.31	17.00
AQLCM1 US	88005314	1"	Quick Lock	098268152074	10	1.41	18.25
AQLCM114 US	88005315	1-1/4"	Quick Lock	098268152098	10	1.51	20.25
AQLCM112 US	88005986	1-1/2"	Quick Lock	098268162134	10	1.54	23.00
AQLCF34 US	88005316	3/4"	Quick Lock	098268152104	10	1.32	17.00
AQLCF1 US	88005317	1"	Quick Lock	098268152128	10	1.41	18.25
AQLCF114 US	88005318	1-1/4"	Quick Lock	098268152135	10	1.51	20.25
AQLCF112 US	88005987	1-1/2"	Quick Lock	098268162165	10	1.54	23.00



AE12



AME12



AFE12



ARFE3412



AHF34



APU34



AFU34



Quick Locks Joined

*The wetted surface of this product contacted by consumable water contains less than 0.25% of lead by weight.

Consult factory for ordering code numbers of special models/options.

Valves

Model	Ordering Code	Size (in.)	Description	UPC	# Per Inner	Weight Per Carton (lbs.)	List Price (each)
-------	---------------	------------	-------------	-----	-------------	--------------------------	-------------------

ANKA Series Valves

Foot Valves



AFV34

AFV34 US	88005302	3/4"	Foot Valve	098268149784	1	0.30	\$ 23.00
AFV1 US	88005304	1"	Foot Valve	098268151992	1	0.45	26.75
AFV114 US	88005305	1-1/4"	Foot Valve	098268152005	1	0.82	28.25
AFV112 US	88005306	1-1/2"	Foot Valve	098268152012	1	0.95	39.00
AFV2 US	88005307	2"	Foot Valve	098268152029	1	1.15	45.50

Check Valves



ACV1

ACV34 US	88005308	3/4"	Check Valve	098268149791	1	0.25	21.75
ACV1 US	88005309	1"	Check Valve	098268152036	1	0.60	26.75
ACV114 US	88005310	1-1/4"	Check Valve	098268152043	1	0.75	28.25
ACV112 US	88005311	1-1/2"	Check Valve	098268149807	1	0.85	37.50
ACV2 US	88005312	2"	Check Valve	098268152050	1	1.00	44.00

Hose Nozzles

Hose Nozzles and Trigger Guns



AHNT20



AHN25

AHNT20 USA US	88005319	3/4"	Tough Trigger (Trigger Spray Gun)	098268149814	84	29.32	\$ 31.00
AHNT20 HW USA US	88005320	3/4"	Tough Trigger (Trigger Spray Gun)	098268152241	84	28.99	35.00
AHNS20 USA US	88005321	3/4"	Hose Nozzle	098268149821	130	28.12	24.25
AHNS25+25 US	88005322	1"	Hose Nozzle	098268152265	80	29.43	29.75
AHNS32+32 US	88005323	1-1/4"	Hose Nozzle	098268152272	65	25.57	34.00
AHN32+32 US	88005324	1-1/4"	Hose Nozzle	098268152289	45	28.99	46.75
AHN40+40 US	88005325	1-1/2"	Hose Nozzle	098268152296	40	27.67	49.50
AHNT20 USA D US	88005326	3/4"	Hose Nozzle Display Box	098268149845	10	3.31	40.00


Repair Kits

ANRKL US	88005332	N/A	Nozzle Repair Kit Large	098268149869	10	0.72	13.75
ANRKS US	88005333	N/A	Nozzle Repair Kit Small	098268152463	10	0.50	11.00
ATNSK US	88005334	N/A	Trigger Nozzle Service Kit	098268149890	10	0.61	9.50
ATNSK V US	88005335	N/A	Trigger Nozzle Service Kit Viton	098268152494	10	0.61	13.75

*The wetted surface of this product contacted by consumable water contains less than 0.25% of lead by weight.

Consult factory for ordering code numbers of special models/options.

Floats



Model	Ordering Code	Size (in.)	Description	UPC	# Per Inner	Weight Per Carton (lbs.)	List Price (each)
APEX® Series Valves							
BigAl							
BA114 US	88005611	1-1/4"	Tank Valve	098268160208	1	2.28	\$ 234.50
BA112 US	88005612	1-1/2"	Tank Valve	098268160246	1	2.02	237.00
BA2 US	88005613	2"	Tank Valve	098268160451	1	2.41	310.00
PumpBuddy							
PB34 US	88005614	3/4"	Tank Valve	098268160512	1	0.82	109.50
PB34LT US	88005615	3/4"	Tank Valve	098268160574	1	0.85	104.00
PB1 US	88005616	1"	Tank Valve	098268160611	1	0.83	110.50
PB1LT US	88005617	1"	Tank Valve	098268160635	1	0.89	116.50
PB114 US	88005618	1-1/4"	Tank Valve	098268160642	1	0.84	100.00
XtraFlo							
XF134 US	88005620	3/4" & 1"	Trough Valve	098268160703	1	0.84	84.00
XF114 US	88005621	1-1/4"	Trough Valve	098268160734	1	0.77	77.50
XFTEK US	88005622	N/A	Trough Valve Top Entry Kit	098268160741	1	0.35	37.50
XF34LT US	88005623	3/4"	Trough Valve	098268160758	1	0.79	84.00
XF1LT US	88005624	1"	Trough Valve	098268160765	1	0.83	84.00
XF34LTTE US	88005625	3/4"	Trough Valve	098268155792	1	0.72	101.50
XF1LTTE US	88005626	1"	Trough Valve	098268160772	1	0.74	103.00
XFTE34 US	88005627	3/4"	Trough Valve	098268160789	1	0.67	90.75
XFTE1 US	88005628	1"	Trough Valve	098268160796	1	0.67	91.75
XFTE114 US	88005629	1-1/4"	Trough Valve	098268155921	1	0.72	104.00
Xcess							
XS134 US	88005630	3/4" & 1"	Trough Valve	098268160802	1	6.43	48.50
XS134LT US	88005631	3/4" & 1"	Trough Valve	098268160819	1	7.09	52.25
XS134SA US	88005632	3/4" & 1"	Trough Valve	098268160895	1	6.27	56.25
UltraFlo							
UF134 US	88005634	3/4" & 1"	Trough Valve	098268160949	1	6.17	66.50
AP							
AP341 US	88005635	3/4" & 1"	Trough Valve	098268160956	1	5.03	41.75
220P							
220P12 US	88005640	1/2"	Trough Valve	098268161014	1	5.90	39.00
220P34 US	88005641	3/4"	Trough Valve	098268161069	1	5.90	39.00
220P1 US	88005642	1"	Trough Valve	098268161076	1	7.00	41.75
SpaceSaver							
SS12 US	88005643	1/2"	Trough Valve	098268161083	1	3.59	39.00
SS34 US	88005644	3/4"	Trough Valve	098268161090	1	3.48	43.00
Visiball							
VSB US	88005645	48"	Visiball water indicator	098268161106	1	3.90	303.50
PVSB EXT US	88005646	36"	Visiball extension tube	098268161113	1	0.64	132.00
RainAid							
RA34 US	88005647	3/4"	Tank Valve	098268161120	1	0.97	118.50
Reservoir Valve							
RES114 US	88005648	1-1/4"	Reservoir Valve	098268161151	1	2.70	129.50
RES112 US	88005649	1-1/2"	Reservoir Valve	098268161168	1	2.69	129.50
RES2 US	88005650	2"	Reservoir Valve	098268161205	1	2.73	129.50

*The wetted surface of this product contacted by consumable water contains less than 0.25% of lead by weight.

Consult factory for ordering code numbers of special models/options.

Floats



FLT

Model	Ordering Code	Size (in.)	Description	UPC	# Per Inner	Weight Per Carton (lbs.)	List Price (each)
-------	---------------	------------	-------------	-----	-------------	--------------------------	-------------------

APEX Series Fittings

Floats

FLT 115B US	88005654	4-1/2"	Float	098268161250	6	1.60	\$ 24.25
FLT 150B US	88005655	6"	Float	098268161267	4	1.97	35.00
FLT 1500 US	88005656	6"	Float	098268161274	4	1.97	33.50
FLT 1150 US	88005657	4-1/2"	Float	098268161281	6	1.60	18.75
FLT SQBLU US	88005658	4" x 4" x 6"	Float	098268161298	4	1.93	31.00
FLT SS US	88005659	1-1/2" x 2" x 5"	Float	098268161304	5	0.77	16.50

Float Arms

P16 17 US	88005660	12"	Trough Valve Arm	098268161311	10	2.31	12.25
P16 AP US	88005661	12"	Trough Valve Arm	098268161328	10	2.53	12.25
P16 APS US	88005662	12"	Trough Valve Arm	098268161335	10	1.32	10.75
P16 220P US	88005663	12"	Trough Valve Arm	098268161465	10	1.10	11.25
P16 XS US	88005664	12"	Trough Valve Arm	098268161472	10	2.09	12.00
P16 SS US	88005666	8"	Trough Valve Arm	098268161519	10	0.55	11.00
P16 RES US	88005667	12"	Trough Valve Arm	098268161526	10	4.40	14.50
PRESLK US	88005994	N/A	Valve Arm Kit	098268162264	10	1.51	87.75

Repair Kits & Parts

RKXF US	88005670	N/A	Repair Kit	098268161571	5	1.27	53.00
RKBA US	88005671	N/A	Repair Kit	098268161830	5	1.05	87.75
RKXS US	88005672	N/A	Repair Kit	098268161847	5	1.10	34.00
RKPB US	88005677	N/A	Repair Kit	098268161892	5	0.88	38.00
RKRES US	88005678	N/A	Repair Kit	098268161908	5	1.16	38.00
RKSS US	88005679	N/A	Repair Kit	098268161915	5	0.28	30.25
RKRA US	88005680	N/A	Repair Kit	098268161922	5	0.88	42.00
PBN12 US	88005681	1/2"	Plastic Back Nut	098268161939	10	0.30	11.00
PBN34 US	88005682	3/4"	Plastic Back Nut	098268161946	10	0.32	12.75
PBN1 US	88005683	1"	Plastic Back Nut	098268161953	10	0.41	16.75
PBNW12 US	88005684	1/2"	Back Nut Washer	098268161960	10	0.23	7.00
PBNW34 US	88005685	3/4"	Back Nut Washer	098268161977	10	0.22	9.00
PBNW1 US	88005686	1"	Back Nut Washer	098268161984	10	0.25	12.75

*The wetted surface of this product contacted by consumable water contains less than 0.25% of lead by weight.

Consult factory for ordering code numbers of special models/options.

Watts Family of Brands

Watts designs, manufactures, and sells an extensive line of flow control, water safety, water filtration & treatment, drainage, and PEX plumbing products.

The Watts family of companies provides a single source for solutions used to safely convey, conserve, and manage water.

Making Watts your single source for plumbing-related solutions will streamline your operations, save you money, and reduce the variety of repair parts needed for maintenance.



Steam Specialty™



POWERS™



THE DETECTION GROUP

