

# Troubleshoot With Confidence

*With accurate data  
on hand, on-site*

# FloPro™MD

## 3-in-1

Gas Measurement  
Diagnostic System



Pressure

Flow

BTU/Hr



Real Time Data via  
Free, User-Friendly  
Bluetooth App  
(Android™ and iOS™)



Calculates  
Everything  
for You



Flowmeter,  
Manometer, &  
Calculator in  
One Tool



Compatible with  
Natural Gas (NG)  
& Propane (LPG)



See SPEC Sheet

[Go.Dormont.com/flopromd](http://Go.Dormont.com/flopromd)

## Leave FloPro-MD on-site to collect data while you're away

# Diagnose With Confidence Easily Provide Proof



Install



Connect



Diagnose



Report

Intermittent gas appliance issues are tough to diagnose. FlowPro-MD helps you troubleshoot and diagnose gas-related issues on hand, on-site. Troubleshoot with confidence, reduce callbacks, and provide solid service your customers can count on.

- ✓ Easy installation with common, off-the-shelf tools
- ✓ Ideal for servicing, diagnostics, & routine maintenance
- ✓ Perfect for commercial kitchen appliances, boilers, tankless water heaters, furnaces, dryers, kitchen appliances, standby power generators, light commercial boilers and water heaters & rooftop units
- ✓ App available for download at these locations



## To speak to a Dormont Rep

(800) 367-6668 (USA)

(905) 332-4090 (Canada)

(52) 81-1001-8600 (Latin America)

### FEATURES & FUNCTIONS

#### Operating Range

- Natural Gas (NG):  
15,000 to 325,000 BTU/Hr
- Propane (LPG):  
15,000 to 500,000 BTU/Hr

#### Measures & Displays

- Gas Flow Rate: Cubic Feet/ Hour (CFH)
- Gas Flow Capacity: BTU/Hour
- Gas pressure measurement: inches water column (" w.c.)

#### Materials & Connections

- Corrosion-resistant aluminum construction with black finish
- Standard 3/4" Female NPT connections
- Annunciator LEDs communicate device status

