Engineering Specification

Job Name	Contractor
Job Location	Approval
Engineer	Contractor's P.O. No.
Approval	Representative
	Tiepresertative
Tag	

FS-700

8" Round x 3" Deep Sanitary Floor Sink

Specification


Watts FS-700 8"(203) round \times 3"(76) deep flanged sanitary floor sink with white acid resistant porcelain enamel coated interior, loose set porcelain enamel coated cast iron grate, polypropylene dome bottom strainer, and no hub (standard) outlet.

Pipe Sizing		
Suffix	Description	
2	2"(51) Pipe Size	
3	3"(76) Pipe Size	
4	4"(102) Pipe Size	

Outlet Type		
Suffix Description		
NH	No Hub (MJ)	
Р	Push-On	

Options		
Suffix	Suffix Description	
-FC	Flashing Clamp	
-1	Nickel Bronze Top	
-5	Sediment Bucket	
-6	Vandal Proof	
-7	Trap Primer Tapping	
-21	Secondary Strainer	
-33	Less Grate	
-150	1/2 Grate	
-175	3/4 Grate	
-F4-1	4" Round Nickel Bronze Funnel	
-F6-1	6" Round Nickel Bronze Funnel	
-G-1	4x9" Oval Nickel Bronze Funnel	

Free Area Sq. In.	
Standard Grate	With-1 Rim & Grate
16	14



* Add 5/8"(16) for -1 Nickel Bronze Rim & Grate

- Pipe Size -

NOTICE

The information contained herein is not intended to replace the full product installation and safety information available or the experience of a trained product installer. You are required to thoroughly read all installation instructions and product safety information before beginning the installation of this product.

Watts product specifications in U.S. customary units and metric are approximate and are provided for reference only. For precise measurements, please contact Watts Technical Service. Watts reserves the right to change or modify product design, construction, specifications, or materials without prior notice and without incurring any obligation to make such changes and modifications on Watts products previously or subsequently sold.

 $(51)^*$

-F Optional Flange with Weepholes



USA: T: (800) 338-2581 • F: (828) 248-3929 • Watts.com **Canada:** T: (888) 208-8927 • F: (905) 481-2316 • Watts.ca **Latin America:** T: (52) 55-4122-0138 • Watts.com

ES-WD-FS-700 2127