

For Commercial Applications

Job Name _____

Contractor _____

Job Location _____

Approval _____

Engineer _____

Contractor's P.O. No. _____

Approval _____

Representative _____

Series PWHSJUMBO

JUMBO-SS Cartridge Housings

Stainless Steel Single Cartridge Models

Connection Size: 2" MNPT (50mm)

Flow Rates: up to 150gpm (567 lpm)

The ideal filter housings for optimum convenience and savings. Series PWHSJUMBO housing filters are designed to accept "JUMBO-SS" series cartridges for easy installation and replacement. Filter housings are constructed using 316 stainless steel and are rated for pressures to 150psi. Pipe fittings on single cartridge models are 2" MNPT with pressure gauges installed on inlet and outlet fittings. Convenient, band clamp lid closures are easy to use, safe and secure. Protective poly coat over stainless steel is standard finish.

Features

- Adjustable compression cap provides superior sealing for both ends of the jumbo cartridge
- User friendly jumbo cartridges are easy to install, easy to service and easy to replace
- Housings accept "JUMBO SS" series cartridges
- Heavy-duty 316 stainless steel construction for durability
- Band clamp lid closure are convenient, easy to use and secure
- Pipe fittings are readily accessible for easy installation
- Pressure gauges are installed on pipe fittings
- Heavy-duty mounting legs are standard
- 3 models available for a wide range of flow rates

PURE WATER



Model
PWHSJUM40

Model
PWHSJUM90

Model
PWHSJUM170



Commercial Quality Jumbo Cartridge Filter Housings in 316SS

MODEL NO.	MATERIAL	MAX FLOW (GPM)	CARTRIDGE STYLE	NUMBER OF CARTRIDGES	PIPE SIZE	LID CLOSURE
PWHSJUM40	316SS	50	"40"	1	2" NPT	V-Band
PWHSJUM90	316SS	100	"90"	1	2" NPT	V-Band
PWHSJUM170	316SS	150	"170"	1	2" NPT	V-Band

Note: Commercial quality jumbo cartridge housings are rated for pressures to 150psi (10 bar) and temperatures to 212°F (100°C). Pressure gauges included and installed on inlet and outlet.

Watts product specifications in U.S. customary units and metric are approximate and are provided for reference only. For precise measurements, please contact Watts Technical Service. Watts reserves the right to change or modify product design, construction, specifications, or materials without prior notice and without incurring any obligation to make such changes and modifications on Watts products previously or subsequently sold.



Jumbo Filter Cartridges



PWJPL40

PWJPL40

FILTER HOUSING MODEL NO.	MICRON RATING	MODEL NO. WITH SYNTHETIC MEDIA	NUMBER PER CASE
40	1 Absolute	PWJPL40M1AB	1
	0.35	PWJPL40M.35	1
	1	PWJPL40M1	1
	5	PWJPL40M5	1
	20	PWJPL40M20	1
	50	PWJPL40M50	1
	100	PWJPL40M100	1



PWJPL90

PWJPL90

FILTER HOUSING MODEL NO.	MICRON RATING	MODEL NO. WITH SYNTHETIC MEDIA	NUMBER PER CASE
90	1 Absolute	PWJPL90M1AB	1
	0.35	PWJPL90M.35	1
	1	PWJPL90M1	1
	5	PWJPL90M5	1
	20	PWJPL90M20	1
	50	PWJPL90M50	1
	100	PWJPL90M100	1



PWJPL170

PWJPL170

FILTER HOUSING MODEL NO.	MICRON RATING	MODEL NO. WITH SYNTHETIC MEDIA	NUMBER PER CASE
170	1 Absolute	PWJPL170M1AB	1
	0.35	PWJPL170M.35	1
	1	PWJPL170M1	1
	5	PWJPL170M5	1
	20	PWJPL170M20	1
	50	PWJPL170M50	1
	100	PWJPL170M100	1

Note: Do not use with water that is microbiologically unsafe or of unknown quality without adequate disinfection before or after the system.



A Watts Water Technologies Company



USA: Tel. (800) 224-1299 • www.watts.com

Canada: Tel. (888) 208-8927 • www.watts.ca