For Residential and Commercial Applications

Job Name	Contractor
Job Location	Approval
Engineer	Contractor's P.O. No.
Approval	Representative

Series 26A, 263A Small Pressure Regulators

Sizes: 26A: ½" - ½" (3 - 15mm) 263A: ½" - ½" (8 - 15mm)

Series 26A, 263A Small Pressure Regulators are general purpose pressure regulators for water and no. 2 fuel oil. These regulators are ideal for use in beverage dispensers, ice cube machines, paint sprayers, humidifiers and other similar applications.

Features

- Rugged forged brass body
- Tee handle adjustment
- Oversized orifice

Models

26A 2-way regulator263A 3-way regulator

Materials

Body: Brass Spring Cage: Aluminum

Disc: Buna-N stainless steel
Diaphragm: Reinforced Buna-N

Pressure – Temperature

Temperature Range: 0°F – 140°F (-18°C – 60°C) Maximum Working Pressure: 300psi (21 bars)

Reduced Pressure Range:

Suffix	Rai	Std.	Std. Set at		
	psi	bars	psi	bars	
Α	1 – 25	0.1 - 1.7	10	0.7	
В	3 – 50	0.2 - 3.4	15	1.0	
С	10 – 125	0.7 - 8.6	25	1.7	
D	50 – 175	3.4 - 12.1	50	3.4	

Options

G Pressure gauge

SS All stainless steel construction

X Slotted adjusting screw








263A 3-Way

Capacity



Dimensions – Weights

ı	Model	Size (DN)		Α		C		Weight	
		in.	mm	in.	mm	in.	mm	lbs	kgs
	26A	1/8	3	21/8	54	43/8	111	1	.45
	26A/263A	1/4	8	21/8	54	43/8	111	1	.45
	26A/263A	3/8	10	21/8	54	43/8	111	1	.45
	26A/263A	1/2	15	21/8	54	43/8	111	1	.45

Watts product specifications in U.S. customary units and metric are approximate and are provided for reference only. For precise measurements, please contact Watts Technical Service. Watts reserves the right to change or modify product design, construction, specifications, or materials without prior notice and without incurring any obligation to make such changes and modifications on Watts products previously or subsequently sold.



