

## For Commercial, Residential and Institutional HVAC Applications

Job Name \_\_\_\_\_  
 Job Location \_\_\_\_\_  
 Engineer \_\_\_\_\_  
 Approval \_\_\_\_\_

Contractor \_\_\_\_\_  
 Approval \_\_\_\_\_  
 Contractor's P.O. No. \_\_\_\_\_  
 Representative \_\_\_\_\_

# Series G-TB

## Thermowells

### Size: 1/2" (15mm)

Series G-TB Thermowells are brass parts used with thermometer Models TB and TBC in commercial, residential, and institutional HVAC applications. These thermowells feature set screws and 1/2" (15mm) MNPT connections.



G-TB

### Features

- Brass body
- Set screw
- 1/2" (15mm) MNPT connection

### Approvals

Certified by The Northern Certification Society of Italy  
 (Det Norske Verita Italia S.r.l.)



### Standards

ISO 9002 quality standard

### Materials

Body: Brass

### Dimensions



SIZE (DN)	MODEL	DIMENSIONS				WEIGHT	
		in.	mm	in.	mm	in.	mm
1/2	15	G-TB-1	1 1/8	35		7/16	11
1/2	15	G-TB-2	2	51		7/16	11
1/2	15	G-TB-4	3 15/16	100		7/16	11
1/2	15	G-TB-6	5 1/2	140		7/16	11
1/2	15	G-TB-8	7 1/2	191		7/16	11
1/2	15	G-TB-12	11 1/16	291		7/16	11

Watts product specifications in U.S. customary units and metric are approximate and are provided for reference only. For precise measurements, please contact Watts Technical Service. Watts reserves the right to change or modify product design, construction, specifications, or materials without prior notice and without incurring any obligation to make such changes and modifications on Watts products previously or subsequently sold.



**USA:** 815 Chestnut St., No. Andover, MA 01845-6098; [www.watts.com](http://www.watts.com)

**Canada:** 5435 North Service Rd., Burlington, ONT. L7L 5H7; [www.wattscanada.ca](http://www.wattscanada.ca)