Engineering Specification

Job Name	Contractor
Job Location	Approval
Engineer	Contractor's P.O. No.
Approval	Representative

LEAD FREE*

Series LFSC-8

Lead Free* Cast Brass Hose Bibbs

with Separate Tamper-proof Vacuum Breaker

Watts offers six styles of hose bibbs which are supplied with separate vacuum breaker to be attached to the hose bibb after hose bibb installation. Once the vacuum breaker is properly installed to the hose bibb it is tamper-proof. This provides backsiphonage protection for potable hoses connected to hose thread faucets. Garden hoses are an extension of the plumbing system and have been known to cause illness or death when unprotected in uses such as with chemical sprayers, flushing of tanks or pipes, or the filling of pools.

Models

- LFSC8-1 No kink faucet, ½" male NPT or copper sweat connection with vacuum breaker.
- **LFSC8-2** No kink hose faucet, ¾" copper sweat connection with vacuum breaker.
- **LFSC8-3** Lawn faucet, ½" or ¾" regular pattern, dual sweat connection with vacuum breaker.
- **LFSC8-4** Lawn faucet, ¾" female NPT regular pattern with vacuum breaker.
- LFSC8-5 Hose bibb hex shoulder, ½" male NPT with tee handle and vacuum breaker.
- LFSC8-6 Hose bibb hex shoulder, ¾" male NPT with tee handle and vacuum breaker.

Features

- Backflow backsiphonage protection
- Separate non-removable vacuum breaker (with break-away screw)















NOTICE

The information contained herein is not intended to replace the full product installation and safety information available or the experience of a trained product installer. You are required to thoroughly read all installation instructions and product safety information before beginning the installation of this product.

*The wetted surface of this product contacted by consumable water contains less than 0.25% of lead by weight.



Standards

Tamper-proof vacuum breaker (Watts Model LF8B) is tested and approved in conformance with Standard 1011 of the American Society of Sanitary Engineers and by all principal cities, states and areas having these requirements. Additionally listed with IAPMO Uniform Plumbing Code, as well as NSF (National Sanitation Foundation) to Standard NSF/ANSI 372.


Please refer to ES-LF8 and ES-LFSC for independent listings.

How it Works


Series LFSC-8 is a combination hose bibb with separate tamper-proof vacuum breaker - to be attached after installation. Under normal conditions, the inner diaphragm opens to permit generous flow, while the circumferential diaphragm closes the air vents.

Should supply pressure drop and a backflow begin, the inner diaphragm immediately closes to prevent backflow into the main line, while the circumferential diaphragm opens the air vents to break the vacuum.

Capacity



Dimensions - Weight



MODEL	ORDER NO.	SIZE	DESCRIPTION	DIMENSIONS							WEIGHT	
				A		В		С				
		in.		in.	mm.	in.	mm.	in.	mm.	lbs.	kgs.	
NO KINK HOSE FAUCET with tee handle and vacuum breaker												
LFSC8-1	0124294	1/2	Male I.P. or Copper Connection	31//8	79	21/2	64	21/4	57	.75	.34	
LFSC8-2	0124295	3/4	Copper Connection	31//8	79	21/2	64	21/4	57	.75	.34	
LAWN FAUCET (Sillcock) with cast iron handwheel and vacuum breaker												
LFSC8-3	0124296	½ or ¾	Regular Pattern, Dual Connections	31/4	83	21/2	64	21/4	57	.75	.34	
LFSC8-4	0124297	3/4	I.P. Regular Pattern	31/4	83	21/2	64	21/4	57	.75	.34	
HOSE BIBB HEX SHOULDER with tee handle												
LFSC8-5	0124298	1/2	I.P. Inlet Hose End	35%	92	2	51	21/4	57	.75	.34	
LFSC8-6	0124299	3/4	I.P. Inlet Hose End	33/4	95	2	51	21/4	57	.75	.34	

Note: Models LFSC8-1 through LFSC8-5 are packaged with the Model LF8B vacuum breaker with break-away set screw. The LFSC8-6 model is packaged with the Model LF8 which has an allen head set screw.



USA: T: (978) 689-6066 • F: (978) 975-8350 • Watts.com Canada: T: (888) 208-8927 • F: (905) 481-2316 • Watts.ca Latin America: T: (52) 55-4122-0138 • Watts.com

ES-LFSC-8 2133 © 2021 Watts