

Pure Water Visual Test Kits

Watts® Pure Water Visual Test Kits

provide a quick, portable, and convenient way to measure some of the most common water quality test parameters anywhere at any time. Accurate chemistry, simple to read comparator

cards with instruction allows for testing on site without having to take water samples back to a chemistry laboratory.



Individual Visual Test Kits

ORDERING CODE	MODEL NUMBER	PARAMETER	TEST TYPE	RANGE (PPM)	# TEST
7100700	PWTTOTALIRON	Total Iron (Fe+3) Kit	Visual Comparator, Colorimetric	0-9	≥ 100
7100701	PWTFERROUSIRON	Ferrous Iron (Fe+2) Kit	Visual Comparator, Colorimetric	0-9	≥ 100
7100702	PWVTMANAGANESE	Manganese Kit	Visual Comparator, Colorimetric	0-10	≥ 100
7100703	PWTTOTALALK	Total Alkalinity Kit	Visual Comparator, Colorimetric	0-500	≥ 100
7100704	PWVTpH	pH Kit	Visual Comparator, Colorimetric	6-8	≥ 100
7100705	PWVTCHLORINE	Chlorine (Free & Total) Kit	Visual Comparator, Colorimetric	0-6	≥ 100
7100706	PWVTHARDNESS	Total Hardness Kit	Visual Drop Count, Titrimetric	0-500/0-30ppg	≥ 100

Individual Kits contain all necessary reagents, comparator card, syringe, cuvettes, and instructions to perform measurements
*Comparator Holder and handheld TDS Meter are sold separately.



Accessories

ORDER CODE	DESCRIPTION
7100708	Comparator Card Holder



TDS Handheld Meter with Carrying Case

ORDER CODE	DESCRIPTION
7300782	TDS Meter 0 - 99990 (mg/l) Temp 32°F - 176°F

This handheld TDS Meter provides a quick, reliable way to assess water quality. Accurately measures total dissolved solids (TDS) levels. Ideal for evaluating reverse osmosis membrane performance and determining when replacement is needed. Designed for both residential and commercial use. Compact and portable—convenient to carry in a pocket or toolbox.