For Non-Health Hazard Applications

| Job Name | Contractor |
|--------------|-----------------------|
| Job Location | Approval |
| | |
| Engineer | Contractor's P.O. No. |
| Approval | Representative |

LEAD FREE*

Spool Adapters


DuraCheck to MasterSeries® Spacer Spool Adapter Kit

Size: 4" - 8" (100mm - 200mm)

The FEBCO DuraCheck to MasterSeries® Spacer Spool Adapters ease retrofit of the old style in-line FEBCO DuraCheck backflow preventers (Models 825YD, 805YD and 806YD in 4" – 8" (100mm - 200mm) with the new style in-line FEBCO MasterSeries® (Models 850/LF850, 860/LF860, and 856/856ST in 4" – 8" (100mm - 200mm). This kit eliminates the need for expensive custom fabricated spools and provides a quick and easy way to retrofit the valve. The adapter kit comes complete with the proper length spool, gasket, nuts, and studs to retrofit the longer DuraCheck Valves with the shorter in-line MasterSeries®. See the retrofit chart below. The gasket is to be used between the backflow preventer and the spool adapter. MasterSeries® 2½" and 3" (65, 80mm) units do not require a spacer spool adapter to retrofit.

Features

- Easy retrofit
- Epoxy coated body
- Adapter Kit Includes: Spool, Gasket, Nuts and Studs
- End Details Flanged ANSI B16.42, Class 150



Pressure - Temperature

Maximum Working Pressure: 175psi (12.1 bar) Hydrostatic Test Press: 350psi (24.1 bar)

Temperature Range: 33°F to 140°F (0.5°C to 60°C)

Materials

Main Valve Body: Carbon Steel or Ductile Iron (ANSI B16.1)
Coating: Epoxy coated internal and external,

AWWA C550

Elastomers: Gaskets

Trim: Hex Nuts & Studs - plated steel


DuraCheck to MasterSeries® Spool Adapter Kits

| RETROFIT PART NUMBER CHART | | | | | | | | | | |
|----------------------------|-------------|-----------------------|-----------------------------|-----------------------------|-----------------------------|--|--|--|--|--|
| Type of Device | DuraCheck | MasterSeries | Spool Adapter 4" (100mm) | Spool Adapter 6" (150mm) | Spool Adapter 8" (200mm) | | | | | |
| Double Check | Model 805YD | Model 850/LF850 | 905523 | 905524 | 905525 | | | | | |
| Double Check Detector | Model 806YD | Model 856/856ST/LF856 | 905523 | 905524 | 905525 | | | | | |
| Reduced Pressure | Model 825YD | Model 860/LF860 | 905523 | 905524 | 905525 | | | | | |



Typical Installation

FEBCO Model 850/LF850 With Spool Adapter Outdoor Installation




Dimensions - Weights

Size: 4" - 8" (65 - 100mm)

| SIZE | (DN) | DIMENSIONS | | | WEIGHT | | |
|------|------|------------|-----|--------|--------|------|------|
| | | , | A | В | | | |
| in. | mm | in. | mm | in. | mm | lbs. | kgs. |
| 4 | 65 | 9 | 229 | 4 | 102 | 35 | 15.9 |
| 6 | 80 | 11 | 279 | 315/16 | 90 | 48 | 21.8 |
| 8 | 100 | 131/2 | 343 | 4 | 102 | 75 | 34.0 |

Weights shown are approximate. Dimensions are nominal. Allowances must be made for normal manufacturing tolerances.



Flange and bolt holes per ANSI B16.42, Class 150



A WATTS Brand

USA: Tel: (800) 767-1234 • Fax: (800) 788-4491 • FEBCOonline.com **Canada:** Tel: (905) 332-4090 • Fax: (905) 332-7068 • FEBCOonline.ca **Latin America:** (52) 81-1001-8600 • Fax: (52) 81-8000-7091 • FEBCOonline.com