Engineering Specification

Job Name	Contractor
Job Location	Approval
Engineer	Contractor's P.O. No.
Approval	
Approval	Representative

Ductile Iron Screwed End Y Strainer

Model: 251-DI, Class 300 Sizes: 1/4" - 3" (8 - 80mm)

Typical Service

 Used extensively to strain foreign matter from pipelines and provide economical protection for costly pumps, meters, valves, and other similar mechanical equipment.

Features

• Machined seats in both body and cap align and lock the screen in place to stop sediment bypass.

Construction

 Gasketed cap is used for easy disassembly and assembly. Many others use Loctite, rendering disassembly virtually impossible.

NOTE: Bolted covers are supplied on sizes 2½" and 3".

Self-Cleaning

 Self-cleaning is accomplished by opening the plug or valve connected to the blowoff outlet.

Blowoff Outlets

- Outlets are NPT tapped.
- Sizes of tapping are specified on next page.
- Not normally furnished with plug. Plug available, specify with order.

Capacity

- · Generously proportioned bodies.
- Open Area Ratio much greater than pipe size, ensuring low pressure drop.



Model 251-DI

PRESSURE/TEMPERATURE - NON-SHOCK				
Model	Material	Rating		
251-D1	Ductile iron	640psi @ 100°F 450psi @ 650°F		

Screens

		STANDARD	(WATER)	STEAM RECOMMENDATION		
Model	Sizes	Material	Opening	Material	Opening	
251-DI	1/4" - 3"	304SS	.062 perf	304SS	.045 perf	

NOTICE

The information contained herein is not intended to replace the full product installation and safety information available or the experience of a trained product installer. You are required to thoroughly read all installation instructions and product safety information before beginning the installation of this product.




BILL OF MATERIAL					
Item	QTY		Description		
1	1	Body	Ductile Iron SA536 65-45-12		
2	1	Cap	Duplicate Ion SA536 65-45-12		
3	1	Screen	304 ST. STL.		
4	1	Gasket	316 ST. STL. Tanged Graphoil		

Dimensions and Weights

SI	ZE	DIMENSIONS					WEIGHT		
		A		В		C (NPT)			
in.	mm	in.	mm	in.	mm	in.	mm	lbs.	kgs.
1/4	6	313/16	97	2 ³ / ₁₆	56	3/8	10	2	.9
3/8	10	313/16	97	3 ³ ⁄ ₁₆	56	3/8	10	2	.9
1/2	15	313/16	97	2 ³ / ₁₆	56	3/8	10	2	.9
3/4	20	43/4	120	27/8	73	1/2	12	2.5	1.1
1	25	5 ⁷ / ₁₆	138	31/4	83	3/4	15	4	1.8
11/4	32	6 5⁄16	160	3¾	95	3/4	15	5	2.2
11/2	40	71/2	190	411/16	119	1	25	7.5	3.4
2	50	81//8	206	51/2	140	11/4	32	12	5.4
21/2	65	10½	266	65%	168	11/2	40	22	10
3	80	12½	318	67/8	175	11/2	40	33	15

Apply for certified drawings.



Pressure Drop

 See Pressure Drop Charts in Technical Data Section in the Mueller Steam Specialty Engineering binder.

Limited Warranty: Mueller Steam Specialty warrants each product to be free from defects in material and workmanship under normal usage for a period of one year from the date of original shipment. In the event of such defects within the warranty period, the Company will, at its option, replace or recondition the product without charge. This shall constitute the sole and exclusive remedy for breach of warranty, and the Company shall not be responsible for any incidental, special or consequential damages, including without limitation, lost profits or the cost of repairing or replacing other property which is damaged if this product does not work properly, other costs resulting from labor charges, delays, vandalism, negligence, fouling caused by foreign material, damage from adverse water conditions, chemical, or any other circumstances over which the Company has no control. This warranty shall be invalidated by any abuse, misuse, misapplication or improper installation of the product. THIS WARRANTY IS IN LIEU OF ALL OTHER WARRANTIES, EXPRESS OR IMPLIED, INCLUDING ANY IMPLIED WARRANTIES OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE. Any implied warranties that are imposed by law are limited in duration to one year.

Some States do not allow limitations on how long an implied warranty lasts, and some States do not allow the exclusion or limitation of incidental or consequential damages. Therefore the above limitations may not apply to you. This Limited Warranty gives you specific legal rights, and you may have other rights that vary from State to State. You should consult applicable state laws to determine your rights.



ES-MS-251-DI 2123 © 2021 Watts