### **Model: 752**

Job Name	Contractor
Job Location	Approval
Engineer	Contractor's P.O. No.
Ligition	Contractor of .C. INC.
Approval	Representative

## **LEAD FREE\***

# Cast Iron Flanged End Y Strainers

Model: 752 Sizes: 1½"- 24"

WORKING PRESSURE-NON-SHOCK			
	ASME B16.1		
	500psi @ -20 to 150°F		
NPT Sizes	34.5 bar @ -29 to 65°C		
1½" - 12"	250psi @ 450°F		
	17.2 bar @ 232°C		
	300psi @ -20 to -150°F		
NPT Sizes	20.7 bar @ -29 to 65°C		
14"-24"	200psi @ 406°F		
	13.8 bar @ 208°C		

#### 752 - Class 250

#### **Features**

- Mueller "Breech-Lok Strainers"
- Furnished as standard in sizes 8" and larger
- A one-quarter turn securely locks the screen in its seat
- Allows for easy bolting of the cover flange
- Tapered seats in both the body and cover flange retain screen and prevent particle bypass

#### Construction

• Gasketed cover, O-ring seats available

#### Self-Cleaning

 Self-cleaning is accomplished by opening the plug or valve connected to the blowoff outlet

#### **Blowoff Outlets**

- Outlets are NPT tapped
- Sizes of tapping specified on next page
- Not normally furnished with plug. Plug available, specify with order



Model 752

#### Capacity

- Generously proportioned bodies
- Open Area Ratio much greater than pipe size, ensuring low pressure drop

#### Screens

		STANDARD (WATER)		STEAM RECOMMENDATION		
MODEL	SIZES	MATERIAL	OPENING	MATERIAL	OPENING	
752	11/2" - 4"	304SS .062 perf		304SS	.045 perf	
	5" - 10"	304SS	.125 perf	304SS	.045 perf	
	10" & Up	304SS	.125 perf	304SS	.062 perf	

#### NOTICE


The information contained herein is not intended to replace the full product installation and safety information available or the experience of a trained product installer. You are required to thoroughly read all installation instructions and product safety information before beginning the installation of this product.

\*The wetted surface of this product contacted by consumable water contains less than 0.25% of lead by weight.

Mueller Steam Specialty product specifications in U.S. customary units and metric are approximate and are provided for reference only. For precise measurements, please contact Mueller Steam Specialty Technical Service. Mueller Steam Specialty reserves the right to change or modify product design, construction, specifications, or materials without prior notice and without incurring any obligation to make such changes and modifications on Mueller Steam Specialty products previously or subsequently sold.



#### **Materials**



BILL OF MATERIAL - 752				
ITEM	DESCRIPTION MATERIAL			
1	BODY	Cast Iron ASTM A126-B		
2	COVER **	Cast Iron ASTM A126-B		
3	SCREEN	304 SS		
4	GASKET	Non-Asbestos		
5	HEX HEAD CAP SCREWS	SAE J429 Gr. 5		

<sup>\*\*</sup> Cover may be manufactured from equivalent grade plate material

#### **Pressure Drop**

See Pressure Drop Charts in Technical Data section of the Mueller Steam Specialty Engineering binder.  $C_V$  values are noted in the Dimensions and Weights table below.

#### **Dimensions and Weights**

SIZE	DIMENSIONS				WEIGHT			
	1	A	В		C			
in.	in.	mm	in.	mm	in.	mm	lbs.	kgs.
11/2	81/16	204	<b>4</b> ¾	121	1/2	15	24	10.9
2	95/16	237	6	152	1/2	15	26	12
21/2	<b>11</b> ½16	281	71//8	181	1	25	40	18
3	12%	321	91/8	232	11/4	32	59	26.8
31/2	14%	365	9	229	11/4	32	76	34
4	15%	397	107//8	276	11/2	40	93	42
5	181/4	464	<b>12</b> <sup>15</sup> ⁄ <sub>16</sub>	329	2	50	146	66
6	203/16	512	141/2	368	2	50	194	88
8	251/8	638	<b>16</b> <sup>7</sup> / <sub>16</sub>	418	2	50	316	143
10	291/8	739	21	533	2	50	475	215
12	33¾	857	25	635	2	50	750	3740
14	38¾	984	28¾	730	2	50	908	412
16	441/8	1128	295/8	752	2	50	1135	515
18	47¾	1213	3411/16	881	2	50	2400	1090
20	56	1422	39	991	2	50	3350	1522
24	57½	1461	45	1143	2	50	4705	2138

Apply for Certified Drawings.

Limited Warranty: Mueller Steam Specialty warrants each product to be free from defects in material and workmanship under normal usage for a period of one year from the date of original shipment. In the event of such defects within the warranty period, the Company will, at its option, replace or recondition the product without charge. This shall constitute the sole and exclusive remedy for breach of warranty, and the Company shall not be responsible for any incidental, special or consequential damages, including without limitation, lost profits or the cost of repairing or replacing other property which is damaged if this product does not work properly, other costs resulting from labor charges, delays, vandalism, negligence, fouling caused by foreign material, damage from adverse water conditions, chemical, or any other circumstances over which the Company has no control. This warranty shall be invalidated by any abuse, misuse, misuse, misuse, branch or improper installation of the product. THIS WARRANTIES, EXPRESS OR IMPLIED, INCLUDING ANY IMPLIED WARRANTIES OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE. Any implied warranties that are imposed by law are limited in duration to one year.

Some States do not allow limitations on how long an implied warranty lasts, and some States do not allow the exclusion or limitation of incidental or consequential damages. Therefore the above limitations may not apply to you. This Limited Warranty gives you specific legal rights, and you may have other rights that vary from State to State. You should consult applicable state laws to determine your rights.

