

Engineering Specification

Job Name _____

Contractor _____

Job Location _____

Approval _____

Engineer _____

Contractor's P.O. No. _____

Approval _____

Representative _____

CO20

Cast Iron Adjustable Floor
Cleanout w/Round Top

Specification

Watts Light Commercial CO20 cast iron adjustable floor cleanout with round nickel bronze, ductile iron, or stainless steel non-skid top, and removable gasketed cleanout plug.




Call customer service if you need assistance with technical details.

PIPE SIZING	
SUFFIX	DESCRIPTION
-2PT	2"(51) Push On
-3NH	3"(76) No Hub
-3PT	3"(76) Push On
-4NH	4"(102) No Hub
-4PT	4"(102) Push On

OPTIONS	
SUFFIX	DESCRIPTION
-DI	Ductile Iron Top
-SS	Stainless Steel Top
-VP	Vandal Proof Screws

NOTICE

The information contained herein is not intended to replace the full product installation and safety information available or the experience of a trained product installer. You are required to thoroughly read all installation instructions and product safety information before beginning the installation of this product.



Watts product specifications in U.S. customary units and metric are approximate and are provided for reference only. For precise measurements, please contact Watts Technical Service. Watts reserves the right to change or modify product design, construction, specifications, or materials without prior notice and without incurring any obligation to make such changes and modifications on Watts products previously or subsequently sold.

