Troubleshoot With Confidence

With accurate data on hand, on-site

Flo**Pro**MD 3-in-1

Gas Measurement Diagnostic System





Real Time Data via Free, User-Friendly Bluetooth App (Android™ and iOS™)



Calculates Everything for You



Flowmeter, Manometer, & Calculator in One Tool



Compatible with Natural Gas (NG) & Propane (LPG)



Leave FloPro-MD on-site to collect data while you're away

Go.Dormont.com/flopromd

Diagnose With Confidence Easily Provide Proof











Install

Connect

Diagnose

Report

Intermittent gas appliance issues are tough to diagnose. FlowPro-MD helps you troubleshoot and diagnose gas-related issues on hand, on-site. Troubleshoot with confidence, reduce callbacks, and provide solid service your customers can count on.

- Easy installation with common, off-the-shelf tools
- Ideal for servicing, diagnostics & routine maintenance
- Perfect for commercial kitchen appliances, boilers, tankless water heaters, furnaces, dryers, kitchen appliances, standby power generators, light commercial boilers and water heaters & rooftop units
- App available for download at these locations





To speak to a Dormont Rep

(800) 367-6668 (USA) (905) 332-4090 (Canada) (52) 81-1001-8600 (Latin America)

FEATURES & FUNCTIONS

Operating Range

- Natural Gas (NG): 15,000 to 325,000 BTU/Hr
- Propane (LPG): 15,000 to 500,000 BTU/Hr

Measures & Displays

- Gas Flow Rate: Cubic Feet/ Hour (CFH)
- Gas Flow Capacity: BTU/Hour
- Gas pressure measurement: inches water column (" w.c.)

Materials & Connections

- Corrosion-resistant aluminum construction with black finish
- Standard 3/4" Female NPT connections
- Annunciator LEDs communicate device status

