Job Name	Contractor
Job Location	Approval
Engineer	Contractor's P.O. No.
Approval	Representative

# LEAD FREE\*

# AquaLock™ Plastic **Elbows**

Watts AquaLock push-to-connect Elbows are designed and manufactured for many years of trouble free service. Produced of off white Polysulfone, a high performance thermal plastic material, the Watts AquaLock design allows for quick and easy connections without the use of installation tools.

# **Specifications**

Connection shall be made using Watts AquaLock Plastic fitting with Integral Collet and O-Ring guide. Fitting shall be able to fully rotate under pressure and allow for easy disconnect and reuse without the use of disconnection tools. Fitting must not disassemble to disconnect.

## **Approvals**

NSF-61, NSF-14, CSA B137.5, ASTM F877, UPC, ASSE 1061

## Ratings

100psi @ 180°F (6.8 bar @ 82°C) 250psi @ 75°F (17.3 bar @ 24°C)

### Example

3512-1008 35 = Plastic 12 = Hose Barb Elbow  $1008 = \frac{1}{2}$ " CTS x  $\frac{1}{2}$ " Barb

### **A** CAUTION

The polysulfone material used in the AquaLock™ fittings can be compromised by exposure to volatile organic compounds (VOC's) and caustic chemicals. Therefore, **DO NOT** expose this product to any such chemical or foreign substance, which would include exposure to the following products: Pipe Dopes (thread sealants), bug sprays, lubricants, cleaners, paints, bleaches, acids, solder fluxes, plastic piping primers and cements, oxidizing agents, alkaline solutions, thinners, fuels, oil based caulks, hydrocarbons, spray foam of foaming agents (insulation).

It is also recommended that all threaded connections be made with Teflon® tape only.

# AquaLock™





3512







3518



3519





#### NOTICE

The information contained herein is not intended to replace the full product installation and safety information available or the experience of a trained product installer. You are required to thoroughly read all installation instructions and product safety information before beginning the installation of this product.


\*The wetted surface of this product contacted by consumable water contains less than 0.25% of lead by weight.



# Dimensions - Weights - Weight and Dimensions are approximate (tolerance +/ - 1/8)


## Hose Barb Elbows

MODEL	ORDERING Code	SIZE & CONNECTION	ITEM LENGTH		ITEM LENGTH		ITEM HEIGHT		ITEM V	VEIGHT
			A		В					
			in.	mm	in.	mm	OZ.	gr.		
Package Type: Sin	igle Pack									
3512-1008	0959472	1/2" CTS x 1/2"Barb	11/2	38	21//8	54	0.3	.14		
Package Type: Bulk Pack										
3512-1008CP	81902902	1/2" CTS x 1/2"Barb	1½	38	21//8	54	0.3	.14		



## **Elbow**

MODEL	ORDERING CODE	SIZE & CONNECTION	ITEM LENGTH		ITEM HEIGHT		ITEM WEIGHT			
			l A	4		3				
			in.	mm	in.	mm	OZ.	gr.		
Package Type: Sin	Package Type: Single Pack									
3517-08	0959035	3%" CTS	13/4	44	<sup>15</sup> / <sub>16</sub>	24	0.6	.27		
3517-10	0959087	½" CTS	21//8	54	11//8	29	1	.45		
3517-14	0959138	3/4" CTS	211/16	68	1%	35	1.8	.81		
3517-18	0959300	1" CTS	3	76	11/2	38	2.4	1.09		
Package Type: Bu	lk Pack									
3517-08CP	81902933	3%" CTS	13/4	44	<sup>15</sup> ⁄ <sub>16</sub>	24	0.6	.27		
3517-10CP	81902934	½" CTS	21/8	54	11//8	29	1	.45		
3517-14CP	81902936	3/4" CTS	211/16	68	1%	35	1.8	.81		
3517-18CP	81902939	1" CTS	3	76	1½	38	2.4	1.09		




## **Reducing Elbow**

MODEL	ORDERING CODE	SIZE & CONNECTION	ITEM LENGTH		ITEM HEIGHT		ITEM LENGTH ITEM HEIGHT		ITEM V	VEIGHT
			A		В					
			in.	mm	in.	mm	oz.	gr.		
Package Type: Single Pack										
3517R-1410	0959339	3/4" CTS x 1/2" CTS	21/2	63.5	11/4	31.75	1.4	0.63		


## Stackable Elbows

MODEL	ORDERING CODE	SIZE & CONNECTION	ITEM LENGTH		ITEM LENGTH		ITEM I	HEIGHT	ITEM V	VEIGHT
			,	4		3				
			in.	mm	in.	mm	OZ.	gr.		
Package Type: Single Pack										
3518-08	0959036	3%" CTS	13/4	44	<sup>15</sup> / <sub>16</sub>	24	0.4	.18		
3518-10	0959096	½" CTS	2	51	11//8	29	0.7	.32		
3518-14	0959141	3/4" CTS	25/8	67	1%"	35	0.8	.36		
3518-18	0959794	1" CTS	3	76	13/4	45	1.9	.86		
Package Type: Bu	lk Pack									
3518-08CP	81902940	3%" CTS	13/4	44	<sup>15</sup> / <sub>16</sub>	24	0.4	.18		
3518-10CP	81902941	1/2" CTS	2	51	11//8	29	0.7	.32		
3518-14CP	81902943	3/4" CTS	25/8	67	1%"	35	0.8	.36		
3518-18CP	81902945	1" CTS	3	76	13/4	45	1.9	.86		




## **Drop Ear Elbows**

ORDERING CODE	SIZE & CONNECTION	ITEM LENGTH		ITEM HEIGHT		ITEM LENGTH ITEM HEIGHT ITEN		ITEM V	VEIGHT
		A		В					
		in.	mm	in.	mm	OZ.	gr.		
igle Pack		·	,						
0959092	½" CTS x ½" NPT	21/8	54	1 13/16	46	1.1	.50		
Package Type: Bulk Pack									
81902958	½" CTS x ½" NPT	21/8	54	<b>1</b> 13/16	46	1.1	.50		
	ORDERING CODE  Igle Pack 0959092  Ik Pack	ORDERING SIZE & CONNECTION CODE  Igle Pack  0959092  ½" CTS x ½" NPT  Ik Pack	ORDERING CODE         SIZE & CONNECTION         ITEM L           in.         in.           1gle Pack         0959092         ½" CTS x ½" NPT         2½           Ik Pack         2½	ORDERING CODE         SIZE & CONNECTION         ITEM LENGTH           A         in.         mm           Igle Pack         0959092         ½" CTS x ½" NPT         2½         54           Ik Pack         1k Pack <td>ORDERING CODE         SIZE &amp; CONNECTION         ITEM LENGTH         ITEM ITEM ITEM ITEM ITEM ITEM ITEM ITEM</td> <td>ORDERING CODE         SIZE &amp; CONNECTION         ITEM LENGTH         ITEM HEIGHT           A         B         in.         mm         in.         mm           Igle Pack         0959092         ½" CTS x ½" NPT         2½         54         1½/6         46           Ik Pack</td> <td>ORDERING CODE         SIZE &amp; CONNECTION         ITEM LENGTH         ITEM HEIGHT         ITEM V           A         B         in.         mm         in.         mm         oz.           Igle Pack         0959092         ½" CTS x ½" NPT         2½         54         113/16         46         1.1           Ik Pack         Ik Pack</td>	ORDERING CODE         SIZE & CONNECTION         ITEM LENGTH         ITEM ITEM ITEM ITEM ITEM ITEM ITEM ITEM	ORDERING CODE         SIZE & CONNECTION         ITEM LENGTH         ITEM HEIGHT           A         B         in.         mm         in.         mm           Igle Pack         0959092         ½" CTS x ½" NPT         2½         54         1½/6         46           Ik Pack	ORDERING CODE         SIZE & CONNECTION         ITEM LENGTH         ITEM HEIGHT         ITEM V           A         B         in.         mm         in.         mm         oz.           Igle Pack         0959092         ½" CTS x ½" NPT         2½         54         113/16         46         1.1           Ik Pack         Ik Pack		




## Male Elbow

MODEL	ORDERING Code	SIZE & CONNECTION	ITEM LENGTH		ITEM HEIGHT		NGTH ITEM HEIGHT ITEM		ITEM V	VEIGHT
			/	4	E	3				
			in.	mm	in.	mm	OZ.	gr.		
Package Type: Sin	igle Pack									
3519-1006	0959089	½"CTS x ¾"NPT	2	51	11//8	29	0.7	.32		
3519-1008	0959088	1/2" CTS x 1/2"NPT	2	51	11//8	29	0.7	.32		
3519-1412	0959791	3/4" CTS x 3/4"NPT	21/4	57.15	1½	38.1	1	.45		
3519-1816	0959795	1" CTS x 1" NPT	23/4	70	13/4	45	1.9	.86		
Package Type: Bu	lk Pack									
3519-1006CP	81902947	1/2"CTS x 3/8"NPT	2	51	11//8	29	0.7	.32		
3519-1008CP	81902948	½" CTS x ½"NPT	2	51	11//8	29	0.7	.32		
3519-1816CP	81902949	1" CTS x 1"NPT	23/4	70	13/4	45	1.9	.86		



## Female Swivel Elbows

MODEL	ORDERING Code	SIZE & CONNECTION	ITEM LENGTH		ITEM HEIGHT		ITEM V	VEIGHT	
				4	E	3			
			in.	mm	in.	mm	OZ.	gr.	
Package Type: Single Pack									
3520-0808	0959037	3/8" CTS x 1/2"NPS	2	51	1%	41	0.7	.32	
3520-0813	0959043	3/4" CTS x 3/4" Closet	2	51	1%	41	0.8	.36	
3520-1008	0959090	1/2" CTS x 3/4"NPS	23/16	56	2	51	1	.45	
3520-1012	0959091	½" CTS x ¾"NPS	23/16	56	2	51	1.2	.54	
3520-1013	0959093	½" CTS x ¾"Closet	23/16	56	2	51	1.1	.50	
3520-1014	0959293	1/2" CTS x 3/4"FGHT	23/16	56	2	51	1	.45	
3520-1412	0959792	3/4" CTS x 3/4"NPS	23/16	56	2	51	1	.45	
Package Type: Bu	lk Pack								
3520-0808CP	81902950	3%" CTS x 1/2"NPS	2	51	1%	41	0.7	.32	
3520-1008CP	81902952	½" CTS x ½"NPS	23/16	56	2	51	1	.45	
3520-1012CP	81902955	½" CTS x ¾"NPS	23/16	56	2	51	1.2	.54	
3520-1014CP	81902957	1/2" CTS x 3/4"FGHT	23/16	56	2	51	1	.45	





USA: T: (978) 689-6066 • F: (978) 975-8350 • Watts.com
Canada: T: (905) 332-4090 • F: (905) 332-7068 • Watts.ca
Latin America: T: (52) 55-4122-0138 • Watts.com

ES-AQ-35Elbows 1935 © 2019 Watts