

Engineering Specification

Job Name _____

Contractor _____

Job Location _____

Approval _____

Engineer _____

Contractor's P.O. No. _____

Approval _____

Representative _____

FD20-R

On-Grade Cast Iron Adjustable Floor Drain w/Round Strainer

Specification


Watts Light Commercial FD20-R on-grade cast iron floor drain with adjustable round nickel bronze, ductile iron, or stainless steel strainer.

Call customer service if you need assistance with technical details.

PIPE SIZING	
SUFFIX	DESCRIPTION
-2NH	2"(51) No Hub
-2PT	2"(51) Push-On
-3NH	3"(76) No Hub
-3PT	3"(76) Push-On
-4NH	4"(102) No Hub
-4PT	4"(102) Push-On

STRAINERS	
SUFFIX	DESCRIPTION
-5R	5"(127) Round Nickel Bronze
-5RDI	5"(127) Round Ductile Iron
-5RSS	5"(127) Round Stainless Steel
-6R	6"(152) Round Nickel Bronze
-6RSS	6"(152) Round Stainless Steel

OPTIONS	
SUFFIX	DESCRIPTION
-B	Sediment Bucket
-BV	Backwater Valve
-E	Strainer Extension
-G	CI Round Funnel
-GNB	NB Round Funnel
-H	CI Oval Funnel
-HNB	NB Oval Funnel
-TPT	Trap Primer Tapping
-VP	Vandal Proof Screws



NOTICE

The information contained herein is not intended to replace the full product installation and safety information available or the experience of a trained product installer. You are required to thoroughly read all installation instructions and product safety information before beginning the installation of this product.

Watts product specifications in U.S. customary units and metric are approximate and are provided for reference only. For precise measurements, please contact Watts Technical Service. Watts reserves the right to change or modify product design, construction, specifications, or materials without prior notice and without incurring any obligation to make such changes and modifications on Watts products previously or subsequently sold.

