

Engineering Specification

Job Name _____

Contractor _____

Job Location _____

Approval _____

Engineer _____

Contractor's P.O. No. _____

Approval _____

Representative _____

FS55

Porcelain Enameled Cast Iron Floor Sink

Specification


Watts Light Commercial FS55 12" square x 6" deep white porcelain enamel coated cast iron floor sink with loose set grate, and aluminum dome bottom strainer.

Call customer service if you need assistance with technical details.



PIPE SIZING	
SUFFIX	DESCRIPTION
2NH	2"(51) No Hub
2PT	2"(51) Push-On
3NH	3"(76) No-Hub
3PT	3"(76) Push-On
4NH	4"(102) No Hub
4PT	4"(102) Push-On

OPTIONS	
SUFFIX	DESCRIPTION
-2G	1/2 Grate
-3G	3/4 Grate
-B	Sediment Bucket
-G	CI Round Funnel
-GNB	NB Round Funnel
-H	CI Oval Funnel
-HNB	NB Oval Funnel
-LG	Less Grate
-NB	Nickel Bronze Top
-VP	Vandal Proof Screws (w/-NB Only)



NOTICE

The information contained herein is not intended to replace the full product installation and safety information available or the experience of a trained product installer. You are required to thoroughly read all installation instructions and product safety information before beginning the installation of this product.

Watts product specifications in U.S. customary units and metric are approximate and are provided for reference only. For precise measurements, please contact Watts Technical Service. Watts reserves the right to change or modify product design, construction, specifications, or materials without prior notice and without incurring any obligation to make such changes and modifications on Watts products previously or subsequently sold.



USA: T: (800) 338-2581 • Watts.com

Canada: T: (888) 208-8927 • Watts.ca

Latin America: T: (52) 55-4122-0138 • Watts.com

ES-WDLC-FS55 2636

© 2026 Watts