ANKA® Series

Rural Water Solutions

Agricultural, Irrigation, Rural and Municipal, & Plumbing Applications





ANKA® Series of fittings, valves and hose nozzles are robust high quality and built to last and perform. Made from NSF approved fiber glass reinforced nylon and acetyl ANKA products are non-corrosive and UV stabilized.


High pressure, leakfree and reuseable fittings, full flow valves and indestructible nozzles; ANKA series has a solution. Serving the Rural and Municipal Water, Agricultural, Horticultural, Industrial, Irrigation, Marine, Rain Water Harvesting and Hydroponic markets.

Contents

lose Nozzles
Wash Down/ Tuff Trigger™ Spray Guns4-5
Foot & Check Valves6-7
Pipe Fittings8-10
Pipes Unions1
Quick-Lock Couplings1








Hose Nozzles

AHN Series

Our hose nozzles are durable, robust and reliable to ensure a long life withstanding high impact and excessive wear. ANKA hose nozzles operate with a quick action on/off and fully adjustable spray pattern providing very high flow rates ensuring a fast and efficient wash down. Applications include Dairy, Livestock, Agricultural, Heavy Equipment, Industrial, Landscape and Irrigation, Horticultural and marine wash down.

- Quick action ON/OFF
- Full Flow and High Impact
- Adjustable Spray Patterns
- Serviceable kits available
- Non-marking rubber outer ring designed to protect again high impact and excessive wear
- Durable Made of fiberglass reinforced nylon
- Made from potable and food grade materials



Wash Down Nozzles

FEATURES & BENEFITS

- Protective outer rubber ring
- High flow rates
- Durable
- Quick action on/off
- Adjustable spray pattern
- Non-corrodible high-quality materials
- Serviceable

SPARES & ACCESSORIES

- Hose tails
- Service Kits

SPECIFICATIONS

Materials: Fiberglass Reinforced Nylon body **Temperature Range:** Cold water applications

Ordering Code	Model No.	Size (in)
88005321	AHNS20 USA	3/4"
88005322	AHNS25-25	1"
88005323	AHNS32-32	1 1/4"
88005324	AHN32-32	1 1/4"
88005325	AHN40-40	1 1/2"







AHN32 1 ¼" Large



AHNS32 1 1/4" Small



AHN25 1" Small



Hose Reel Nozzle

FEATURES & BENEFITS

- Protective outer rubber ring
- Durable
- Quick action on/off
- Adjustable spray pattern
- Non-corrodible high-quality materials

AVAILABLE SIZES

• 3/4"

SPARES & ACCESSORIES

• Hose Tail









Tuff Trigger™ Spray Gun

APPLICATION

Tuff Trigger™ Spray guns are made from high quality, industrial grade glass fiber reinforced nylon and nitrile rubber or viton seals (hot water trigger) making them durable and reliable. Practical features like a quick on off action, adjustable spray pattern, adaptable 3/4" hose connection and a protective and non-marketing outer rubber ring.

Applications include dairy, livestock, agricultural, heavy equipment, industrial, landscape, lawn/garden, Irrigation and Horticultural, Marine and wash down.

FEATURES & BENEFITS

- Adjustable Spray Pattern
- High (full) flow
- Non corrosive
- High quality, durable glass fiber reinforced nylon
- Serviceable
- Quick Action On/Off
- Max working pressure 100psi
- Hot water 180°F
- Non-marketing protective rubber outer ring

SPECIFICATIONS

Materials: Fiberglass Reinforced Nylon body **Temperature Range:** Cold water applications

Note: The Hot Water Trigger Spray Gun is recommended for temperatures above 180°F (82°C). At that temperature, a heat-safe connection such as ANKA Male Coupling must be used.


Ordering Code	Model No.	Size (in)
88005319	AHNT20 USA	3/4"
88005320	AHNT20 USA HW	3/4"

SPARES & ACCESSORIES


• Service Kits



Performance Curve (Small Hose Nozzles)



Performance Curve (Large Hose Nozzles)



Foot & Check Valves

APPLICATION

ANKA Foot and Check Valves are plunger style and full flow. Unlike traditional poppet-style valves, ANKA valves are spring loaded, plunger style, non-return valves. Providing an upward of more than 60% more flow, can be installed at any angle and open with just 1/2 psi, ANKA valves are high performance, high quality and durable. Designed for use in line check or at the end of a suction line to assist the pump in drawing water while also maintaining prime in the line.

Manufactured of potable, high grade, fiberglass reinforced nylon and acetyl, ANKA valves are durable and reliable.

Applications include, rural water supply, pump and pressure, irrigation, agricultural, industrial, plumbing and marine; essentially anywhere water or fluid flows!

FEATURES & BENEFITS

- Full Flow (plunger valve)
- Versatile Operates at any angle
- Outperforms brass and PVC valves
- Non-Corrosive
- Serviceable
- Durable glass reinforced nylon
- Made from NSF 61 potable materials

HOW IT WORKS

- Plunger opens fully when pump turns on
- Water flows through valve
- Plunger securely closes and seals eliminating back flow

SPECIFICATIONS

Working Pressure: 230psi (1600kpa) @ 68°F (20°C) Temperature Range: Cold water applications

Threads: NPT (National Pipe Threads)

Check valves are FIPT (Female pipe thread)

Materials: Glass Fiber Reinforced Nylon body

316 Stainless Steel spring

Acetyl plunger


Nitrile rubber washer & O-rings

Polypropylene screen (Foot Valves only)





Check Valves



Foot & Check Valves

AVAILABLE SIZES

Foot Valve

- 1/2"
- 3/4"
- 1"
- 11/4"
- 11/2"
- 2"

Check Valve

- ½" x ½"
- ½" x ½"
- 3/4" x 3/4"
- 1" x 1"
- 1 1/4" x 11/4"
- 1 ½" x 1½"
- 2" x 2"


FOOT VALVES

Ordering Code	Model No.	Size (in)
88005302	AFV34	3/4"
88005304	AFV1	1"
88005305	AFV114	1 1/4"
88005306	AFV112	1 1/2"
88005307	AFV2	2"

CHECK VALVES

Ordering Code	Model No.	Size (in)
88001961	ACV15	1/2"
88005308	ACV34	3/4"
88005309	ACV1	1"
88005310	ACV114	1 1/4"
88005311	ACV112	1 1/2"
88005312	ACV2	2"

Performance Curve (Foot & Check Valves)





Pipe Fittings

ANKA series

ANKA fittings are high pressure, insert- compression poly pipe fittings made from high quality, potable, non corrosive and durable fiberglass reinforced nylon. An easy to use and leak free connection for Rural, Municipal, Pump and Pressure, Irrigation, Agricultural, Hydroponic and Marine applications.

- Non Corrosive made from extremely durable, high quality potable materials
- Fiberglass reinforced nylon
- Easy to use Reuseable, one piece fitting
- Leak Free* Unique captive self threading nut
- UV Stabilized for above ground or below grade applications
- No Tools required
- Designed for use with all ID (inside diameter) rated pipe
- Can be used on poly pipe, clear or braided hose, garden or wash down hose



ASC STRAIGHT COUPLING



Available sizes: 1/2", 3/4", 1", 1 1/4"

Ordering Code	Model No.	Size (in)
88005243	ASC12	1/2"
88005244	ASC34	3/4"
88005245	ASC1	1"
88005246	ASC114	1 1/4"



ASC REDUCING STRAIGHT COUPLING AND ARC



Available sizes: 1/2", 3/4", 1", 1 1/4"

Ordering Code	Model No.	Size (in)
88005247	ASC3412	3/4" x 1/2"
88005248	ARSC112	1" x 1/2"
88005249	ARSC134	1" x 3/4"
88005250	ARSC1141	11/4" x 1"





Available sizes: 1/2", 3/4", 1", 1 1/4"

Ordering Code	Model No.	Size (in)
88005251	AMA12	1/2"
88005252	AMA34	3/4"
88005253	AMA1	1"
88005254	AMA114	1 1/4"








Available sizes: 1/2", 3/4", 1", 1 1/4"

Ordering Code	Model No.	Size (in)
88005258	AFA12	1/2"
88005259	AFA34	3/4"
88005260	AFA1	1"
88005261	AFA114	1 1/4"

ARMA REDUCING MALE

1 1/4" x 1"





Ordering Code	Model No.	Size (in)
88005255	ARMA1234	3/4" x 1/2"
88005256	ARMA121	1" x 1/2"
88005257	ARMA1114	1" x 3/4"

ARFA REDUCING FEMALE **ADAPTER**

Available sizes: 3/4" x 1/2", 1" x 3/4", 1 1/4" x 1", 1 1/2" x 1 1/4"



Ordering Code	Model No.	Size (in)
88005262	ARFA1234	1/2" x 3/4"

Note: All threaded connections are NPT (national pipe thread). Available in Male NPT and Female NPT configurations.

KEY:

Female Couplings, Elbows & Tees

Elbows

Male Couplings, Elbows & Tees

Tees

Reducing Couplings, Elbows & Tees

Straight Couplings

Bracket Elbows





Available sizes: 1/2", 3/4", 1", 1 1/4"



Ordering Code	Model No.	Size (in)
88005263	AT12	1/2"
88005264	AT34	3/4"
88005265	AT1	1"
88005266	AT114	1 1/4"

AFT FEMALE TEE



Available sizes: 1/2", 3/4", 1", 1 1/4"



Ordering Code	Model No.	Size (in)
88005271	AFT12	1/2"
88005273	AFT34	3/4"
88005274	AFT1	1"

AME MALE ELBOW



Available sizes: $\frac{1}{2}$ ", $\frac{3}{4}$ ", $\frac{1}{4}$ ", $\frac{1}{4}$ "

_	3

Ordering Code	Model No.	Size (in)
88005279	AME12	1/2"
88005280	AME34	3/4"
88005281	AME1	1"
88005282	AME114	1 1/4"

ARFE REDUCING FEMALE ELBOW



Available sizes: $\frac{1}{2}$ " x $\frac{3}{4}$ ", 1" x $\frac{1}{2}$ ", 1" x $\frac{3}{4}$ "

Ordering Code	Model No.	Size (in)
88005287	ARFE3412	3/4" x 1/2"
88005288	ARFE112	1" x 1/2"
88005289	ARFE134	1" x 3/4"

AHF YARD HYDRANT ELBOW



Available sizes: 3/4" x 3/4", 1" x 3/4"

Ordering Code	Model No.	Size (in)
88225113	AHF34	3/4" x 3/4"
88225114	AHF134	1" x 3/4"

ART REDUCING TEE



Available sizes: 3/4" x 1/2", 1" x 1/2", 1" x ¾", 1 ¼" x 1"



Ordering Code	Model No.	Size (in)
88005267	ART3412	3/4" x 1/2"
88005268	ART112	1" x 1/2"
88005269	ART134	1" x 3/4"
88005270	ART1141	1" 1/4 x 1"

AE ELBOW



Available sizes: $\frac{1}{2}$ ", $\frac{3}{4}$ ", $\frac{1}{4}$ ", $\frac{1}{4}$ "



Ordering Code	Size (in)	
88005275	AE12	1/2"
88005276	AE34	3/4"
88005277	AE1	1"
88005278	AF114	1 1/4"

AFE FEMALE ELBOW



Available sizes: 1/2", 3/4", 1", 1 1/4"

Ordering Code	Model No.	Size (in)
88005280	AFE12	1/2"
88005284	AFE34	3/4"
88005285	AFE1	1"
88005286	ΔΕΕ11/I	1 1///"

APU PUMP UNION



Available sizes: 3/4", 1", 1 1/4"

Ordering Code	Model No.	Size (in)
88005290	APU34	3/4"
88005291	APU1	1"
88005292	APU114	1 1/4"

How to use ANKA fittings

These strong, non corrosive and easy to use fittings are suited for a wide range of applications including rural and municipal water supply, pump and pressure systems, agricultural, livestock watering, irrigation, lawn and garden, hydroponic and marine.

Designed to fit a large range of pipe and hose including SIDR 9.5, 11, 15 and 19 (60-200psi) polyethylene pipe in all densities (low to high density), clear and braided hose, garden and wash down hose or tubing. The captive nut is tapered to connect to a variety of ID (inside diameter) or nominally sizes pipe and tube.

ANKA insert is a double barbed insert connection with a captive nut ensuring you get a consistent and leak free fit. The barb is tapered and non restrictive to flow and is designed to work with the captive blue nut to secure and grip to the surface area on the pipe compressing insert, pipe and nut for a leak free connection.

SPECIFICATIONS

Material: Glass Fiber Reinforced Nylon

Working Pressure: 230psi (1600kpa) @ 68°F (20°C) Temperature Range: 34°F - 140°F (1°C - 60°C)

INSTALLATION

- Can be fitted to cold pipe in most situations
- Softening with hot water will help installation
- Option use thread tape or thread sealant on all threads, we recommend Loctite 5331
- Simply push the pipe over the barbs up to the "stop", tighten the BLUE NUT by hand, then tighten 1-2 turns with a wrench.




1 Cut & clean pipe, then slide nut away from pipe stop.



Push pipe over the barbed fitting tail until it touches the pipe stop.



Hand tighten the Easy Grip nut, then moderately tighten with a wrench.



Pipe Unions

AFU Series

ANKA pipe unions can be used in place of traditional metal fittings, designed for in-line servicing, connect/disconnect and removal of valves, pumps, pipe and fittings. Made from high grade fiberglass reinforced nylon for durability and reliability making servicing and winterizing easy.

FEATURES & BENEFITS

- Can be taken apart for servicing
- Working Pressure: 230psi (1600kpa) @ 68°F (20°C)
- Temperature Range: 34°F 140°F (1°C 60°C)

Ordering Code	Model No.	Size (in)
88005293	AFU34	3/4"
88005294	AFU 1	1"
88005295	AFU 114	1 1/4"
88005984	AFU 112	1 1/2"
88005985	AFU2	2"

Quick-Lock Couplings

QL Series

ANKA Quick-lock couplings are designed for easy twist action connect and disconnect for in-line servicing, winterizing of pipe, fittings, pumps or valves. The quick-lock is easily adapted to a hose nozzles for easy wash down, versatility and durability in Agricultural applications.

ANKA Quick-locks are interchangeable with a consistent nitrile rubber seal ring allowing a wide range of configurations.

Quick-locks as similar to a camlock style fitting are used in a variety of applications such as rural water, agricultural watering and wash down, irrigation and industrial.





FEATURES & BENEFITS

- Universal connection to allow for custom combinations
- Leak free nitrile rubber o-ring seal
- Easily take piping apart for maintenance or to change lines
- Working Pressure: 0 150psi (0 1000kPa) @ 68°F (20°C)
- Temperature Range: 34°F 140°F (1°C 60°C)

Ordering Code	Model No.	Size (in)
88005313	AQLCM34 (male NPT)	3/4"
88005314	AQLCM1 (male NPT)	1"
88005315	AQLCM114 (male NPT)	1 1/4"
88005986	AQLCM112 (male NPT)	1 1/2"
88005316	AQLCF34 (female NPT)	3/4"
88005317	AQLCF1 (female NPT)	1"
88005318	AQLCF114 (female NPT)	1 1/4"
88005987	AQLCF112 (female NPT)	1 1/2"

\\\WATTS WORKS



Scan to start learning

LEARNING PROGRAM

Online Training

Spruce up your skills anywhere, anytime with Watts eLearning courses.

- up to 20 courses on pipe fittings and valves, from novice to expert training
 - Self-paced courses <10 minutes
 - · On-demand from any device
 - Earn tokens to spend lifestyle merchandise with Learn & Earn

Learning Centers

Our state-of-the-art classrooms staffed with highly-qualified instructors will give you the hands-on training you need to better understand the right product for the job and how to use and maintain it.

- North Andover, MA
- St. Pauls, NC
- Woodland, CA

- Burlington, Canada
- Blauvelt, NY

Watts Family of Brands









Dormont















Watts designs, manufactures, and sells an extensive line of flow control, water safety, water filtration & treatment, drainage, and PEX plumbing products.

The Watts family of companies provides a single source for solutions used to safely convey, conserve, and manage water.

Making Watts your single source for plumbing-related solutions will streamline your operations, save you money, and reduce the variety of repair parts needed for maintenance.



©2023 Watts