# **Solutions for Agriculture and Irrigation Applications**

ANKA® Pipe Fittings









ELBOW		FEMALE ELBOW		MALE ELBOW		FEMALE ADAPTOR	
AE12 US	1/2"	AFE12 US	1/2"	AME12 US	1/2" x 1/2"	AFA12 US	1/2"
AE34 US	3/4"	AFE34 US	3/4"	AME34 US	3/4" x 3/4"	AFA34 US	3/4"
AE1 US	1"	AFE1 US	1"	AME1 US	1" x 1"	AFA1 US	1"
AE114 US	1 1/4"	AFE114 US	1 1/4"	AME114 US	1 1/4" x 1 1/4"	AFA114 US	1 1/4"
		ARFE3412 US	3/4" x 1/2"			ARFA1234 US	1/2" x 3/4"
		ARFE112 US	1" x 1/2"				
		ARFE134 US	1 x 3/4"				











MALE ADAPTOR			COUPLING				FEMALE TEE		
AMA12 US	1/2"	ARMA1234 US	1/2 x 3/4"	ASC12 US	1/2"	ARSC3412 US	3/4" x 1/2"	AFT12	1/2" x 1/2" x 1/2"
AMA34 US	3/4"	ARMA121 US	1/2 x 1"	ASC34 US	3/4"	ARSC112 US	1" x 1/2"	AFT34	3/4" x 3/4" x 3/4"
AMA1US	1"	ARMA1114 US	1" x 1 1/4"	ASC1US	1"	ARSC134 US	1" x 3/4"	AFT1	1" x 1" x 1"
AMA114 US	1 1/4"			ASC114 US	1 1/4"	ARSC1141 US	1 1/4" x 1"		









TEE				PIPE UNION		FEMALE UNION	
AT12 US	1/2" x 1/2" x 1/2"	ART3412 US	3/4" x 3/4" x 1/2"	APU34 US	3/4"	AFU34 US	3/4"
AT34 US	3/4" x 3/4" x 3/4"	ART112 US	1" x 1" x 1/2"	APU1 US	1"	AFU1 US	1"
AT1 US	1" x 1" x 1"	ART134 US	1" x 1" x 3/4"	APU114 US	1 1/4"	AFU114 US	1 1/4"
AT114 US	1 1/4" x 1 1/4" x 1 1/4"	ART1141 US	1 1/4" x 1 1/4" x 1"				

### **Connecting to Poly-pipe**







## ANKA® Full Flow Valves

#### **How it Works**

- Plunger opens fully when pump turns on
- Increased water flows through valve
- Plunger securely closes & seals eliminating back flow




Reliable
Serviceable
Non-corrodible


# Features & Benefits

- Install at any angle
- Durable, versatile & non-corrodible materials
- Glass fibre reinforced nylon body
- Nitrile rubber o-ring seat/seal
- Stainless steel spring
- Serviceable
- Increased flow









# ANKA Quick-Lock Coupling



Service & Winterize with ease

PUMP / VALVE / INLINE DISCONNECT					
AQLCM34 US	3/4" (20mm) Male	AQLCF34 US	3/4" (20mm) Female		
AQLCM1 US	1" (25mm) Male	AQLCF1 US	1" (25mm) Female		
AQLCM114 US	1 1/4" (32mm) Male	AQLCF114 US	1 1/4" (32mm) Female		
AQLCM112 US	1 1/2" (40mm) Male	AQLCF112 US	1 1/2" (40mm) Female		

