For Commercial and Industrial Applications

Job Name	Contractor
Job Location	Approval
Engineer	Contractor's P.O. No.
Approval	Representative

Series HY42

Non-Freeze Wall Hydrants with Backflow Preventer

For Wall Thickness: 21/2" - 18"

Series HY42 is an automatic draining, freezeless wall hydrant with vacuum breaker-backflow preventer protection to prevent backsiphonage. It is designed to blend with modern architecture for installation on restaurants, schools, office buildings, churches, apartments, motels, stores, shopping centers and industrial buildings.

Features

- Threaded inlet connection 3/4" female or 1" male I.P.S.
- Tamper resistant Tee key operates hydrant
- Permanent type brass valve body
- Replaceable EPDM seat surface
- One piece valve plunger which accurately controls both the flow and drainage with a minimum number of turns
- · Casing consists of rugged brass pipe
- Exterior finish of chrome-plated brass

Standards

ASSE Standard 1019

Pressure

Maximum Operating Pressure: 125psi (8.6 bar)

Approvals


ASSE



Canadian Standards Association Listed by IAPMO

Specifications

Wall hydrant shall be exposed-type Watts automatic draining Series HY42 with vacuum breaker-backflow preventer protection, 3/4" hose thread nozzle, one piece valve plunger to control both flow and drain functions, rugged brass pipe construction, chrome- plated brass finish. Loose Tee key to be furnished with each hydrant. Complies with ASSE 1019.



Dimensions - Weights

MODEL	WALL THICKNESS		WEIGHT	
	in	mm	lbs.	kgs
HY42-025	21/2	64	3.5	1.6
HY42-04	4	100	4.5	2.0
HY42-06	6	150	4.9	2.2
HY42-08	8	200	5.3	2.4
HY42-10	10	250	5.7	2.6
HY42-12	12	305	6.1	2.8
HY42-14	14	356	6.5	2.9
HY42-16	16	406	6.9	3.1
HY42-18	18	457	7.3	3.3

NOTICE

The information contained herein is not intended to replace the full product installation and safety information available or the experience of a trained product installer. You are required to thoroughly read all installation instructions and product safety information before beginning the installation of this product.



Series HY42 (with Box)

Non-Freeze Wall Hydrants with Backflow Preventer and Mounting Box

For Wall Thickness: 21/2" - 18"

Series HY42 is an automatic draining, freezeless wall hydrant with vacuum breaker-backflow preventer protection to prevent backsiphonage enclosed in a flush mounting wall box. It is designed to blend with modern architecture for installation on restaurants, schools, office buildings, churches, apartments, motels, stores, shopping centers and industrial buildings.

Features

- Threaded inlet connection ³/₄" female or 1" male I.P.S.
- Tamper resistant Tee key operates hydrant
- Permanent type brass valve body
- Replaceable EPDM seat surface
- One piece valve plunger which accurately controls both the flow and drainage with a minimum number of turns
- Casing consists of rugged brass pipe
- · Exterior finish of chrome on brass
- Box door hinges in the up position, locks in the open position allowing hose free access to either side
- Exterior finish on box and door of chrome-plated brass

Standards

ASSE Standard 1019

Pressure

Maximum Operating Pressure: 125psi (8.6 bar)

Approvals


ASSE Listed by IAPMO





Specifications

Wall hydrant shall be exposed-type Watts automatic draining Series HY42 with vacuum breaker-backflow preventer protection, ¾" hose thread nozzle, one piece valve plunger to control both flow and drain functions, rugged brass pipe construction, locking chrome-plated brass box and hydrant. Mounting box locks in the up position allowing hose access to either side. Loose Tee key to be furnished with each hydrant. Complies with ASSE 1019.



Series HY42

MODEL	WALL THICKNESS		WEIGHT	
	in	mm	lbs.	kgs
HY42-025	21/2	64	3.5	1.6
HY42-04	4	102	4.5	2.0
HY42-06	6	152	4.9	2.2
HY42-08	8	203	5.3	2.4
HY42-10	10	254	5.7	2.6
HY42-12	12	305	6.1	2.8
HY42-14	14	356	6.5	2.9
HY42-16	16	406	6.9	3.1
HY42-18	18	457	7.3	3.3
HY42 Box			5.0	2.3
HY42 Tee-Key			1.0	0.5
HY42 Wall Clamp			2.0	0.9

5.25"

6.25"



USA: T: (978) 689-6066 • F: (978) 975-8350 • Watts.com Canada: T: (905) 332-4090 • F: (905) 332-7068 • Watts.ca Latin America: T: (52) 81-1001-8600 • Watts.com

ES-HY42 1018 © 2010 Watts