For Point-of-Use Water Applications

Job Location Approval Engineer Contractor's P.O. No.	Job Name	Contractor
	lob Location	Approval
Approval Representative		

LEAD FREE*

Series 10 Quick-Connect Tees

Watts Quick-Connect Tees are designed and manufactured for many years of trouble free service. Produced of off white polypropylene, a high performance thermoplastic material, the Watts Quick-Connect design allows for quick and easy connections without the use of installation tools.

Specifications

Connection shall be made using Watts Series 10 Quick-Connect fitting with Integral Collet and O-Ring Guide. Fitting shall be able to fully rotate under pressure and allow easy disconnect and reuse without the use of disconnection tools. Fitting must not disassemble to disconnect.

Approvals

 Listed by the National Sanitation Foundation to NSF Standard 61 for use in potable water systems



Ratings

150psi @ 70°F (10 bar @ 20°C) 60psi @ 140°F (4 bar @ 60°C) Min. 33°F (1°C)

Example

1024RB-04

10 = Series 10 24 = Reducing Tee R = Reducing B = Bag 060604 = 3%" OD x 3%" OD x 1/4" OD

Caution: The polypropylene material used in the Quick-Connect fittings can be compromised by exposure to volatile organic compounds (VOC's) and caustic chemicals. Therefore, DO NOT expose this product to any such chemical or foreign substance, which would include exposure to the following products: Pipe Dopes (thread sealants), bug sprays, lubricants, cleaners, paints, bleaches, acids, solder fluxes, plastic piping primers and cements, oxidizing agents, alkaline solutions, thinners, fuels, oil based caulks, hydrocarbons, spray foam of foaming agents (insulation).

*The wetted surface of this product contacted by consumable water contains less than one quarter of one percent (0.25%) of lead by weight.



1023B




1024RB



Dimensions - Weights approx. (tolerance +/- 1/8")

Type 23 Union Tee

MODEL	SIZE & CONNECTION	ITEM L	.ENGTH	ITEM H	IEIGHT	ITEM WEIGHT		
		Α		В				
		in.	mm	in.	mm	lbs.	kg.	
1023B-04	1/4" OD	11//8	47	11/4	32	0.30	8.50	
1023B-06	%" OD	21/4	57	1%16	39	0.50	14.17	
1023B-08	½" OD	25/8	66	1 ¹³ ⁄ ₁₆	45	0.80	22.68	



Type 24R Reducing Tee

MODEL	SIZE & CONNECTION		ITEM LENGTH		ITEM HEIGHT		ITEM WEIGHT		
	1 2 3		А		В				
		(2)	(3)	in.	mm	in.	mm	lbs.	kg.
1024RB-060604	%" OD x 3/	%" OD x	1/4" OD	21/4	57	11/2	38	0.50	14.17
1024RB-080806	½" OD x ½	ź" OD x	%" OD	25/8	66	1 13/16	45	0.80	22.68

