Job Name	Contractor
Job Location	Approval
Engineer	Contractor's P.O. No.
Approval	Representative

Series 440 Fotoguard

Specifications

ALL SERIES 440 WATER MIXING VALVES CONSIST OF:

- a) Thermostatic mixing valve
- b) Separate volume control and shutoff valves
- c) Volume control
- d) Inlet strainer checkstops
- e) ½" (15mm) NPT inlets and outlets


440-1500 — Capacity 1 to 6 gpm @ 45psi (0.06 to 0.38 l/s @ 310 kPa) differential.

440-1510 (High Capacity) — Capacity 1 to 14 (US) gpm @ 45psi (0.32 to 0.88 l/s @ 310 kPa) differential.

131-1575 (Supply Fixture) — Includes on/off valve, thermometer, vacuum breaker, and chrome plated brass piping. Capacity 1 to 6 (US) gpm @ 45psi (0.06 to 0.38 l/s @ 310 kPa) differential.

131-1813 (High Capacity Supply Fixture) — Includes on/off valve, thermometer, vacuum breaker, and chrome plated brass piping. Capacity 5 to 14 (US) gpm @ 45psi (0.32 to 0.88 l/s @ 310 kPa) differential.

440-1550 (for Concealed Piping) — Capacity 1 to 6 (US) gpm @ 45psi (0.06 to 0.38 l/s @ 310 kPa) differential.



440-1500 440-1510

131-1575 131-1813




440-1550

NOTICE


The information contained herein is not intended to replace the full product installation and safety information available or the experience of a trained product installer. You are required to thoroughly read all installation instructions and product safety information before beginning the installation of this product.




Roughing-In Dimensions




PRODUCT NO.	Α	В	C	D	E
131-1575	2 ¹⁵ / ₁₆ "	5%"	5½"	1"	1%"
	75	149	140	25	48
131-1813	2 ¹⁵ / ₁₆ "	5¾"	7"	1¾"	1 ¹⁵ / ₁₆ "
	75	146	178	44	44



PRODUCT NUMBER 440-1500



PRODUCT NUMBER 440-1550





A WATTS Brand

USA: T: (800) 669-5430 • F: (847) 229-0526 • PowersControls.com Canada: T: (905) 332-4090 • F: (905) 332-7068 • PowersControls.ca Latin America: T: (52) 81-1001-8600 • PowersControls.com