AquaLock[™]

Push-to-Connect Plumbing Fittings





LEAD FREE*

Before using standard material product for potable water systems consult your local water authority and building & plumbing codes. Interpretation of the new federal Lead Free law, effective January 4, 2014, may vary according to local governing authorities.

 $^{\star}\text{The}$ wetted surface of this product contacted by consumable water contains less than 0.25% of lead by weight.

Electronic is Green!

For the latest Watts pricing information in electronic format, visit our Data Exchange at:

https://www.watts.com/resources/electronic-data-services

- Download product and list price data in .csv, .pdf, .tsv, .xls and .xml formats
- Easy access to list price data for business systems
- Sign up for e-mail alerts when data is updated
- Access other Watts Water Technologies brands pricing data



Elbow Pump Connector......16

Table of Contents

Terms & Conditions	2	Connectors		Connectors	
Technical Information	3-5	Couplings	17	Couplings	27
Features		Reducing Couplings	17	Reducing Couplings	27
		Male Adapters		Male Adapters	
Model Number Meaning	8	Female Swivel Adapters		Female Adapters	
Brass Series		Hose Barb Adapters		Stems	
Tees		Pump Adapters			
	0	Stems		Male Stems	
Tee w/Gauge				Reducing Stems	28
Reducing Tees		Male Stems		Stops	
Double Reducing Tees		Female Stems		End Caps	28
Repair Tees	9	Reducing Stems			
Elbows		Hose Barb Stems	19	Valves	
Elbows	10	Ends		Straight Valves	
Reducing Elbows	10	End Caps	19	Male Straight Valves	
Stackable Elbows		•		Female Angle Valves	29
Male Elbows		Valves			
Female Elbows		Straight Valves	20	Matria Carias	
Drop Ear Elbows		Female Straight Valves	20	Metric Series	
·		Stackable Valves	20	Tees	
Connectors		Tee Valves	20	Reducing Tees	30
Couplings		Check Valves	20	Stackable Tees	
Reducing Couplings	11	3-Way Selector Valves	21		
Male Adapters	11	3-Way Bypass Valves		Elbows	
Female Adapters	11	Angle Valves	21	Elbows	31
Slip Repair Couplings	11	Female Angle Valves		Stackable Elbows	31
Stems		Female Angle Valves GHT	21	Male Elbows	
Male Stems	12	Panel Mount Valve	21	Female Swivel Elbows	
Female Stems		Shutoff Valves	21	Drop Ear Elbows	31
	12	Garden Hose Angle Valve	21	Elbow Pump Adapters	31
Ends		Miscellaneous		Connectors	
End Caps	12		22	Couplings	32
Transition Fittings		Collet Clips		Reducing Couplings	
Male Adapters	10	Cone Seal		Male Adapters	
Female Adapters		PEX Tube Stiffeners		Female Swivel Adapters	
Coupling			22	Hose Barb Adapters	
End Caps		Manifolds - Single		Pump Adapters	
	12	Manifolds - Single Body	23	Compression Adapters (Brass)	
Kits		Manifolds - Single Stem Body - Right			
Shower Installation Kits	13	Manifold - Single Stem Body - Left	23	Stems	
Valves		Manifold Single Side Mounting Kits	23	Male Stems (Brass)	
Ball Valves	12	Manifolds - Dual		Reducing Stem	33
Tee Valves			00	Ends	
Washing Machine Valves		Manifolds - Dual Body Manifolds - Dual Stem Body		End Caps	33
Garden Hose Valves		Manifold Dual Side Mounting Kits		End Plugs	
daluell nose valves	13	Manifold Dual Side Mounting Kits	23		
		Manifold Accessories		Valves	
Plastic Series		Manifold Divider Plugs	24	Straight Valves	
Tees		Manifold Return Ends	24	Stackable Valves	
Reducing Tees	1.1	Manifold Red Label Plates	24	Tee Valves	34
Double Reducing Tees		Manifold Blue Label Plates	24	Check Valves	
Male Threaded Tees		Manifold Valve Repair Kits	24	Male Stem Check Valves (Brass)	
Stackable Tees		MT Manifold Tool	24	Stem Check Valves (Brass)	34
Reducing Stackable Tees		End Plugs	24	Miscellaneous	
Stackable Branch Tees				Collet Clip	25
	13			Collet Cover	
Elbows		Mini Series		Elbow Clip	
Elbows	15	Tees		•	
Reducing Elbows	15	Tees	25	Metric Manifolds - Single	35
Stackable Elbows	15	Reducing Tees		Metric Manifolds - Dual	36
Male Elbows	16	•	20	Metric Manifold Accessories	36
Female Swivel Elbows	16	Elbows			-
Drop Ear Elbows	16	Elbows			
Hose Barb Elbows	16	Reducing Elbows	26		



Terms and Conditions

FREIGHT TERMS: All shipments are F.O.B. shipping point. Shipments from factory less than 1000 lbs. are F.O.B. factory. Factory shipments of 2500 and over

within the continental U.S.A. will be prepaid and allowed when made at the lowest motor carrier transportation rate.

TERMS OF SALE: All sales are F.O.B. shipping point.

PAYMENT TERMS: The invoices are due and payable 30 days from the date of invoice.

PURCHASEOrders submitted on customer's own purchase order forms will be accepted only with the express understanding that no statements, clauses, or conditions contained in said order form will be binding on the Seller if they in any way modify the Seller's own terms and conditions of sales.

SPECIAL PRODUCTS: Orders for special or modified products are non-cancelable. In the event that the customer cancels an order for such products, Watts shall

charge the customer an amount equal to Watts' costs and expenses incurred in performing the purchase order prior to receipt of notice of

cancellation.

LIMITED WARRANTY: A. Watts Regulator Co. ("Watts") warrants its WaterPEX® cross-linked polyethylene tubing, barbed PEX fittings, brass and plastic AquaLockTM fittings and manifolds, factory manufactured copper manifolds and AquaLockTM accessories to be free of defects in material and workmanship when used under normal usage in potable water systems, and installed in accordance with all Watts printed installation instructions. Specific warranty durations apply as follows:



1. Watts WaterPEX® cross-linked polyethylene (non-barrier PEX) pipe, brass and plastic barbed PEX fittings, and factory manufactured copper manifolds when installed as a system using Watts WaterPEX pipe, Watts brass or plastic barbed PEX fittings, and Watts factory manufactured copper manifolds for a period of twenty-five (25) years from the date of original shipment.

- 2. Watts WaterPEX® cross-linked polyethylene (non-barrier PEX) pipe, when installed with brass or plastic barbed PEX fittings manufactured by others that meet the applicable ASTM Standards (brass ASTM F 1807) (plastic ASTM F 2159) for a period of ten (10) years from the date of original shipment.
- 3. Watts WaterPEX® brass or plastic barbed PEX fittings and factory manufactured copper manifolds when installed with cross-linked polyethylene (non-barrier PEX) pipe manufactured by others that meet the ASTM F 876 requirements for a period of ten (10) years from the date of original shipment.
- 4. Brass, Plastic and Mini AquaLock™ fittings and manifolds for a period of twenty-five (25) years from the date of original shipment.
- 5. All other valves and accessories sold under the Watts WaterPEX or Watts AquaLock™ brand name for a period of two (2) years from the date of original shipment.

Watts's obligation will be to repair or replace, at its discretion, any of these products proven to be defective in material or workmanship when these products are covered under this limited warranty.

- B. In the event of a system malfunction or leak caused by defective Watts warranted materials (and not by incorrect installation, incorrect handling procedures or by jobsite or installation damage), a reasonable pre-approved amount will be allowed for repair materials and repair labor. In the event of a leak occurring in a factory manifold, you may contact Watts for either a free replacement manifold or any parts reasonably needed to repair such a leak (freight prepaid). Note that Watts limits its warranty to its tubing, valves and accessories, fittings and manifolds. Watts does not warrant the connection on any installation, as the integrity of the connection is subject to the workmanship of the contractor/installer. The connection is the sole responsibility of the person who installs it.
- C. In order to qualify for a warranty remedy under paragraph B, you must contact Watts in advance and receive a written authorization for this remedy from an authorized Watts representative. Repair materials, repair labor and freight expenses not authorized in writing in advance by Watts in this way will not be compensated.
- D. To qualify for the warranty described above, you must do the following:
- 1. Use good construction techniques to install our materials, as specified in our current design and installation guidelines and technical notes. This must include field pressure testing our warranted materials before they are covered by concrete or otherwise made inaccessible.
- 2. Install Watts WaterPEX® and Watts AquaLock™ materials according to all guidelines and manuals published by Watts.
- Install Watts WaterPEX® and Watts AquaLock™ products in a system that will not operate at temperatures or at pressures that exceed the rating printed on the tubing.
- 4. The Watts warranted product must be installed in compliance with local building and plumbing codes.
 - E. Evidence of tampering, mishandling, neglect, accidental damage, freeze damage or unauthorized repairs that cause damage to Watts's warranted products will void any warranty coverage for those particular products. All field connections are specifically excluded from the terms of this warranty.
 - F. Watts provides a complete plumbing system offering so that it is possible to complete an installation with Watts products. However, it is possible that other manufacturers' tubing and/or fittings may be installed in any given installation. Providing that the tubing and/or fittings are manufactured to their applicable ASTM standards, and have been certified by a recognized third-party testing agency, the Watts product in the given installation will continue to be covered under this warranty. In the event of a system malfunction or leak that has other tubing and/or fitting manufacturers' components installed within the failed system, Watts will be responsible only for proven defects in material or workmanship in the Watts products. Products manufactured by another company should be reported to that manufacturer for its warranty response.
 - G. Disclaimer of Warranty. THE WARRANTY SET FORTH HEREIN IS GIVEN EXPRESSLY AND IS THE ONLY WARRANTY GIVEN BY WATTS WITH RESPECT TO THE PRODUCTS LISTED IN PARAGRAPH A. WATTS MAKES NO OTHER WARRANTIES, EXPRESS OR IMPLIED. WATTS HEREBY SPECIFICALLY DISCLAIMS ALL OTHER WARRANTIES, EXPRESS OR IMPLIED, INCLUDING BUT NOT LIMITED TO THE IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE.
 - H. Limitation of Liability. The remedy described above shall constitute the sole and exclusive remedy for breach of warranty, and, apart from that remedy, Watts shall not be responsible for any incidental, special or consequential damages, including without limitation, lost profits or the cost of repairing or replacing other property which is damaged if these warranted products do not work properly, other costs resulting from labor charges, delays, vandalism, negligence, fouling caused by foreign material, damage from adverse water conditions, adverse chemical environments, or any other circumstances over which Watts has no control. This warranty shall be invalidated by any abuse, misuse, misapplication or improper installation of the product. Some states do not allow limitations on how long an implied warranty lasts, and some states do not allow the exclusion or limitation of incidental or consequential damages. Therefore the above limitations may not apply to you. This Limited Warranty gives you specific legal rights, and you may have other rights that vary from state to state. You should consult applicable state laws to determine your rights. SO FAR AS IS CONSISTENT WITH APPLICABLE STATE LAW, ANY IMPLIED WARRANTIES THAT MAY NOT BE DISCLAIMED, INCLUDING THE IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE, ARE LIMITED IN DURATION TO ONE YEAR FROM THE DATE OF ORIGINAL SHIPMENT.
 - 1. RETURNED GOODS: No material shall be returned without authorization. When credit is issued it will be at the price charged, or prevailing price if lower, less handling charges based on costs of reconditioning, boxing, etc. However, a minimum 25% handling charge will apply. A minimum handling charge of 20.00 is applied whenever the 25% handling deduction does not total 20.00. Products which are obsolete or made to special order are not returnable.

NOTE: Prices and terms are subject to change without notice and supersede all previous quotations. The right is reserved to change or modify product design or construction without prior notice and without incurring and obligation to make such changes and modifications on products previously or subsequently sold.



Technical Information - Brass Fittings

Material Specifications

Body: Lead Free* Brass Alloy

O-Ring: EPDM
Gripper Ring: Stainless Steel
Push Ring: Delrin
Tube Liner: Polysulfone
Push Ring Clip: Delrin

Fitting Performance

 $\label{eq:continuous_problem} \mbox{AquaLock}^{\mbox{\tiny TM}} \qquad \mbox{Max. Pres.} \qquad \mbox{200psi @ 200°F} \qquad \mbox{(13.8 bar @ 93°C)}$

Brass Min. Temp. 33°F (0.5°C)

Approvals



ASTM F877: Watts Brass AquaLock™ fittings are tested, certified and approved to ASTM F877 performance standards.



IAPMO ASSE 1061: Watts Brass AquaLock[™] fittings are tested, certified and approved to ASSE 1061, and approved to Canadian Standard CSA B137.5 and NSF/ANSI 61.

Lead free product is certified to NSF/ANSI 372 and conforms with the lead content requirements for lead free plumbing as defined by California, Vermont, Maryland, and Louisiana state laws and the U.S. Safe Drinking Water Act.

*The wetted surface of this product contacted by consumable water contains less than 0.25% of lead by weight.

Watts AquaLock™ Brass fittings are designed and manufactured to be trouble free for many years of service. All Brass fittings are tested, approved and certified to NSF/ANSI 61, CSA B137.5, ASTM F877 and ASSE 1061. Brass fittings are available in standard imperial inch sizes. The unique design of Brass fittings allows for quick and easy connections without installation tools.

Watts AquaLockTM Brass fittings are designed for potable water systems. For other applications please refer to our Technical Service Department. Tubing should be supported at minimum of 36" to prevent excessive load to the connectors. Do not install tubing supports closer than 3 inches from the connector ends. We strongly recommend that new installations be thoroughly tested prior to use. Do not use with explosive gases, petroleum products, or other fuels.

A CAUTION

The polysulfone material used in the AquaLockTM fittings can be compromised by exposure to volatile organic compounds (VOC's) and caustic chemicals. Therefore, **DO NOT** expose this product to any such chemical or foreign substance, which would include exposure to the following products: **Pipe Dopes (thread sealants)**, bug sprays, lubricants, cleaners, paints, bleaches, acids, solder fluxes, plastic piping primers and cements, oxidizing agents, alkaline solutions, thinners, fuels, oil based caulks, hydrocarbons, spray foam of foaming agents (insulation).

Watts recommends that all fittings and parts be stored in their original packaging until installation to protect the fitting internals from dirt and debris that may cause damage to the o-ring and the o-ring guide.

It is also recommended that all threaded connections be made with Teflon® tape only.

Failure to follow these instructions will void the warranty and possibly result in leaks and water damage.

All Brass Fittings come complete with a removable push ring clip to prevent accidental release of the fitting prior to pressurization.





Technical Information - Plastic Fittings

Material Specifications

Body: Polysulfone
Collet: Nylon
O-Ring: EPDM
Spacer: Acetal
Tube Liner: Polysulfone
Collet Clip: Delrin

Fitting Performance

 AquaLock™
 Max. Pres.
 250psi @ 75°F
 (17.25 bar @ 24°C)

 Plastic
 Max. Temp.
 100psi @ 180°F
 (6.8 bar @ 82°C)

 Min. Temp.
 33°F (0.5°C)

Thread Torque Values

Size	Min. Torque Values	Max. Torque Values
1/2"	17.7 in - lbs.	26.5 in - lbs.
3/4"	22.7 in - lbs.	31 in - lbs.

Approvals



FDA: Watts Plastic fittings are produced from FDA approved materials.



NSF/ANSI 61-G: Watts Plastic fitting products are tested, certified, and approved for contact with drinking water.



NSF/ANSI 14: Watts Plastic fitting products are tested, certified, and approved to NSF-14 standards.



ASTM F877: Watts Plastic fitting products are tested, certified, and approved to ASTM F877 performance standards.



NSF-U.P. Code: Watts Plastic fitting products are tested, certified, and approved and meet the requirements of the Uniform Plumbing Code.



IAPMO ASSE 1061: Watts Plastic fitting fittings are tested, certified and approved to ASSE 1061 for AquaLock[™] fittings and approved to Canadian Standard CSA B137.5.

Lead free product is certified to NSF/ANSI 372 and conforms with the lead content requirements for lead free plumbing as defined by California, Vermont, Maryland, and Louisiana state laws and the U.S. Safe Drinking Water Act.

*The wetted surface of this product contacted by consumable water contains less than 0.25% of lead by weight.

Watts AquaLock™ Plastic fittings are designed and manufactured to be trouble free for many years of service life. Plastic fitting products are designed and manufactured in polysulfone, a high performance thermal plastic material. All Plastic fitting products are approved and certified to NSF-61-G, NSF 14, CSA B137.5, ASTM F877, and to the Uniform Plumbing Code (U.P. Code) and ASSE 1061. Plastic fitting products are available in standard imperial inch sizes. The Watts AquaLock™ design allows for quick and easy connections without installation tools. Simply cut the plastic, copper or CPVC tubing and snap a Watts AquaLock™ fitting in place for a zero-leak connection.

Watts AquaLockTM Plastic fittings are designed for potable water systems. For other applications please refer to our Technical Service Department. Tubing should be supported at minimum of 36" to prevent excessive load to the connectors. Do not install tubing supports closer than 3 inches from the connector ends. We strongly recommend that new installations be thoroughly tested prior to use. Do not use with explosive gases, petroleum products, or other fuels.

A CAUTION

The polysulfone material used in the AquaLock™ fittings can be compromised by exposure to volatile organic compounds (VOC's) and caustic chemicals. Therefore, **DO NOT** expose this product to any such chemical or foreign substance, which would include exposure to the following products: **Pipe Dopes (thread sealants)**, bug sprays, lubricants, cleaners, paints, bleaches, acids, solder fluxes, plastic piping primers and cements, oxidizing agents, alkaline solutions, thinners, fuels, oil based caulks, hydrocarbons, spray foam of foaming agents (insulation).

Watts recommends that all fittings and parts be stored in their original packaging until installation to protect the fitting internals from dirt and debris that may cause damage to the o-ring and the o-ring guide.

It is also recommended that all threaded connections be made with Teflon® tape only.

Failure to follow these instructions will void the warranty and possibly result in leaks and water damage.





Technical Information - Mini Fittings

Material Specifications

Body: Polypropylene
Collet: Acetal
O-Ring: EPDM
Spacer: Acetal

Fitting Performance

 AquaLock™
 Max. Pres.
 150psi @ 70°F
 (10.3 bar @ 20°C)

 Mini
 Max. Temp.
 60psi @ 140°F
 (4.1 bar @ 60°C)

 Min. Temp.
 33°F (0.5°C)

Thread Torque Values

Size	Max. Torque Values	
1/8", 1/4" (3.8mm)	13.3 in - lbs. (1.5 Nm)	
3/8", 1/2" (10, 15mm)	26.6 in - lbs. (3.0 Nm)	

Approvals



FDA: Watts AquaLock[™] Mini fittings are produced from FDA approved materials.



NSF/ANSI 61-G: Watts AquaLockTM Mini fitting products are tested, certified, and approved for contact with drinking water.

Lead free product is certified to NSF/ANSI 372 and conforms with the lead content requirements for lead free plumbing as defined by California, Vermont, Maryland, and Louisiana state laws and the U.S. Safe Drinking Water Act.

*The wetted surface of this product contacted by consumable water contains less than 0.25% of lead by weight.

Watts AquaLock™ Mini fittings are designed and manufactured to be trouble free for many years of service life. Mini fitting products are designed and manufactured in polypropylene, a rugged thermoplastic polymer. All Mini fitting products are approved and certified to NSF-61-G. Mini fitting products are available in standard imperial inch sizes. The Watts AquaLock™ design allows for quick and easy connections without installation tools. Simply cut the plastic or copper piping and snap a Watts AquaLock™ fitting in place for a zero leak connection.

Watts AquaLock™ Mini fittings are designed for low pressure fluids. For other applications please refer to our Technical Service Department. Tubing should be supported at minimum of 36" to prevent excessive load to the connectors. Do not install tubing supports closer than 3 inches from the connector ends. We strongly recommend that new installations be thoroughly tested prior to use. Do not use with explosive gases, petroleum products, or other fuels.

A CAUTION

The polypropylene material used in the AquaLockTM fittings can be compromised by exposure to volatile organic compounds (VOC's) and caustic chemicals. Therefore, **DO NOT** expose this product to any such chemical or foreign substance, which would include exposure to the following products: **Pipe Dopes (thread sealants)**, bug sprays, lubricants, cleaners, paints, bleaches, acids, solder fluxes, plastic piping primers and cements, oxidizing agents, alkaline solutions, thinners, fuels, oil based caulks, hydrocarbons, spray foam of foaming agents (insulation).

Watts recommends that all fittings and parts be stored in their original packaging until installation to protect the fitting internals from dirt and debris that may cause damage to the o-ring and the o-ring guide.

It is also recommended that all threaded connections be made with Teflon® tape only.

Failure to follow these instructions will void the warranty and possibly result in leaks and water damage.





Features


Making a Fast and Secure Connection with Mini and Plastic Fittings



Cut the pipe or tubing squarely using a sharp tubing cutter (plastic) or rotary copper pipe cutter (copper). Inspect the outside diameter of the pipe or tubing to be sure there is no damage, nicks, burrs, or debris. Deburr and clean pipe or tubing as necessary.



Measure the insertion depth on the pipe or tubing end. The fittings have an insertion line molded into the body of the fitting.






To disconnect, ensure system has been depressurized before removing fitting. Push the collet in squarely against the face of the fitting. With the collet held securely in this position, the tubing can be removed.

Zero-Leak O-Ring Guide

All Watts AquaLockTM Plastic fittings incorporate an exclusive patented O-ring Guide for improved reliability. This unique feature provides a zero-leak connections by:

- Protecting the 0-ring from damage during connection
- . Increasing the connectors' side load capacity
- Correctly aligning the tubing with the O-ring every time.
- Preventing the 0-ring from becoming dislodged.





Watts AquaLock™ fittings utilize a swivel nut with NPS straight threads and a cone seal. This allows the installer to thread onto NPT, NPS, BSP, and most threads without tools or thread sealant. Simply thread on, hand tight, for a zero leak seal.

Connect to Multiple Materials

The Watts AquaLockTM fittings incorporates Stainless Steel Gripping Teeth in its Collet. These corrosion resistant teeth allow AquaLockTM fittings to interconnect with multiple materials without tools.



Rotates under pressure

After a joint is made the tubing can still swivel while connected, even under maximum pressure. The ability to rotate under pressure makes these connectors ideal for vibrating and dynamic applications.



Highest Flow

Watts AquaLock[™] fittings join the tubing on the outside. Because there is no barb fitting on the inside of the tubing the flow capacity is increased by more than 30%. Only AquaLock[™] fittings offer complete flow, allowing for a more efficient system.



Create mini-manifolds

With AquaLock™ fittings small lengths of tubing can be eliminated by using our stackable connector configurations. Simply snap together Tees and/or Elbows to create a mini-manifold of fittings. Because AquaLock™ fittings rotate the direction of the tubing can be oriented

by a simple twist, reducing the amount of tubing required to plumb a water system.

^{**}To comply with ASSE 1061, a tube liner (provided) must be used on all PEX pipe connections Plastic AquaLock™.

Features



Making a Fast and Secure Connection with Brass Fittings




Cut the pipe or tubing squarely using a sharp tubing cutter (plastic) or rotary copper pipe cutter (copper). Inspect the outside diameter of the pipe or tubing to be sure there is no damage, nicks, burrs, or debris. Deburr and clean pipe or tubing as necessary.


2


Measure the insertion depth on the pipe or tubing end. For Brass fittings, use the Insertion Depth Guide provided.

Insertio	!	
Size	Insertion	Depth
3/8" CTS 1/2" CTS 3/4" CTS 1" CTS	1" 1" 1 ¹ / ₈ " 1 ¹ / ₄ "	25mm 25mm 29mm 32mm

fitting until it comes into contact with the internal tube








Slip Repair Fittings (For copper and CPVC only)

- Remove 2" section of pipe. Ensure pipe is cut squarely and is free of damage, nicks, burrs, or debris.
- 2. Measure the insertion depth of the pipe using the depth gauge mark on one end of the fitting.
- 3. Push pipe and Slip End of fitting together.

-

4. Press the push ring of Slip End and slide the fitting onto the end of the pipe with insertion depth until it reaches the internal tube stop.



Connect to Multiple Materials

The Watts AquaLock™ fittings incorporates a Stainless Steel Gripper Ring. These corrosion resistant teeth allow AquaLock™ fittings to interconnect with multiple materials without tools.

- LDPE, MDPE, & HDPE PEX Tubings
- Copper
- CPVC
- Non-Oxygen Barrier PEX
- Potable Manowall PEX

Rotates under pressure

After a joint is made the tubing can still swivel while connected, even under maximum pressure. The ability to rotate under pressure makes these connectors ideal for vibrating and dynamic applications.



Highest Flow

Watts AquaLockTM fittings join the tubing on the outside. Because there is no barb fitting on the inside of the tubing the flow capacity is increased by more than 30%. *Only AquaLockTM fittings offer complete flow, allowing for a more efficient system.


*For Non-PEX pipe, AquaLock fittings do not require a pipe insert. This allows AquaLock fitting to ensure that flow is unrestricted unlike other connections that have the tube liner built into the fitting.



^{**}To comply with ASSE 1061, a tube liner (provided) must be used on all PEX pipe connections (Brass AquaLock™ Series).



Model Number Meaning





Model	Ordering Code	Size & Connection	UPC	Unit Pack	(Inner Ctn.) Minimum	Master Carton	Unit Weight
				Qty.	Order Qty.	Qty.	(lbs.)

Brass Tees

Tees



Package Type: Single Pack

₩ LF4723-10	0472035	1/2" x 1/2" x 1/2" CTS	098268022315	1	12	120	0.23
LF4723-14	0472036	3/4" x 3/4" x 3/4" CTS	098268022322	1	12	120	0.4
₫ LF4723-18	0472037	1" x 1" x 1" CTS	098268022339	1	6	60	0.66

Tee w/Gauge

Package Type: Single Pack

LEAD FREE* LF4723G-14	0472070	3/4" x 3/4" CTS	098268145922	1	5	50	0.7



Reducing Tees

Package Type: Single Pack

₽# LF4724R-141410	0472038	3/4" x 3/4" x 1/2" CTS	098268022346	1	12	120	0.34
≝ E LF4724R-141014	0472040	3/4" x 1/2" x 3/4" CTS	098268022360	1	12	120	0.36



Double Reducing Tees

Package Type: Single Pack

LF4726R-141010	0472042	3/4" x 1/2" x 1/2" CTS	098268022391	1	6	60	0.35
----------------	---------	------------------------	--------------	---	---	----	------

LF4726R

LF4724R

Repair Tees

Package Type: Single Pack



W W W	LF4732-10	0472050	1/2" CTS	098268022568	1	6	60	0.32
I O	LF4732-14	0472051	3/4" CTS	098268022582	1	6	60	0.4
9	LF4732-18	0472052	1" CTS	098268022612	1	6	60	0.44

LF4732

Water Heater Expansion Tank Tee

I F4723-141214	0472105	3/4" CTS x 3/4" NPT x 3/4" CTS	098268549256	1	6	60	0.4	



	Model	Ordering Code	Size & Connection	UPC	Unit Pack Qty.	(Inner Ctn.) Minimum Order Qty.	Master Carton Qty.	Unit Weight (lbs.)
--	-------	------------------	-------------------	-----	----------------------	---------------------------------------	--------------------------	--------------------------

Brass Elbows

Elbows

Package Type: Single Pack



LF4717

ų	LF4717-08	0472061	3/8" CTS	098268040876	1	6	60	0.12
Ě	LF4717-10	0472016	1/2" CTS	098268022056	1	12	120	0.17
9	LF4717-14	0472017	3/4" CTS	098268022070	1	12	120	0.3
1	LF4717-18	0472018	1" CTS	098268022087	1	6	60	0.48
	Package Type:	Bulk Pack						
* W	LF4717-10CP	0472066	1/2" CTS	098268145816	5	5	5	1.35
H	LF4717-14CP	0472067	3/4" CTS	098268145861	5	5	5	2.35

Reducing Elbows

Package Type: Single Pack

₽# LF4717R-1410	0472019	3/4" x 1/2" CTS	098268022094	1	12	120	0.21
≝E LF4717R-1814	0472020	1" x 3/4" CTS	098268022100	1	6	60	0.4

LF4717R

Stackable Elbows

Package Type: Single Pack



ä	LF4718-10	0472021	1/2" CTS	098268022117	1	6	60	0.17
Ē	LF4718-14	0472022	3/4" CTS	098268022124	1	6	60	0.3
H	LF4718-18	0472023	1" CTS	098268022131	1	6	60	0.48

098268022155

098268022162

60

60

6

0.2

0.3

Male Elbows





	Package Type:	Single Pack
	LF4719-1008 LF4719-1412	0472025
꽲	LF4719-1412	0472026

LF4719

Female Elbows





Q iu	LF4720-1008	0472028	1/2" CTS x 1/2" NPT	098268022193	1	6	60	0.2
4 E	LF4720-1412	0472029	3/4" CTS x 3/4" NPT	098268022209	1	6	60	0.3

1/2" CTS x 1/2" NPT

3/4" CTS x 3/4" NPT



Drop Ear Elbows

LF4721-1008	0472034	1/2" CTS x 1/2" FPT	098268022308	1	6	60	0.23
≝E LF4721-10	0472104	1/2" CTS x 1/2" CTS	098268549249	1	3	30	0.25



0.12

0.14

0.23

0.33

0.6

0.95

6

12

12

6

5

1

1

5

120

120

60

5

5

ı	Model	Ordering Code	Size & Connection	UPC	Unit Pack	(Inner Ctn.) Minimum	Master Carton	Unit Weight
					Qty.	Order Qty.	Qty.	(lbs.)

098268040845

098268021806

098268021837

098268021851

098268145762

098268145786

Brass Connectors

Couplings

LF4715-08

LF4715-10

LF4715-14

LF4715-18

LF4715-10CP

LF4715-14CP

Package Type: Single Pack

Package Type: Bulk Pack

0472060

0472000

0472001

0472002

0472064

0472065











Package Type: Single Pack

우谯 LF4715R-1410	0472003	3/4" CTS x 1/2" CTS	098268021868	1	12	120	0.2
발표 LF4715R-1814	0472004	1" CTS x 3/4" CTS	098268021875	1	6	60	0.3

3/8" CTS

1/2" CTS

3/4" CTS

1" CTS

1/2" CTS

3/4" CTS



Male Adapters

Package Type: Single Pack

	3 71	3						
	LF4701-0806	0472058	3/8" CTS x 3/8" NPT	098268040814	1	6	60	0.12
	LF4701-1008	0472011	1/2" CTS x 1/2" NPT	098268021981	1	12	120	0.13
ı	LF4701-1012	0472012	1/2" CTS x 3/4" NPT	098268022001	1	6	60	0.18
ı	EF4701-1412	0472013	3/4" CTS x 3/4" NPT	098268022018	1	12	120	0.2
	LF4701-1816	0472015	1" CTS x 1" NPT	098268022032	1	6	60	0.28

Package Type: Bulk Pack

at 154701 10000D	0472005	1 (OII OTC 1 (OII NDT	00000010000	-			0.10
LF4/01-1008CP	04/2085	1/2" CTS x 1/2" NPT	098268186680	5	5	5	0.13
☐E LF4701-1412CP	0472089	3/4" CTS x 3/4" NPT	098268186734	5	5	5	0.2

Female Adapters

Package Type: Single Pack



	LF4710-0806	0472059	3/8" CTS x 3/8" FNPT	098268040821	1	6	60	0.11
	LF4710-1008	0472005	1/2" CTS x 1/2" FNPT	098268021905	1	12	120	0.14
*.	LF4710-1012	0472006	1/2" CTS x 3/4" FNPT	098268021912	1	6	60	0.2
ij	LF4710-1408	0472062	3/4" CTS x 1/2" FNPT	098268043297	1	6	60	0.2
Ш	LF4710-1412	0472007	3/4" CTS x 3/4" FNPT	098268021929	1	6	60	0.21
EA	LF4710-1416	0472008	3/4" CTS x 1" FNPT	098268021936	1	6	60	0.22
	LF4710-1816	0472010	1" CTS x 1" FNPT	098268021974	1	6	60	0.3
	LF4710-0417	0472071	1/4" OD x 3/8" CMP	098268146813	1	5	50	0.45
	LF4710-0617	0472072	3/8" OD x 3/8" CMP	098268146820	1	5	50	0.5

Package Type: Bulk Pack

₽ LF4710-1008CP	0472086	1/2" CTS x 1/2" NPT	098268186703	5	5	5	0.14
≝	0472090	3/4" CTS x 3/4" NPT	098268186741	5	5	5	0.21



Slip Repair Couplings

	_rackage typ	e. Single Fack						
ا م	LF4716-10	0472047	1/2" CTS	098268022506	1	12	120	0.25
M	LF4716-14	0472048	3/4" CTS	098268022520	1	6	60	0.39
ш	LF4716-18	0472049	1" CTS	098268022537	1	6	60	0.55



Ī	Model	Ordering Code	Size & Connection	UPC	Unit Pack Qty.	(Inner Ctn.) Minimum Order Qtv.	Master Carton	Unit Weight (lbs.)
					uty.	Oluel Qty.	Qty.	(ID2.)

Brass Stems

Male Stems

Package Type: Single Pack

		Ġ
	LF4727	

LF4727-1003	0472068	1/2" CTS x 1/2" NPT	098268145908	1	5	50	0.19
LF4727-1412	0472056	3/4" CTS x 3/4" NPT	098268022698	1	5	50	0.4



Female Stems

Package Type: Single Pack

	LF4728-1008	0472069	1/2" CTS x 1/2" NPT	098268145915	1	5	50	0.13
뿔뚠	LF4728-1412	0472057	3/4" CTS x 3/4" NPT	098268022780	1	5	50	0.31

LF4728

Brass Ends

End Caps

Package Type: Single Pack



O iiu	LF4745-10	0472044	1/2" CTS	098268340679	1	12	120	0.09
	LF4745-14	0472045	3/4" CTS	098268340686	1	6	60	0.14
-111	LF4745-18	0472046	1" CTS	098268340693	1	6	60	0.21

Package Type: Bulk Pack

₽# LF4745-10CP	0472087	1/2" CTS	098268186727	5	5	5	0.09
☐ LF4745-14CP	0472091	3/4" CTS	098268186789	5	5	5	0.14

Brass Transition Fittings for Schedule 40 PVC

Male Adaptors

ı ii.	LF4701-2008	0472095	1/2" SCH 40 PVC x 1/2" NPT	098268548785	1	12	120	0.1	
ij	LF4701-2212	0472096	3/4" SCH 40 PVC x 3/4" NPT	098268549027	1	6	60	0.18	_
н	LF4701-2216	0472097	3/4" SCH 40 PVC x 1" NPT	098268549102	1	6	60	0.2	

LF4701-2008



Female Adaptors

	i oiliaio / taaj	3.0.0						
O.*	LF4710-2008	0472098	1/2" SCH 40 PVC x 1/2" FNPT	098268549188	1	12	120	0.1
	LF4710-2212	0472099	3/4" SCH 40 PVC x 3/4" FNPT	098268549195	1	6	60	0.18
-114	LF4710-2216	0472100	3/4" SCH 40 PVC x 1" FNPT	098268549201	1	6	60	0.2

LF4710-2008



Coupling

E B	LF4715-1020	0472093	1/2" SCH 40 PVC x 1/2" CTS	098268548655	1	12	120	0.1
뿔뜺	LF4715-1424	0472094	3/4" SCH 40 PVC x 3/4" CTS	098268548754	1	6	60	0.18

LF4715-1020



End Caps
LE4745-20

n žu	LF4745-20	0472101	1/2" SCH 40 PVC	098268549218	1	12	120	0.1
	LF4745-22	0472102	3/4" SCH 40 PVC	098268549225	1	6	60	0.18
1	LF4745-24	0472103	1" SCH 40 PVC	098268549232	1	6	60	0.2

LF4745-20



Model	Ordering Code	Size & Connection	UPC	Unit Pack Qty.	(Inner Ctn.) Minimum Order Qtv.	Master Carton	Unit Weight (lbs.)
				Qty.	order diy.	Qty.	(105.)

Brass Kits

Shower Installation Kits



_								
	LF47SIK-F	0472106	Includes 2 Drop Ear Elbows,	098268549263	1	1	5	5.5
ų			2 1/2" Female Adaptors,					
Ĭ			2 1/2" Female Elbows					
ą	LF47SIK-M	0472107	Includes 2 Drop Ear Elbows,	098268549300	1	1	5	5.5
4			2 1/2" Male Adaptors,					
			2 1/2" Male Elbows					

LF47SIK-M

Brass Valves

Ball Valves



Package Type: Single Pack

n ii.	LF47FBVQC-10	0472053	1/2" CTS	098268022667	1	6	60	0.44
	LF47FBVQC-14	0472054	3/4" CTS	098268022674	1	6	60	0.63
- 16	LF47FBVQC-18	0472055	1" CTS	098268022681	1	6	60	1.17

Tee Valves

Package Type: Single Pack

Ĭш	LF4750-101004	0472075	1/2" x 1/2" CTS x 1/4" OD	098268147667	1	5	50	0.315
Ë	LF4750-101006	0472076	1/2" x 1/2" CTS x 3/8" OD	098268147674	1	5	50	0.315
P	LF4750-141404	0472077	3/4" x 3/4" CTS x 1/4" OD	098268147681	1	5	50	0.44
3	LF4750-141406	0472078	3/4" x 3/4" CTS x 3/8" OD	098268147698	1	5	50	0.44



Washing Machine Valves

Package Type: Single Pack

e iu	LF4751-1014S	0472079	1/2" CTS x 3/4" GHT	098268180183	1	5	50	0.315
H Æ	LF4751-1014A	0472080	1/2" CTS x 3/4" GHT	098268180190	1	5	50	0.315

LF4751

Garden Hose Valves



Package	Type:	Single	Pack

į,	LF4751-1014D	0472081	1/2" CTS x 3/4" GHT	098268180220	1	5	50	0.315
Ë	LF4751-1414D	0472082	3/4" CTS x 3/4" GHT	098268180237	1	5	50	0.315
PD	LF4751-1014HB	0472083	1/2" CTS x 3/4" GHT	098268180282	1	5	50	0.44
	LF4751-1414HB	0472084	3/4" CTS x 3/4" GHT	098268180305	1	5	50	0.44

LF475



Model	Ordering Code	Size & Connection	UPC	Unit Pack Qty.	(Inner Ctn.) Minimum Order Qtv.	Master Carton	Unit Weight (lbs.)
				uty.	Uluel Qty.	Qty.	(IDS.)

Plastic Fitting Tees

Tees

Package Type: Single Pack



Ĭ.	3523-08	0959038	3/8" x 3/8" x 3/8" CTS	098268298697	1	5	60	0.05
Ĕ	3523-10	0959094	1/2" x 1/2" x 1/2" CTS	098268299458	1	5	30	0.08
8	3523-14	0959139	3/4" x 3/4" x 3/4" CTS	098268299939	1	5	15	0.14
ä	3523-18	0959297	1 x 1" x 1" CTS	098268346596	1	5	15	0.20
	Package Typ	e: Bulk Pack						
į.	3523-08CP	81902960	3/8" x 3/8" x 3/8" CTS	840213003142	10	10	120	0.05
Ĕ	3523-10CP	81902961	1/2" x 1/2" x 1/2" CTS	840213003159	10	10	80	0.08
Q M	3523-14CP	81902963	3/4" x 3/4" x 3/4" CTS	840213003166	5	5	40	0.14
ы	3523-18CP	81902965	1" x 1" x 1" CTS	840213003173	5	5	25	0.20

Reducing Tees

Package Type: Single Pack



*	3524R-101004	0959095	1/2" CTS x 1/2" CTS x 1/4" OD	098268299465	1	5	30	0.08
Ë	3524R-141410	0959140	3/4" x 3/4" x 1/2" CTS	098268299946	1	5	15	0.14
۳	3524R-181814	0959796	1" x 1" x 3/4" CTS	098268050738	1	5	15	0.18
	Package Type:	Bulk Pack						
*	3524R-101004CP	81902967	1/2" CTS x 1/2" CTS x 1/4" OD	840213003180	10	10	80	0.08
Ë	3524R-141410CP	81902968	3/4" x 3/4" x 1/2" CTS	840213003197	5	5	50	0.14
u.	3524R-181814CP	81902969	1" x 1" x 3/4" CTS	840213003203	5	5	30	N 18

Double Reducing Tees

Package Type: Single Pack

LEAD 3526R-141010	0959340	3/4" x 1/2" x 1/2" CTS	098268966213	1	5	30	0.11
Package Type:	Bulk Pack						
LEAD 3526R-141010CP	81902970	3/4" x 1/2" x 1/2" CTS	840213003210	10	10	80	0.11

Male Threaded Tees

Package Type: Single Pack

LEAD 3530-1008	0959406	1/2" x 1/2" x 1/2" NPT	098268533392	1	5	30	0.09
Package Type	e: Bulk Pack						
1530-1008CP	81902973	1/2" x 1/2" x 1/2" NPT	840213003241	10	10	80	0.09

Stackable Tees

3533-18CP

Package Type: Single Pack

81902978



ů	3533-08	0959039	3/8" x 3/8" x 3/8" CTS	098268298703	1	5	60	0.04
1	3533-10	0959097	1/2" x 1/2" x 1/2" CTS	098268299489	1	5	30	0.07
6	3533-14	0959142	3/4" x 3/4" x 3/4" CTS	098268299960	1	5	15	0.13
Ë	3533-18	0959797	1" x 1" x 1" CTS	098268050745	1	5	15	0.18
	Package Ty	pe: Bulk Pack						
į.	3533-08CP	81902974	3/8" x 3/8" x 3/8" CTS	840213003258	10	10	120	0.04
	3533-10CP	81902975	1/2" x 1/2" x 1/2" CTS	840213003265	10	10	100	0.07
9	3533-14CP	81902977	3/4" x 3/4" x 3/4" CTS	840213003272	5	5	40	0.13

840213003289

5

5

25

0.18

1" x 1" x 1" CTS

^{*}The wetted surface of this product contacted by consumable water contains less than 0.25% of lead by weight. Consult factory for ordering code numbers of special models/options.



Model	Ordering Code	Size & Connection	UPC	Unit Pack	(Inner Ctn.) Minimum	Master Carton	Unit Weight
				Qty.	Order Qty.	Qty.	(lbs.)

Plastic Fitting Tees (continued)

Reducing Stackable Tees

Package Type: Single Pack

Q L	3533R-1004	0959470	1/2" CTS x 1/2" CTS x 1/4" OD	098268089202	1	5	30	0.07
5	3533R-1410	0959476	3/4" x 3/4" x 1/2" CTS	098268089387	1	5	15	0.10
	Package Type:	Bulk Pack						
Q i	3533R-1004CP	81902980	1/2" CTS x 1/2" CTS x 1/4" OD	840213003296	1	1	100	0.07
38	3533R-1410CP	81902981	3/4" x 3/4" x 1/2" CTS	840213003302	1	1	100	0.10

Stackable Branch Tees

Package Type: Single Pack

LEAD 3534-10	0959342	1/2" x 1/2" x 1/2" CTS	098268966237	1	5	15	0.07
Package Type	e: Bulk Pack						
LEAD FREE* 3534-10CP	81902983	1/2" x 1/2" x 1/2" CTS	840213003319	10	10	100	0.07

Plastic Fitting Elbows

Elbows

Package Type: Single Pack



	. 7 0 - 1	omigio i don	
3517_08		0050035	

Ĭ.	3517-08	0959035	3/8" CTS	098268298598	1	5	60	0.04
Ĕ	3517-10	0959087	1/2" CTS	098268299342	1	5	30	0.06
8	3517-14	0959138	3/4" CTS	098268299915	1	5	25	0.11
3	3517-18	0959300	1" CTS	098268346657	1	5	15	0.15
	Package Ty	pe: Bulk Pack						

3517-18

	donago .yp	or Bank r don						
į.	3517-08CP	81902933	3/8" CTS	840213002985	10	10	200	0.04
-	3517-10CP	81902934	1/2" CTS	840213002992	10	10	100	0.06
9	3517-14CP	81902936	3/4" CTS	840213003005	10	10	50	0.11
Ë	3517-18CP	81902939	1" CTS	840213003012	5	5	40	0.15

Reducing Elbow

Package Type: Single Pack

	omigio i don						
LEAD 3517R-1410	0959339	3/4 CTS x 1/2 CTS	098268966206	1	5	15	11.5

Stackable Elbows

Package Type: Single Pack



ř.	3518-08	0959036	3/8" CTS	098268298604	1	5	60	0.03
Ĕ	3518-10	0959096	1/2" CTS	098268299472	1	5	60	0.04
AD	3518-14	0959141	3/4" CTS	098268299953	1	5	15	0.05
ä	3518-18	0959794	1" CTS	098268050714	1	5	30	0.12

3518-10

	Package Typ	e: Bulk Pack						
ř.	3518-08CP	81902940	3/8" CTS	840213003029	10	10	200	0.03
Ë	3518-10CP	81902941	1/2" CTS	840213003036	10	10	100	0.04
AD	3518-14CP	81902943	3/4" CTS	840213003043	10	10	80	0.05
ä	3518-18CP	81902945	1" CTS	840213003050	5	5	30	0.12



Model	Ordering Code	Size & Connection	UPC	Unit Pack Qty.	(Inner Ctn.) Minimum Order Qtv.	Master Carton	Unit Weight (lbs.)
				uty.	Uluel Qty.	Qty.	(IDS.)

Plastic Fitting Elbows (continued)

Male Elbows

Package Type: Single Pack



351	Q_1	111	2

ř.	3519-1006	0959089	1/2"CTS x 3/8" NPT	098268299366	1	5	60	0.04
Ĕ	3519-1008	0959088	1/2" CTS x 1/2" NPT	098268299359	1	5	60	0.04
AD	3519-1412	0959791	3/4" CTS x 3/4" NPT	098268040920	1	5	30	0.10
"	3519-1816	0959795	1" CTS x 1" NPT	098268050721	1	5	15	0.12
	Package Type	e: Bulk Pack						
o iu	3519-1006CP	81902947	1/2"CTS x 3/8" NPT	840213003067	10	10	100	0.04
	3519-1008CP	81902948	1/2" CTS x 1/2" NPT	840213003074	10	10	100	0.04
- 114	3519-1816CP	81902949	1" CTS x 1" NPT	840213003081	5	5	50	0.12

Female Swivel Elbows

Package Type: Single Pack



352	^ 4	04	
ふつノ	U- I	w	_

3520-0808	0959037	3/8" CTS x 1/2" NPS	098268298611	1	5	60	0.04
3520-0813	0959043	3/8" CTS x 7/8" BC	098268298741	1	5	60	0.04
3520-1008	0959090	1/2" CTS x 1/2" NPS	098268299373	1	5	30	0.06
3520-1012	0959091	1/2" CTS x 3/4" NPS	098268299380	1	5	30	0.06
3520-1013	0959093	1/2" CTS x 7/8" BC	098268299441	1	5	30	0.10
3520-1014	0959293	1/2" CTS x 3/4" FGHT	098268343854	1	5	30	0.06
3520-1412	0959792	3/4" CTS x 3/4" NPT	098268040937	1	5	30	0.10
Package Type	: Bulk Pack						
3520-0808CP	81902950	3/8" CTS x 1/2" NPS	840213003098	10	10	100	0.04
3520-1008CP	81902952	1/2" CTS x 1/2" NPS	840213003104	10	10	100	0.06
3520-1012CP	81902955	1/2" CTS x 3/4" NPS	840213003111	10	10	100	0.08
3520-1014CP	81902957	1/2" CTS x 3/4" FGHT	840213003128	10	10	100	0.06
	3520-0813 3520-1008 3520-1012 3520-1013 3520-1014 3520-1412 Package Type 3520-0808CP 3520-1008CP 3520-1012CP	3520-0813 0959043 3520-1008 0959090 3520-1012 0959091 3520-1013 0959093 3520-1014 0959293 3520-1412 0959792 Package Type: Bulk Pack 3520-0808CP 81902950 3520-1008CP 81902952 3520-1012CP 81902955	3520-0813 0959043 3/8" CTS x 7/8" BC 3520-1008 0959090 1/2" CTS x 1/2" NPS 3520-1012 0959091 1/2" CTS x 3/4" NPS 3520-1013 0959093 1/2" CTS x 7/8" BC 3520-1014 0959293 1/2" CTS x 3/4" FGHT 3520-1412 0959792 3/4" CTS x 3/4" NPT Package Type: Bulk Pack 3520-0808CP 81902950 3/8" CTS x 1/2" NPS 3520-1008CP 81902952 1/2" CTS x 3/4" NPS 3520-1012CP 81902955 1/2" CTS x 3/4" NPS	3520-0813 0959043 3/8" CTS x 7/8" BC 098268298741 3520-1008 0959090 1/2" CTS x 1/2" NPS 098268299373 3520-1012 0959091 1/2" CTS x 3/4" NPS 098268299380 3520-1013 0959093 1/2" CTS x 7/8" BC 098268299441 3520-1014 0959293 1/2" CTS x 3/4" FGHT 098268343854 3520-1412 0959792 3/4" CTS x 3/4" NPT 098268040937 Package Type: Bulk Pack 3520-0808CP 81902950 3/8" CTS x 1/2" NPS 840213003098 3520-1008CP 81902952 1/2" CTS x 3/4" NPS 840213003104	3520-0813 0959043 3/8" CTS x 7/8" BC 098268298741 1 3520-1008 0959090 1/2" CTS x 1/2" NPS 098268299373 1 3520-1012 0959091 1/2" CTS x 3/4" NPS 098268299380 1 3520-1013 0959093 1/2" CTS x 7/8" BC 098268299441 1 3520-1014 0959293 1/2" CTS x 3/4" FGHT 098268343854 1 3520-1412 0959792 3/4" CTS x 3/4" NPT 098268040937 1 Package Type: Bulk Pack 3520-0808CP 81902950 3/8" CTS x 1/2" NPS 840213003098 10 3520-1008CP 81902952 1/2" CTS x 1/2" NPS 840213003104 10 3520-1012CP 81902955 1/2" CTS x 3/4" NPS 840213003111 10	3520-0813 0959043 3/8" CTS x 7/8" BC 098268298741 1 5 3520-1008 0959090 1/2" CTS x 1/2" NPS 098268299373 1 5 3520-1012 0959091 1/2" CTS x 3/4" NPS 098268299380 1 5 3520-1013 0959093 1/2" CTS x 7/8" BC 098268299441 1 5 3520-1014 0959293 1/2" CTS x 3/4" FGHT 098268343854 1 5 3520-1412 0959792 3/4" CTS x 3/4" NPT 098268040937 1 5 Package Type: Bulk Pack 3520-0808CP 81902950 3/8" CTS x 1/2" NPS 840213003098 10 10 3520-1008CP 81902955 1/2" CTS x 3/4" NPS 840213003104 10 10	3520-0813 0959043 3/8" CTS x 7/8" BC 098268298741 1 5 60 3520-1008 0959090 1/2" CTS x 1/2" NPS 098268299373 1 5 30 3520-1012 0959091 1/2" CTS x 3/4" NPS 098268299380 1 5 30 3520-1013 0959093 1/2" CTS x 7/8" BC 098268299441 1 5 30 3520-1014 0959293 1/2" CTS x 3/4" FGHT 098268343854 1 5 30 3520-1412 0959792 3/4" CTS x 3/4" NPT 098268040937 1 5 30 Package Type: Bulk Pack 3520-0808CP 81902950 3/8" CTS x 1/2" NPS 840213003098 10 10 100 3520-1008CP 81902955 1/2" CTS x 3/4" NPS 840213003104 10 10 100

Drop Ear Elbows



Package Type: Single Pack

LEAD FREE* 3521-1008	0959092	1/2" CTS x 1/2" NPT	098268299397	1	5	30	0.07
Package Type	: Bulk Pack						
1521-1008CP	81902958	1/2" CTS x 1/2" NPT	840213003135	10	10	80	0.07

Hose Barb Elbows

Package	Type:	Single	Pack

montage .ype	. omigic i don						
1512-1008 STEE	0959472	1/2" CTS x 1/2" HB	098268089240	1	5	60	0.02
Package Type	: Bulk Pack						
TREE* 3512-1008CP	81902902	1/2" CTS x 1/2" HB	840213002831	10	10	200	0.02

Elbow Pump Adapter

Package 1	Mo:	Rulk	Dack

	Jpor Dame : don						
FREE* 3576-10CP	81903041	1/2" CTS	840213003876	10	10	100	0.05



0.02

Model	Ordering Code	Size & Connection	UPC	Unit Pack	(Inner Ctn.) Minimum	Master Carton	Unit Weight
				Qty.	Order Qty.	Qty.	(lbs.)

Plastic Fitting Connectors

Couplings

Package Type: Single Pack



ĭ	3515-08	0959032	3/8" CTS	098268298550	1	5	60	0.03	
	3515-10	0959079	1/2" CTS	098268299267	1	5	60	0.05	
9	3515-14	0959133	3/4" CTS	098268299861	1	5	30	0.09	
ľ	3515-18	0959299	1" CTS	098268346640	1	5	30	0.13	
	Package Type: Bulk Pack								
ì	3515-08CP	81902913	3/8" CTS	840213002909	10	10	200	0.03	
Ė	3515-10CP	81902914	1/2" CTS	840213002916	10	10	100	0.05	
	3515-14CP	81902916	3/4" CTS	840213002923	10	10	60	0.09	
E	3515-18CP	81902918	1" CTS	840213002930	5	5	40	0.13	

Reducing Couplings

Package Type: Single Pack



3515R-1004

į	3515R-1004	0959080	1/2" CTS x 1/4" OD	098268299274	1	5	60	0.05
ä	3515R-1008	0959081	1/2" CTS x 3/8" CTS	098268299281	1	5	60	0.04
6	3515R-1410	0959134	3/4" CTS x 1/2" CTS	098268299878	1	5	30	0.08
Ë	3515R-1814	0959793	1" CTS x 3/4" CTS	098268050707	1	5	30	0.11
	Package Type:	Bulk Pack						
į	3515R-1004CP	81902924	1/2" CTS x 1/4" OD	840213002947	10	10	100	0.05
ä	3515R-1008CP	81902925	1/2" CTS x 3/8" CTS	840213002954	10	10	100	0.04
G 5	3515R-1410CP	81902926	3/4" CTS x 1/2" CTS	840213002961	10	10	100	0.08
E	3515R-1814CP	81902927	1" CTS x 3/4" CTS	840213002978	5	5	40	0.11

Male Adapters

3501-0806

Package Type: Single Pack

0959033



3501-1412

	3501-1006	0959269	1/2" CTS x 3/8" NPT	098268338447	1	5	60	0.03
*	3501-0808	0959034	3/8" CTS x 1/2" NPT	098268298574	1	5	60	0.03
Ė	3501-1008	0959083	1/2" CTS x 1/2" NPT	098268299304	1	5	60	0.04
9	3501-1012	0959084	1/2" CTS x 3/4" NPT	098268299311	1	5	60	0.04
ŀ	3501-1412	0959136	3/4" CTS x 3/4" NPT	098268299892	1	5	30	0.06
	3501-1416	0959788	3/4" CTS x 1" NPT	098268040890	1	5	30	0.09
	3501-1816	0959301	1" CTS x 1" NPT	098268346664	1	5	30	0.11
Package Type: Bulk Pack								
	3501-0806CP	81902877	3/8" CTS x 3/8" NPT	840213002671	10	10	100	0.02

098268298567

3/8" CTS x 3/8" NPT



3501-1816

3501	-0806CP	81902877	3/8" CTS x 3/8" NPT	840213002671	10	10	100	0.02
3501	-1006CP	81902879	1/2" CTS x 3/8" NPT	840213002695	10	10	100	0.03
3501	-0808CP	81902878	3/8" CTS x 1/2" NPT	840213002688	10	10	200	0.03
3501	-1008CP	81902880	1/2" CTS x 1/2" NPT	840213002701	10	10	100	0.04
3501	-1012CP	81902882	1/2" CTS x 3/4" NPT	840213002718	10	10	100	0.04
₫ 3501	-1014CP	81902883	1/2" CTS x 3/4" GHT	840213002725	10	10	100	0.04
3501	-1412CP	81902885	3/4" CTS x 3/4" NPT	840213002732	10	10	100	0.06
3501	-1416CP	81906544	3/4" CTS x 1" NPT	098268131543	10	10	100	0.09
3501	-1816CP	81902887	1" CTS x 1" NPT	840213002749	5	5	50	0.11

0.04



Plastic Fittings

Model	Ordering Code	Size & Connection	UPC	Unit Pack Qty.	(Inner Ctn.) Minimum Order Qtv.	Master Carton	Unit Weight (lbs.)
				uty.	Uluel Qty.	Qty.	(IDS.)

Plastic Fitting Connectors (continued)

Female Swivel Adapters

Package Type: Single Pack



_								
	3510-0808	0959790	3/8" CTS x 1/2" NPS	098268040913	1	5	60	0.04
	3510-1008	0959085	1/2" CTS x 1/2" NPS	098268299328	1	5	60	0.04
, W	3510-1012	0959086	1/2" CTS x 3/4" NPS	098268299335	1	5	30	0.06
Ë	3510-1013	0959292	1/2" CTS x 3/4" Closet	098268343847	1	5	30	0.06
PD	3510-1014	0959235	1/2" CTS x 3/4" FGHT	098268965148	1	5	30	0.08
ä	3510-1412	0959137	3/4" CTS x 3/4" NPS	098268299908	1	5	30	0.08
	3510-1416	0959789	3/4" CTS x 1" NPS	098268040906	1	5	30	0.09
	3510-1816	0959298	1" CTS x 1" NPS	098268346633	1	5	30	0.11

00

3510-1013

Package Type: Bulk Pack											
3510-0808CP	81902888	3/8" CTS x 1/2" NPS	840213002756	10	10	100					
3510-0814CP	81902890	3/8" CTS x 1/2" FGHT	840213002763	10	10	100					
3510-1008CP	81902891	1/2" CTS x 1/2" NPS	840213002770	10	10	100					

ı	3510-0814CP	81902890	3/8" CTS x 1/2" FGHT	840213002763	10	10	100	0.06
į	3510-1008CP	81902891	1/2" CTS x 1/2" NPS	840213002770	10	10	100	0.04
ï	3510-1012CP	81902894	1/2" CTS x 3/4" NPS	840213002787	10	10	100	0.06
9	3510-1013CP	81902895	1/2" CTS x 3/4" Closet	840213002794	10	10	100	0.06
Ė	3510-1014CP	81902896	1/2" CTS x 3/4" FGHT	840213002800	10	10	100	0.08
	3510-1412CP	81902897	3/4" CTS x 3/4" NPS	840213002817	10	10	100	0.08
	3510-1816CP	81902899	1" CTS x 1" NPS	840213002824	5	5	80	0.11

Hose Barb Stems

Package Type: Single Pack

LEAD 3511-1008	0959471	1/2" CTS x 1/2" Barb	098268089219	1	6	540	0.3
Package Type	: Bulk Pack						
LEAD 3511-1008CP	81906548	1/2" CTS x 1/2" Barb	098628068535	10	200	2,000	0.3

Hose Barb Adapters

Package Type: Single Pack



0	3513-1008	0959291	1/2" CTS x 1/2" HB	098268089219	1	5	60	0.04
ΕA	3513-1412	0959477	3/4" CTS x 3/4" HB	098268089394	1	5	30	0.06
	3513-1816	0959478	1" CTS x 1" HB	098268089417	1	5	30	0.09
Package Type: Bulk Pack								
ΔA	# 3513-1008CP	81902904	1/2" CTS x 1/2" HB	840213002848	10	10	100	0.04
=	5513-1412CP	81902906	3/4" CTS x 3/4" Barb	840213002855	10	10	100	0.06

Pump Adapters

Package Type: Bulk Pack

rackage type	- Dant Tuon						
LEAD 3575-10CP	81903040	1/2" CTS	840213003586	10	10	100	0.04



60

0.02

Model	Ordering Code	Size & Connection	UPC	Unit Pack	(Inner Ctn.) Minimum	Master Carton	Unit Weight
				Qty.	Order Qty.	Qty.	(lbs.)

Plastic Fitting Stems

Male Stems

Package Type: Single Pack

LEAD 3527-1008	0959365	1/2" CTS x 1/2" NPT	098268460391	1	5	30	0.02
Package Type	: Bulk Pack						
₽ 3527-1008CP	81902971	1/2" CTS x 1/2" NPT	840213003227	10	10	200	0.02
≝ 3527-1416CP	81906542	3/4" CTS x 1" NPT	098268131543	10	10	80	0.09

Female Stems

Package Type: Single Pack

3528-1008	0959364	1/2" CTS x 1/2" NPS	098268460384	1	5	60	0.03		
Package Type	Package Type: Bulk Pack								
3528-1008CP	81902972	1/2" CTS x 1/2" NPS	840213003234	10	10	150	0.03		

098268298734

Reducing Stems

Package Type: Single Pack



į.	3514-1008	0959082	1/2" CTS x 3/8" CTS	098268299298	1	5	60	0.03
ä	3514-1410	0959135	3/4" CTS x 1/2" CTS	098268299885	1	5	30	0.04
AD	3514-1810	0959407	1" CTS x 1/2" CTS	098268533408	1	5	30	0.05
=	3514-1814	0959294	1" CTS x 3/4" CTS	098268346565	1	5	30	0.07
	Package Type	: Bulk Pack						
į.	3514-1008CP	81902908	1/2" CTS x 3/8" CTS	840213002862	10	10	100	0.03
1	3514-1410CP	81902909	3/4" CTS x 1/2" CTS	840213002879	10	10	100	0.04
Δ¥	3514-1810CP	81902911	1" CTS x 1/2" CTS	840213002886	5	5	50	0.05
E	3514-1814CP	81902912	1" CTS x 3/4" CTS	840213002893	5	5	50	0.07

Hose Barb Stems

Package Type: Bulk Pack

LEAD 3511-1008	81906548	1/2" CTS	098268068535	200	200	2000	0.02

3/8" CTS

Plastic Fitting Ends

0959042

End Caps

3545-08



3545-10



3545-14

3545-10	0959109	1/2" CTS	098268299618	1	5	60	0.03
3545-14	0959145	3/4" CTS	098268299991	1	5	30	0.06
3545-18	0959263	1" CTS	098268338386	1	5	30	0.08
Package T	ype: Bulk Pack						
3545-08CP	81902997	3/8" CTS	840213003401	10	10	200	0.02
3545-10CP	81902998	1/2" CTS	840213003418	10	10	200	0.03
3545-14CP	81903000	3/4" CTS	840213003425	10	10	100	0.06
3545-18CP	81903002	1" CTS	840213003432	5	5	50	0.08
	3545-14 3545-18 Package T 3545-08CP 3545-10CP 3545-14CP	3545-14 0959145 3545-18 0959263 Package Type: Bulk Pack 3545-08CP 81902997 3545-10CP 81902998 3545-14CP 81903000	3545-14 0959145 3/4" CTS 3545-18 0959263 1" CTS Package Type: Bulk Pack 3545-08CP 81902997 3/8" CTS 3545-10CP 81902998 1/2" CTS 3545-14CP 81903000 3/4" CTS	3545-14 0959145 3/4" CTS 098268299991 3545-18 0959263 1" CTS 098268338386 Package Type: Bulk Pack 3545-08CP 81902997 3/8" CTS 840213003401 3545-10CP 81902998 1/2" CTS 840213003418 3545-14CP 81903000 3/4" CTS 840213003425	3545-14 0959145 3/4" CTS 098268299991 1 3545-18 0959263 1" CTS 098268383836 1 Package Type: Bulk Pack 3545-08CP 81902997 3/8" CTS 840213003401 10 3545-10CP 81902998 1/2" CTS 840213003418 10 3545-14CP 81903000 3/4" CTS 840213003425 10	3545-14 0959145 3/4" CTS 098268299991 1 5 3545-18 0959263 1" CTS 098268383836 1 5 Package Type: Bulk Pack 3545-08CP 81902997 3/8" CTS 840213003401 10 10 3545-10CP 81902998 1/2" CTS 840213003418 10 10 3545-14CP 81903000 3/4" CTS 840213003425 10 10	3545-14 0959145 3/4" CTS 098268299991 1 5 30 3545-18 0959263 1" CTS 098268338386 1 5 30 Package Type: Bulk Pack 3545-08CP 81902997 3/8" CTS 840213003401 10 10 200 3545-10CP 81902998 1/2" CTS 840213003418 10 10 200 3545-14CP 81903000 3/4" CTS 840213003425 10 10 100




Model	Ordering Code	Size & Connection	UPC	Unit Pack Qty.	(Inner Ctn.) Minimum Order Qtv.	Master Carton	Unit Weight (lbs.)
				uty.	Uluel Qty.	Qty.	(IDS.)

Plastic Valves

Straight Valves

Package Type: Single Pack







Collet Covers

Package Type: Single Pack

	3555-1006	0959185	1/2" CTS x 1/4" CTS	098268322651	1	5	30	0.20
96	3555-1008	0959191	1/2" CTS x 3/8" CTS	098268326772	1	5	15	0.60

Female Straight Valves

Package Type: Single Pack

	3552-0806	0959186	1/2" NPS x 1/4" CTS	098268322668	1	5	30	0.08
₩£	3552-0808	0959187	1/2" NPS x 3/8" CTS	098268322675	1	5	30	0.08

Stackable Valves

Package Type: Single Pack

9 3543-10	0959366	1/2" CTS	098268462661	1	5	30	0.11
≝€ 3543R-1004	0959367	1/2" CTS x 1/4" OD	098268463293	1	5	30	0.16
Package Type	e: Bulk Pack						
LEAD 3543-10CP	81902995	1/2" CTS	840213003395	10	10	80	0.11

Tee Valves

Package Type: Single Pack

		3.0						
LEAD FREE	3550-1004	0959358	1/2" CTS x 1/4" OD	098268443547	1	5	15	0.09
	Package Type	: Bulk Pack						
o i	3550-1004CP	81903009	1/2" CTS x 1/4" OD	840213003494	10	10	80	0.09
ă	3550-0404CP	81906441	1/4" OD x 1/4" OD	840213003678	10	10	80	0.09
	3550-1404CP	81906403	3/4" CTS x 1/4" OD	840213003951	5	5	40	0.15

Check Valves

LEAD 3540-10	0959475	1/2" CTS	098268089370	1	5	30	0.06
Package Typ	e: Bulk Pack						
LEAD 3540-10CP	81902993	1/2" CTS	840213003371	10	10	80	0.06



1	Model	Ordering Code	Size & Connection	UPC	Unit Pack Qty.	(Inner Ctn.) Minimum Order Qty.	Master Carton Qty.	Unit Weight (lbs.)
F	Plastic Va	alves (co	ontinued)					
3	B-Way Selec	tor Valves						
P	Package Type:	Single Pack						
REE*	3538-10	0959473	1/2" CTS	098268089318	1	5	15	0.14
P	Package Type:	Bulk Pack						
REE*	3538-10CP	81902985	1/2" CTS	840213003326	10	10	80	0.14
	. W D	V-b						
	B-Way Bypas							
	Package Type:			00000000000				0.14
SEE.	3541-10	0959474	1/2" CTS	098268089363	1	5	15	0.14
	Package Type:		1 /OII OTC	0.4004.0000000	10	10		0.14
EE*	3541-10CP	81902994	1/2" CTS	840213003388	10	10	80	0.14
_	Angle Valves							
	Package Type:							
	3556-1006	0959182	1/2" CTS x 1/4" CTS	098268322613	1	5	30	0.20
الله ۱	3556-1008	0959184	1/2" CTS x 3/8" CTS	098268322644	1	5	30	0.25
	3557-1408	0959188	1/2" CTS x 3/4" MGHT	098268322682	1	5	30	0.25
F	Female Angl	e Valves						
Р	Package Type:	Single Pack						
9 <u>iu</u> 3	3553-0808	0959181	1/2" NPS x 1/4" CTS	098268322576	1	5	30	0.20
9E 3	3553-0608	0959183	1/2" NPS x 3/8" CTS	098268322637	1	5	30	0.12
F	Female Angl	e Valves (GHT					
P	Package Type:	Single Pack						
REE*	3554-1408	0959189	1/2" NPS x 3/4" MGHT	098268322699	1	5	30	0.25
F	Panel Mount	Valve						
_	Package Type:							
	3559-10CP	81903031	1/2" CTS	840213003531	10	10	80	0.13
IEE C	0000 1001	0100001	1/2 010	040210000001	10	10		0.10
	Shutoff Valve							
	Package Type:	Single Pack						
LEAD FREE*	LF3561-0604	0959768	1/4" OD x 3/8" Male Comp x 3/8" Female Comp	098268806236	1	5	5	0.16
	Package Type:	Bulk Pack	5/5 Tomale Ourip					
*			1/4" OD x 3/8" Male Comp x					
E L	LF3561-0604CP	81902858	3/8" Female Comp	098268806908	50	50	250	0.16
AP I	LF3561-0606CP	81902859	3/8" OD x 3/8" Male Comp x	098268806915	50	50	250	0.16
	Li 3301-00000F	01302033	3/8" Female Comp	03070000313	50	JU	200	0.10
C	Garden Hose	e Angle Va	alve					
_	Package Type:	Single Pack						
Р								
_	3557-1006	0959188	1/2" NPT x 3/4" MGHT	098268322682	1	5	30	0.25



Model	Ordering Code	Size & Connection	UPC	Unit Pack	(Inner Ctn.) Minimum	Master Carton	Unit Weight
				Qty.	Order Qty.	Qty.	(lbs.)

Plastic Fitting Miscellaneous

Collet Clips

Package Type: Three Pack



	3 71							
į.	3547-08	0959045	3/8" CTS	098268298758	3	5	60	0.00
Ë	3547-10	0959111	1/2" CTS	098268299649	3	5	60	0.00
Q M	3547-14	0959287	3/4" CTS	098268339062	3	5	60	0.00
۳	3547-18	0959268	1" CTS	098268338430	3	5	60	0.06
	Package Type	e: Bulk Pack						
į	3547-08CP	81903004	3/8" CTS	840213003456	100	100	5000	0.00
Ĕ	3547-10CP	81903005	1/2" CTS	840213003463	100	100	5000	0.00
P	3547-14CP	81903007	3/4" CTS	840213003470	100	100	2500	0.00
۳	3547-18CP	81903008	1" CTS	840213003487	25	25	2500	0.06
_								

Collet Covers

Package Type: Bulk Pack

	o iu	3555-10CP	81903020	1/2" CTS	840213003500	25	25	300	0.00
ŀ		3555-14CP	81903023	3/4" CTS	840213003517	25	25	300	0.00
ı		3555-18CP	81903024	1" CTS	840213003524	25	25	250	0.01



Cone Seal

3560-18CP

Package Type: Bulk Pack

FREE* 161-08CP	81902634	For 1/2" NPT to 1/2" NPS	840213002459	100	100	2000	0.00

161

PEX Tube Stiffeners

Package Type: Three Pack

81903035

3560-08	0959479	3/8" CTS	098268089509	3	5	60	0.01				
£ 3560-10	0959480	1/2" CTS	098268089530	3	5	60	0.01				
3560-14	0959481	3/4" CTS	098268089547	3	5	60	0.02				
3560-18	0959482	1" CTS	098268089554	3	5	60	0.02				
Package Type: Bulk Pack											
ъ 3560-08СР	81903032	3/8" CTS	840213003548	100	100	2000	0.00				
3560-10CP	81903033	1/2" CTS	840213003555	100	100	1000	0.02				
⊋ 3560-14CP	81903034	3/4" CTS	840213003562	100	100	1000	0.01				

840213003579

25

25

250

0.01

1" CTS



	Model	Ordering Code	Size & Connection	UPC	Unit Pack Qty.	(Inner Ctn.) Minimum Order Qty.	Master Carton Qty.	Unit Weight (lbs.)
			_					
	Plastic F	itting M	anifolds - Singl	е				
	Manifolds -	•	-					
LEAD	Package Type:							
FREE*		0959257	1" CTS x 1/2" CTS	098268338324	1	5	25	1.00
LEAD	Package Type:		1" CTS x 1/2" CTS	0.40012002752	20	20	20	1.00
FREE*	3589-1810CP	81903052	1 CISX 1/2 CIS	840213003753	20	20	20	1.00
	Manifolds - S	•	m Body - Right					
LEAD FREE		0959258	1" CTS x 1/2" CTS	098268338331	1	5	15	0.07
BRISS	Package Type:							
LEAD FREE*	3590-1810CP	81903053	1" CTS x 1/2" CTS	840213003760	20	20	20	0.07
	Manifold - S	ingle Sten	n Body - Left					
	Package Type:	Single Pack						
LEAD FREE*	3591-1810	0959259	1" CTS x 1/2" CTS	098268338348	1	5	15	0.26
	Package Type:	Bulk Pack						
LEAD FREE*	3591-1810CP	81903054	1" CTS x 1/2" CTS	840213003777	20	20	20	0.26
	Manifold Sin	•	Mounting Kits					
LEAD FREE*	3581-18	0959260	For 35 Series Single Manifold	098268338355	1	5	30	0.50
	Package Type:	Bulk Pack						
LEAD FREE*	3581-18CP	81903044	For 35 Series Single Manifold	840213003609	10	10	100	0.07
	Plastic F		anifolds - Dual					
	Package Type:		-					
LEAD EREE*	3583-1810	0959303	1" CTS x 1/2" CTS	098268351460	1	5	25	0.40
	Package Type:	Bulk Pack						
LEAD FREE*	3583-1810CP	81903046	1" CTS x 1/2" CTS	840213003633	10	10	10	0.40
	Manifolds - Package Type:		•					
LEAD FREE*	3584-1810	0959304	1" CTS x 1/2" CTS	098268351477	1	5	25	0.59
	Package Type:	Bulk Pack						
LEAD FREE*	3584-1810CP	81903047	1" CTS x 1/2" CTS	840213003746	10	10	10	0.59
	Manifold Du Package Type:		_					
LEAD FREE*	2500 10	0959295	For 35 Series Dual Manifold	098268346572	1	5	30	0.70
<u> </u>	Package Type:				<u> </u>	-		
LEAD FREE*	3580-18CP	81903043	For 35 Series Dual Manifold	840213003593	10	10	100	0.09



Model	Ordering Code	Size & Connection	UPC	Unit Pack Qty.	(Inner Ctn.) Minimum Order Qty.	Master Carton Qty.	Unit Weigh (lbs.)
Plastic	Fitting Ma	anifold Access	ories				
	ivider Plugs						
	e: Single Pack						
3582-18	0959266	For 35 Series	098268338416	1	5	60	0.18
Package Typ		. 0. 00 0000	00020000110				
AD 3582-18CP	81903045	For 35 Series	840213003616	5	5	100	0.0
Manifold B	eturn Ends						
	e: Single Pack						
3585-18	0959296	1" CTS	098268346589	1	5	15	1.0
Package Typ							
3585-18CP	81903048	1" CTS	840213003630	5	5	25	0.1
					,		
Manifold R	ed Label Pla	tes					
	e: Single Pack						
AD 3586-18	0959261	Red - For 35 and Metric	098268338362	1	5	60	0.2
Package Typ	e: Bulk Pack						
Package Typ 3586-18CP	81903049	Red - For 35 and Metric	840213003647	10	10	500	0.0
		Red - For 35 and Metric	840213003647	10	10	500	0.0
3586-18CP	81903049		840213003647	10	10	500	0.0
3586-18CP Manifold B	81903049 Slue Label Pla		840213003647	10	10	500	0.0
Manifold B Package Typ	81903049		840213003647 098268338379	10	10	500	
Manifold B Package Typ AD 3587-18	81903049 Elue Label Pla e: Single Pack 0959262	ntes					
Manifold B Package Typ AD Package Typ	81903049 Elue Label Pla e: Single Pack 0959262	ntes					0.2
Manifold B Package Typ AD Package Typ	81903049 Slue Label Pla e: Single Pack 0959262 e: Bulk Pack	ates Blue - For 35 and Metric	098268338379	1	5	60	0.2
Manifold B Package Typ AD Package Typ	81903049 Slue Label Pla e: Single Pack 0959262 e: Bulk Pack 81903050	Blue - For 35 and Metric Blue - For 35 and Metric	098268338379	1	5	60	0.2
Manifold B Package Typ AD Sarana Package Typ AD Sarana Package Typ AD Sarana Package Typ AD Manifold V	81903049 Filue Label Place: Single Pack 0959262 e: Bulk Pack 81903050	Blue - For 35 and Metric Blue - For 35 and Metric	098268338379	1	5	60	0.2
Manifold B Package Typ AD Package Typ AD S587-18CP Manifold V Package Typ	81903049 Elue Label Pla e: Single Pack 0959262 e: Bulk Pack 81903050 Calve Repair Fee: Bulk Pack	Blue - For 35 and Metric Blue - For 35 and Metric Kits	098268338379 840213003654	1 10	5	60 500	0.2
Manifold B Package Typ AD Package Typ AD Package Typ AD S587-18 Package Typ AD Manifold V Package Typ	81903049 Filue Label Place: Single Pack 0959262 e: Bulk Pack 81903050	Blue - For 35 and Metric Blue - For 35 and Metric	098268338379	1	5	60	0.2
Manifold B Package Typ AD 3587-18 Package Typ AD 3587-18CP Manifold V Package Typ AD 3588-10CP	81903049 Filue Label Place: Single Pack 0959262 e: Bulk Pack 81903050 Falve Repair Fee: Bulk Pack 81903051	Blue - For 35 and Metric Blue - For 35 and Metric Kits	098268338379 840213003654	1 10	5	60 500	0.2
Manifold B Package Typ AD 3587-18 Package Typ AD 3587-18CP Manifold V Package Typ AD 3588-10CP Manifold T	81903049 Slue Label Pla e: Single Pack 0959262 e: Bulk Pack 81903050 Salve Repair Fe: Bulk Pack 81903051	Blue - For 35 and Metric Blue - For 35 and Metric Kits	098268338379 840213003654	1 10	5	60 500	0.2
Manifold B Package Typ AD 3587-18 Package Typ AD 3587-18CP Manifold V Package Typ AD 3588-10CP Manifold T	81903049 Filue Label Place: Single Pack 0959262 e: Bulk Pack 81903050 Falve Repair Fee: Bulk Pack 81903051	Blue - For 35 and Metric Blue - For 35 and Metric Kits	098268338379 840213003654	1 10	5	60 500	0.0

1" CTS

1" CTS

0959264

81903003

Package Type: Bulk Pack

098268338393

840213003449

0.20

0.03

30

5

1546-18 TREE*

LEAD 3546-18CP



Model	Ordering Code	Size & Connection	UPC	Unit Pack	(Inner Ctn.) Minimum	Master Carton	Unit Weight
				Qty.	Order Qty.	Qty.	(lbs.)

Mini Tees


Tees

Package Type: Single Pack



in.	1023-04	17103003	1/4" OD	048643197626	1	5	60	0.02
	1023-06	17103023	3/8" OD	048643201262	1	5	60	0.04
	1023-08	17103033	1/2" OD	048643201347	1	5	60	0.07
	Package 1	Type: Bulk Pack						
*	1023-04CP	0666115	1/4" OD	098268426502	10	20	200	0.15
ë	1023-06CP	0666116	3/8" OD	098268426519	10	10	100	0.30
Н	1023-08CP	0666117	1/2" OD	098268426526	10	6	60	0.45

Reducing Tees





Model	Ordering Code	Size & Connection	UPC	Unit Pack Qty.	(Inner Ctn.) Minimum Order Qtv.	Master Carton	Unit Weight (lbs.)
				Qty.	Olubi Qty.	Qty.	(105.)

Mini Elbows

Elbows



Package Type:	Single Pack
1017-04	17103002

Ë	1017-06	17103022	3/8" OD	048643201255	1	5	60	0.05
ï	1017-08	17103032	1/2" OD	048643201330	1	5	60	0.05
	Package Typ	e: Bulk Pack						
Ť.,	1017-04CP	0666120	1/4" OD	098268426557	10	30	300	0.10
Ë	1017-06CP	0666121	3/8" OD	098268426564	10	10	100	0.20
ü	1017-08CP	0666122	1/2" OD	098268426571	10	10	100	0.30

048643197619

048643201217

5

5

60

0.03

60

0.03

1/4" OD



Reducing Elbows

Package Type: Single Pack

1017R

FREE 1017R-0604 0666146 3/8" OD x 1/4" OD 098268426816 10	20	200	0.10
---	----	-----	------

Stackable Elbows



	Package Ty	pe: Bulk Pack						
٥	1018-04CP	0666142	1/4" OD	098268426779	10	25	250	0.15
Š	1018-06CP	0666143	3/8" OD	098268426786	10	10	100	0.25
	1018-08CP	0666144	1/2" OD	098268426793	8	8	80	0.40

1/4" OD x 1/8" MNPT

Male Elbows

1019-0402



1019

Package Type: Single Pack

17103008

_						-		
ů	1019-0404	17103009	1/4" OD x 1/4" MNPT	048643201224	1	5	60	0.02
Ė	1019-0406	17103028	3/8" OD x 1/4" MNPT	048643201316	1	5	60	0.04
9	1019-0606	17103029	3/8" OD x 3/8" MNPT	048643201323	1	5	60	0.04
ŀ	1019-0806	17103038	1/2" OD x 3/8" MNPT	048643201378	1	5	60	0.05
	1019-0808	17103039	1/2" OD x 1/2" MNPT	048643201385	1	5	60	0.06
	Package Type	e: Bulk Pack						
	1019-0402CP	0666135	1/4" OD x 1/8" MNPT	098268426700	10	30	300	0.10
	1019-0404CP	0666136	1/4" OD x 1/4" MNPT	098268426717	10	30	300	0.05
	1019-0406CP	0666137	1/4" OD x 3/8" MNPT	098268426724	10	20	200	0.20
	1019-0604CP	0666138	3/8" OD x 1/4" MNPT	098268426731	10	10	100	0.15
1	1019-0606CP	0666139	3/8" OD x 3/8" MNPT	098268426748	10	20	200	0.15
١	1019-0806CP	0666140	1/2" OD x 3/8" MNPT	098268426755	10	10	100	0.25
۰	1019-0808CP	0666141	1/2" OD x 1/2" MNPT	098268426762	10	10	100	0.15



Model	Ordering Code	Size & Connection	UPC	Unit Pack	(Inner Ctn.) Minimum	Master Carton	Unit Weight
				Qty.	Order Qty.	Otv	(lbs.)

Mini Connectors

Couplings

Package Type: Single Pack



ř.	1015-04	17103000	1/4" OD	048643197596	1	5	60	0.02
ä	1015-05	17103015	5/16" OD	098268784831	1	5	60	0.04
6	1015-06	17103020	3/8" OD	048643197633	1	5	60	0.03
Ë	1015-08	17103030	1/2" OD	048643197657	1	5	60	0.05
	Package Ty	ype: Bulk Pack						
o ilu	1015-04CP	0666110	1/4" OD	098268426458	10	30	300	0.10
EAD	1015-06CP	0666111	3/8" OD	098268426465	10	10	100	0.20
- 11	1015-08CP	0666112	1/2" OD	098268426472	10	10	100	0.30

Reducing Couplings

1015R

Package Type: Single Pack



048643201170

098268426694

10

15

150

0.15

5

60

0.03

1/4" OD x 1/8" MNPT



Male Adapters

1001-0402

1001-0808CP

Package Type: Single Pack

17103004

0666134

					-	-		
	1001-0404	17103005	1/4" OD x 1/4" MNPT	048643201187	1	5	60	0.02
	1001-0406	17103006	1/4" OD x 3/8" MNPT	048643201194	1	5	60	0.04
į.	1001-0408	17103007	1/4" OD x 1/2" MNPT	048643201200	1	5	60	0.05
Œ	1001-0602	17103024	3/8" OD x 1/8" MNPT	048643201279	1	5	60	0.04
AD	1001-0604	17103025	3/8" OD x 1/4" MNPT	048643201286	1	5	60	0.04
ä	1001-0606	17103026	3/8" OD x 3/8" MNPT	048643201293	1	5	60	0.20
	1001-0608	17103027	3/8" OD x 1/2" MNPT	048643201309	1	5	60	0.05
	1001-0806	17103035	1/2" OD x 3/8" MNPT	048643201354	1	5	60	0.05
	1001-0808	17103036	1/2" OD x 1/2" MNPT	048643201361	1	5	60	0.05
	Package Type	: Bulk Pack						
	1001-0402CP	0666125	1/4" OD x 1/8" MNPT	098268426601	10	30	300	0.05
	1001-0404CP	0666126	1/4" OD x 1/4" MNPT	098268426618	10	30	300	0.10
	1001-0406CP	0666127	1/4" OD x 3/8" MNPT	098268426625	10	30	300	0.10
į.	1001-0408CP	0666128	1/4" OD x 1/2" MNPT	098268426632	10	25	250	0.15
Ë	1001-0602CP	0666129	3/8" OD x 1/8" MNPT	098268426649	10	25	250	0.15
A	1001-0604CP	0666130	3/8" OD x 1/4" MNPT	098268426656	10	20	200	0.15
1	1001-0606CP	0666131	3/8" OD x 3/8" MNPT	098268426663	10	20	200	0.15
	1001-0608CP	0666132	3/8" OD x 1/2" MNPT	098268426670	10	20	200	0.15
	1001-0806CP	0666133	1/2" OD x 3/8" MNPT	098268426687	10	15	150	0.20

1/2" OD x 1/2" MNPT



	Model	Ordering Code	Size & Connection	UPC	Unit Pack Qty.	(Inner Ctn.) Minimum Order Qty.	Master Carton Qty.	Unit Weight (lbs.)
--	-------	------------------	-------------------	-----	----------------------	---------------------------------------	--------------------------	--------------------------

Mini Connectors (continued)

Female Adapters

Package Type: Single Pack



	1010-0404	17103060	1/4" OD x 1/4" FNPT	048643236165	1	5	60	0.04
96	1010-0604	17103065	3/8" OD x 1/4" FNPT	048643236172	1	5	60	0.04
	Package Type:	Bulk Pack						
.	1010-0401CP	0666147	1/4" OD x 7/16" UNS	098268426823	10	20	200	0.20
Ĕ	1010-0601CP	0666148	3/8" OD x 7/16" UNS	098268426830	10	20	200	0.18
AD	1010-0404CP	0666123	1/4" OD x 1/4" FNPT	098268426588	10	20	200	0.15
"	1010-0604CP	0666124	3/8" OD x 1/4" FNPT	098268426595	10	20	200	0.15

Mini Stems

Male Stems

Package Type: Bulk Pack



į,	1027-0402CP	0666104	1/4" OD x 1/8" MNPT	098268426397	10	30	300	0.10	
Ĕ	1027-0604CP	0666106	3/8" OD x 1/4" MNPT	098268426410	10	10	100	0.20	
AD	1027-0606CP	0666107	3/8" OD x 3/8" MNPT	098268426427	10	10	100	0.20	
ш	1027-0806CP	0666108	1/2" OD x 3/8" MNPT	098268426434	10	10	100	0.20	

1014R

Reducing Stems

Package Type: Bulk Pack

LEAD 101	4R-0604CP	0666145	3/8" OD x 1/4" OD	098268426809	10	30	300	0.05

Mini Caps

End Caps



1045



LEAD FREE*	1045-04	17103047	1/4" OD	098268534573	1	5	60	0.05
	Package Typ	e: Bulk Pack						
LEAD FREE*	1045-04CP	0666109	1/4" OD	098268426441	10	50	500	0.05



Model	Ordering Code	Size & Connection	UPC	Unit Pack	(Inner Ctn.) Minimum	Master Carton	Unit Weight
				Qty.	Order Qty.	Qty.	(lbs.)

Mini Valves

Straight Valves

Package Type: Single Pack



E AD	1039-04	17103011	1/4" OD	048643201231	1	5	60	0.05
5 E	1039-06	17103041	3/8" OD	048643197688	1	5	60	0.06
	Package T	ype: Bulk Pack						
Q in	1039-04CP	0666102	1/4" OD	098268426373	10	8	80	0.45
뺼	1039-06CP	0666103	3/8" OD	098268426380	10	6	60	0.55

Male Straight Valves

Package Type: Single Pack



	1062-04	17103012	1/4" OD x 1/4" NPT	048643201248	1	5	60	0.05
끸뜬	1062-06	17103042	3/8" OD x3/8" NPT	048643201392	1	5	60	0.06
	Package Typ	e: Bulk Pack						
	1062-04CP	0666100	1/4" OD x 1/4" NPT	098268426359	10	8	80	0.45
뿔	1062-06CP	0666101	3/8" OD x3/8" NPT	098268426366	10	6	60	0.55

Female Angle Valves

Package Type: Bulk Pack

3 31							
9 iii 1053-0404CP	0666149	1/4" OD x 1/4" NPT	098268426847	10	8	80	0.45
≝	0666150	3/8" OD x 1/4" NPT	098268427134	10	6	60	0.50



Model	Ordering Code	Size & Connection	UPC	Unit Pack	(Inner Ctn.) Minimum	Master Carton	Unit Weight
				Qty.	Order Qty.	Qty.	(lbs.)

Metric Tees

Tees

Package Type: Single Pack

LEAD FREE*	1123-1515	81902169	15MM	840213133573	1	5	50	0.09375
	Package Type: Bu	ılk Pack						
o.*.	1123-1515CP	81902439	15MM	840213002329	10	10	80	0.09375
A H	1123-1515-5CP	81902440	15MM	840213003838	10	10	80	0.09375
-11	1623-2222CP	81902644	22MM	840213002503	5	5	40	0.14375

Reducing Tees

Package Type: Bulk Pack

Q iu	1624-221515CP	81902648	22MM x 15MM x 15MM	840213002510	5	5	60	0.125
5 E	1624-222215CP	81902650	22MM x 22MM x 15MM	840213002527	5	5	50	0.125

Stackable Tees

LEAD 1133-1515	81902172	15MM	840213133603	1	5	50	0.0625
Package Type:	Bulk Pack						
₽ iii 1133-1515CP	81902447	15MM	840213002343	10	10	100	0.0625
∃E 1133-2222CP	81902449	22MM	840213002350	5	5	40	0.125



Model	Ordering Code	Size & Connection	UPC	Unit Pack Qty.	(Inner Ctn.) Minimum Order Qty.	Master Carton Qty.	Unit Weight (lbs.)
Metric I	Filhanna						
	EIDOWS						
Elbows							
	e: Single Pack						
1117-1515	81902163	15MM	840213133511	1	5	50	0.0625
Package Typ	e: Bulk Pack						
1117-1515CP	81902424	15MM	840213002268	10	10	100	0.0625
1617-2222CP	81902640	22MM	840213002480	5	5	50	0.0625
Stackable	Elbows						
Package Typ	e: Single Pack						
1118-1515	81902164	15MM	840213133528	1	5	50	0.05
Package Typ	e: Bulk Pack						
1118-1515CP	81902426	15MM	840213002275	10	10	100	0.05
1618-2222CP	81902642	22MM	840213002497	5	5	80	0.075
_							
Male Elbo	ws						
Package Tyr	e: Bulk Pack						
1119-0815CP	81902428	15MM x 1/2" NPT	840213002282	10	10	100	0.05
1110 001001	01002420	10MW X 1/2 1W 1	040210002202	10	10	100	0.00
	vivel Elbows						
_	e: Single Pack						
1120-0815	81902166	15MM x 1/2" NPS	840213133542	1	5	50	0.0625
Package Typ	e: Bulk Pack						
1120-0815CP	81902431	15MM x 1/2" NPS	840213002299	10	10	100	0.0625
1120-1215CP	81902433	15MM x 3/4" NPS	840213002305	10	10	100	0.06875
Drop Ear E	Elbows						
Package Typ	e: Bulk Pack						
1121-0815CP	81902437	15MM x 1/2" NPS	840213133542	1	5	50	0.0625

Elbow Pump Adapter

	_		
Packa	ge Typ	e: Bull	k Pack

LEAD 2476-15CP	81902812	15MM	840213002626	10	10	100	0.05625



Model	Ordering Code	Size & Connection	UPC	Unit Pack	(Inner Ctn.) Minimum	Master Carton	Unit Weight
				Qty.	Order Qty.	Qty.	(lbs.)

Metric Connectors

Couplings

Package Type: Single Pack

LEAD 1115-1515	81902161	15MM	840213133498	1	5	50	0.0625
Package Type: Bulk Pack							
₽# 1115-1515CP	81902418	15MM	840213002244	10	10	100	0.0625
☐ 1615-2222CP	81902638	22MM	840213002473	5	5	60	0.08125

Reducing Couplings

Package Type: Single Pack

FREE* 1116	1015 8190216	52 1/2" CTS x 15MN	M 840213133504	1	5	50	0.0625			
Package Type: Bulk Pack										
LEAD FREE* 1116-	1015CP 8190242	22 1/2" CTS x 15MN	M 840213002251	10	10	100	0.04375			

Male Adapters (Brass)

Package Type: Bulk Pack

	1201-0815CP	81907005	15MM x 1/2" NPT	098268819816	10	10	10	0.213
HE.	1701-1222CP	81907012	22MM x 3/4" NPT	098268819922	10	10	10	0.33

Male Adapters

Package Type: Single Pack

LEAD FREE*	2402-0815	81902195	15MM x 1/2" NPT	840213133801	1	5	50	0.0375
	Package Type: Bull	k Pack						
Q in	2402-0815CP	81902767	15MM x 1/2" NPT	840213002565	10	10	100	0.0375
<u> </u>	2902-1222CP	81902834	22MM x 3/4" NPT	840213002640	5	5	100	0.0875

Female Swivel Adapters

Package Type: Single Pack

LEAD FREE*	1110-0815	81902158	15MM x 1/2" NPS	840213133467	1	5	50	0.05
	Package Type: Bu	lk Pack						
i.	1110-0815CP	81902402	15MM x 1/2" NPS	840213002206	10	10	100	0.05
Ë	1110-1215CP	81902404	15MM x 3/4" NPS	840213002213	10	10	100	0.06875
AD	2609-1215CP	81902827	15MM x 3/4" FGHT	840213002633	5	5	100	0.05
2	1607-1222CP	81902632	22MM x 3/4" NPS	840213002442	5	5	100	0.0625

Hose Barb Adapters

	rackage Type.	Single Fack						
LEAD FREE	2413-0815	81902200	15MM	840213133856	1	5	50	0.04
	Package Type: I	Bulk Pack						
o:	1413-0615CP	81902602	15MM x 3/8" HB	840213003739	10	10	100	0.0625
Š	2413-0815CP	81902778	15MM x 1/2" HB	840213002572	10	10	100	0.0375
	2913-1222CP	81902839	22MM x 3/4" HB	840213002657	10	10	100	0.0625



Model	Ordering	Size & Connection	UPC	Unit	(Inner Ctn.)	Master	Unit	
	Code			Pack	Minimum	Carton	Weight	
				Qty.	Order Qty.	Qty.	(lbs.)	

Metric Connectors (continued)

Pump Adapters

Package Type: Bulk Pack

LEAD 2475-15CP	81902811	15MM	840213002619	10	10	100	0.0375
THEE .							

Compression Adapters (Brass)

Package Type: Single Pack

LEAD 4040 00450D							
1212-0615CP	81907007	15MM x 3/8" CMP	098268819854	1	1	100	.23

Metric Stems

Male Stems (Brass)

Package Type: Bulk Pack

LEAD 1229-0615CP	81907008	15MM x 1/2" NPT	098268819861	10	10	10	0.15

Reducing Stem

Package Type: Bulk Pack

LEAD 1614-1522CP	81902636	22MM	840213002466	5	5	100	0.04375

Metric Caps

End Caps

Package Type: Single Pack

LEAD 1145-15	81902173	15MM	840213133610	1	5	50	0.03125
Package Type:	Bulk Pack						
₽₩ 1145-15CP	81902452	15MM	840213002374	10	10	200	0.03125
≝E 1645-22CP	81902652	22MM	840213002534	5	5	50	0.05

End Plugs

Package Type: Bulk Pack

₽ 1146-15CP	81902455	15MM	840213002381	10	10	100	0.01875
≝E 1146-18CP	81902456	15MM	840213006570	10	5	30	0.3



Model	Ordering Code	Size & Connection	UPC	Unit Pack Qty.	(Inner Ctn.) Minimum Order Qtv.	Master Carton	Unit Weight (lbs.)
				Qty.	Olubi Qty.	Qty.	(105.)

Metric Valves

Straight Valves

Package Type: Single Pack

LEAD 2439-1515	81902216	15MM	840213134006	1	5	50	0.13125
Package Type: I	Bulk Pack						
2439-1515CP	81902801	15MM	840213002589	10	10	80	0.13125
∃E 2939-2222CP	81902841	22MM	840213002664	5	5	40	0.4375

Stackable Valves

Package Type: Bulk Pack

₽# 2443-0415CP	81902807	15MM x 1/4" OD	840213002602	10	10	80	0.1125
≝ 2440-1515CP	81902803	15MM x 15MM	840213002596	10	10	80	0.1125

Tee Valves

Package Type: Bulk Pack

FREE 2444-0415-5CP 81902809 15MM x 1/4" 0D 8402131373		5	50	.15
---	--	---	----	-----

Check Valves

Package Type: Bulk Pack

LEAD 1140-15CP	81902451	15MM	840213002367	10	10	80	0.0625

Male Stem Check Valves (Brass)

Package Type: Bulk Pack

	3. 31.							
LEAD 1235-	-0815CP	81907010	15MM x 1/2" NPT	098268819892	10	10	10	0.15

Stem Check Valves (Brass)

Package Type: Bulk Pack

LEAD 1237-15CP	81907011	15MM	098268819915	10	10	10	0.15



Model	Ordering	Size & Connection	UPC	Unit	(Inner Ctn.)	Master	Unit	
	Code			Pack	Minimum	Carton	Weight	
				Qty.	Order Qty.	Qty.	(lbs.)	

Metric Miscellaneous

Collet Clip

Package Type: Single Pack

LEAD 1147-15	81902174	15MM	840213133627	3	5	50	0.00375
Package Type:	Bulk Pack						
₽ 1147-15CP	81902457	15MM	840213002398	100	100	5000	0.00125
☐	81902458	22MM	840213002404	100	100	500	0.0025

Collet Cover

Package Type: Bulk Pack

O.	2154-15CP	81902702	15MM	840213002541	25	25	300	0.002625
	2156-15CP	81902704	15MM	840213002558	25	25	300	0.002625
	2957-22CP	81902848	22MM	840213006280	25	25	300	0.003875

Elbow Clip

Package Type: Bulk Pack

₽₩ 2349-15CP	81902747	15MM	840213136895	10	10	300	.003
≝ 2349-22CP	81902748	22MM	840213136901	5	5	150	.003

Metric Manifolds - Single

Manifolds - Single Union Body

Package Type: Single Pack

	9						
LEAD 1189-1815	81902479	15MM	840213003708	1	5	20	0.21

Manifolds - Single Stem Body - Right

Package Type: Single Pack

LEAD 1190-1815	81902481	15MM	840213003715	1	5	20	0.19

Manifold - Single Stem Body - Left

Package Type: Single Pack

LEAD 1190-1815 81902481 15M	VI 840213003715	1 !	5 20	0.19
-----------------------------	-----------------	-----	------	------

Manifold Single Side Mounting Kits

1181-18	81902473	For Metric Series Dual Manifold	098268338355	1	1	50	0.07
---------	----------	----------------------------------	--------------	---	---	----	------



Model	Ordering Code	Size & Connection	UPC	Unit Pack Qty.	(Inner Ctn.) Minimum Order Qty.	Master Carton Qty.	Unit Weight (lbs.)
-------	------------------	-------------------	-----	----------------------	---------------------------------------	--------------------------	--------------------------

Metric Manifolds - Dual

Manifolds - Dual Union Body

Package Type: Single Pack

Manifolds - Dual Stem Body

Package Type: Single Pack

LEAD 1184-1815	81902476	15MM	840213003692	1	1	10	0.37

Manifold Dual Side Mounting Kits

Package Type: Single Pack

LEAD FREE*	1180-18	81902472	For Metric Series Dual Manifold	840213002411	1	1	50	0.09
---------------	---------	----------	------------------------------------	--------------	---	---	----	------

Metric Manifold Accessories

Manifold Return Ends

Package Type: Single Pack

	-						
LEAD 1185-18	81902477	1" CTS	098268346589	1	5	15	1.00

Manifold Red Label Plates

Package Type: Single Pack

1586-18 3586-18	0959261	Red - For 35 and Metric	098268338362	1	5	60	0.20
Package Type: B	ulk Pack						
LEAD FREE* 3586-18CP	81903049	Red - For 35 and Metric	840213003647	10	10	500	0.01

Manifold Blue Label Plates

Package Type: Single Pack

LEAD 3587-18	0959262	Blue - For 35 and Metric	098268338379	1	5	60	0.20	
Package Type: Bulk Pack								
LEAD FREE* 3587-18CP	81903050	Blue - For 35 and Metric	840213003654	10	10	500	0.01	

Manifold Valve Repair Kits

Package Type: Bulk Pack

	Duik Fack						
LEAD 1188-15CP	81902478	15MM	118811	10	10	50	0.04







Watts Family of Brands

Watts designs, manufactures, and sells an extensive line of flow control, water safety, water filtration & treatment, drainage, and PEX plumbing products.

The Watts family of companies provides a single source for solutions used to safely convey, conserve, and manage water.


Making Watts your single source for plumbing-related solutions will streamline your operations, save you money, and reduce the variety of repair parts needed for maintenance.
































USA: T: (978) 689-6066 • Watts.com Canada: T: (905) 332-4090 • Watts.ca Latin America: T: (52) 55-4122-0136 • Watts.com