

# Engineering Specification

Job Name \_\_\_\_\_  
 Job Location \_\_\_\_\_  
 Engineer \_\_\_\_\_  
 Approval \_\_\_\_\_  
 Tag \_\_\_\_\_

Contractor \_\_\_\_\_  
 Approval \_\_\_\_\_  
 Contractor's P.O. No. \_\_\_\_\_  
 Representative \_\_\_\_\_

## WD-LA Series Low-Rough-in Semi-Automatic Draw-Off Grease Interceptor




### Specification

Watts WD-LA Series recessed or floor mounted epoxy coated steel low-rough-in semi-automatic draw-off grease interceptor with gasketed cover secured with hex head perimeter bolts, removable grease accumulating cover and baffle assembly, deep seal trap with cleanout and air relief bypass, internal stainless steel flow control plate, flexible draw-off hose, outlet line shut-off valve, and IPS threaded connections

Flow Rate		
Suffix	Description	
20	20 GPM	<input type="checkbox"/>
25	25 GPM	<input type="checkbox"/>
35	35 GPM	<input type="checkbox"/>
50	50 GPM	<input type="checkbox"/>

Options		
Suffix	Description	
-O	Inlet & Outlet other than Standard	<input type="checkbox"/>
-SS	All Stainless Steel	<input type="checkbox"/>



Model No.	Flow Rate GPM	Grease Capacity Lbs.	A Inlet & Outlet	B Base To Center	C Top To Center	D Length	E Width	F Height
WD-20-LA	20	40	3"(76)	7 3/4"(197)	4"(102)	35"(889)	23"(584)	12"(305)
WD-25-LA	25	50	3"(76)	7"(178)	5"(127)	39 1/2"(1002)	26 1/2"(673)	12"(305)
WD-35-LA	35	70	4"(102)	7"(178)	4 1/2"(114)	41"(1041)	33"(838)	12"(305)
WD-50-LA	50	100	4"(102)	8 1/2"(216)	5 1/2"(140)	55"(1397)	33"(838)	12"(305)

### NOTICE

The information contained herein is not intended to replace the full product installation and safety information available or the experience of a trained product installer. You are required to thoroughly read all installation instructions and product safety information before beginning the installation of this product.

Watts product specifications in U.S. customary units and metric are approximate and are provided for reference only. For precise measurements, please contact Watts Technical Service. Watts reserves the right to change or modify product design, construction, specifications, or materials without prior notice and without incurring any obligation to make such changes and modifications on Watts products previously or subsequently sold.



**USA:** T: (800) 338-2581 • F: (828) 248-3929 • [Watts.com](http://Watts.com)  
**Canada:** T: (888) 208-8927 • F: (905) 481-2316 • [Watts.ca](http://Watts.ca)  
**Latin America:** T: (52) 55-4122-0138 • [Watts.com](http://Watts.com)