ES-WD-FS-740 2332

Engineering Specification

Job Name	Contractor
Job Location	Approval
Engineer	Contractor's P.O. No.
Approval	Representative

FS-740 12" Square x 8" Deep Sanitary Floor Sink

Specification

Watts FS-740 12" square x 8"deep sanitary floor sink with white acid resistant porcelain enamel coated interior, loose set porcelain enamel coated cast iron grate, polypropylene dome bottom strainer, and no hub (standard) outlet.

Call customer service at 1 (800) 338-2581 if you need assistance with technical details.

Pipe Sizing			Outlet Type			
Suffix	Description		Suffix	Description		
2	2"(51) Pipe Size		NH	No Hub (MJ)		
3	3"(76) Pipe Size		Р	Push-On		
4	4"(102) Pipe Size			· · · · · ·		

		_		
	Options			
Suffix	Description			∠ -F Optional Flange with
-F	Flange with Weepholes			Weepholes
-FC	Flange w/Weepholes & Flashing Clamp			
-FS-DS-SS	Stainless Steel Dome Strainer			
-1	Nickle Bronze Top			
-3	Stainless Steel Rim & Grate			
-5	Sediment Bucket			*Add 5/8"(16) for -1 [
-6	Vandal Proof (-1, -3 Only)	1		
-7	Trap Primer Tapping			
-9	Hinged Grate (-1 Only)	-	e Area q. In.	
-21	Secondary Strainer	Standard	With -1/-:	2
-33	Less Grate	Grate	Rim & Gra	
-128	Grate w/2 1/2"(64) Center Opening	31	47	
-150	1/2 Grate			NOTICE
-175	3/4 Grate	1		The information conta
-F4-1	4" Round Nickel Bronze Funnel			full product installatio experience of a traine
-F6-1	6" Round Nickel Bronze Funnel]		thoroughly read all ins
-G-1	4 x 9" Oval Nickel Bronze Funnel			information before be





*Add 5/8"(16) for -1 Nickel Bronze Top or -3 Stainless Steel Top

The information contained herein is not intended to replace the full product installation and safety information available or the experience of a trained product installer. You are required to thoroughly read all installation instructions and product safety information before beginning the installation of this product.

Watts product specifications in U.S. customary units and metric are approximate and are provided for reference only. For precise measurements, please contact Watts Technical Service. Watts reserves the right to change or modify product design, construction, specifications, or materials without prior notice and without incurring any obligation to make such changes and modifications on Watts products previously or subsequently sold.



USA: T: (800) 338-2581 • Watts.com Canada: T: (888) 208-8927 • Watts.ca Latin America: T: (52) 55-4122-0138 • Watts.com