For Residential and Commercial Applications

Contractor _

Representative ____

Approval

Job Location _____

Engineer _

Approval _

LEAD FREE* Series 35 Quick-Connect

Watts Quick-Connect Manifolds are designed and manufactured for many years of trouble free service. Produced of off white Polysulfone, a high performance thermal plastic material, the Watts Quick-Connect design allows for quick and easy connections without the use of installation tools.

Specifications

Manifolds

Connection shall be made using Watts Series 35 Quick-Connect fitting with Integral Collet and O-Ring guide. Fitting shall be able to fully rotate under pressure and allow for easy disconnect and re-use without the use of disconnection tools. Fitting must not disassemble to disconnect.

Approvals

NSF-61, NSF-14, CSA B137.5, ASTM F877, UPC, ASSE 1061

Ratings

100psi @ 180°F (6.8 bar @ 82°C) 250psi @ 75°F (17.3 bar @ 24°C)

Example

3589-1810 35 = Series 35 89 = Type 89 Single Union Body 1810 = 1"CTS x ½"CTS

*The wetted surface of this product contacted by consumable water contains less than one quarter of one percent (0.25%) of lead by weight.

Caution: The polysulfone material used in the Quick-Connect fittings can be compromised by exposure to volatile organic compounds (VOC's) and caustic chemicals. Therefore, **DO NOT** expose this product to any such chemical or foreign substance, which would include exposure to the following products: **Pipe Dopes (thread sealants),** bug sprays, lubricants, cleaners, paints, bleaches, acids, solder fluxes, plastic piping primers and cements, oxidizing agents, alkaline solutions, thinners, fuels, oil based caulks, hydrocarbons, spray foam of foaming agents (insulation).

It is also recommended that all threaded connections be made with $\mathsf{Teflon}^{\otimes}$ tape only.

Watts product specifications in U.S. customary units and metric are approximate and are provided for reference only. For precise measurements, please contact Watts Technical Service. Watts reserves the right to change or modify product design, construction, specifications, or materials without prior notice and without incurring any obligation to make such changes and modifications on Watts products previously or subsequently sold.





Contractor's P.O. No.







3585



Assembly Elements 35 Series Quick-Connect Manifold





Dual Side Style



Installation Dimensions

35 Series Quick-Connect Manifold





Manifolds - Single

Type 89 Manifolds - Single Union Body

MODEL	SIZE & CONNECTION	ITEM \	NEIGHT	
		lbs.	kg.	
Package Type: B	ulk			
3589-1810	1" CTS x ½" CTS	3.4	1.5	
Package Type: P	oly Bag			
3589B-1810	1" CTS x ½" CTS	3.4	1.5	

Type 90 Manifolds - Single Stem Body -Right

MODEL	SIZE & CONNECTION	ITEM \	NEIGHT	
		lbs.	kg.	
Package Type: Bu	ılk			
3590-1810	1" CTS x ½" CTS	3	1.4	
Package Type: Po	oly Bag			
3590B-1810	1" CTS x ½" CTS	3	1.4	

Type 91 Manifolds - Single Stem Body - Left


MODEL	SIZE & CONNECTION	ITEM \	NEIGHT	
		lbs.	kg.	
Package Type: Bu	lk			
3591-1810	1" CTS x ½" CTS	3	1.4	
Package Type: Po	ly Bag			
3591B-1810	1" CTS x ½" CTS	3	1.4	

Type 81 - Manifold Single Side Mounting Kits

SIZE & CONNECTION	ITEM WEIGHT		
	lbs.	kg.	
For 35 Series	1.1	.5	
Bag			
For 35 Series	1.1	.5	
	For 35 Series Bag	lbs. For 35 Series 1.1 Bag	<i>lbs. kg.</i> For 35 Series 1.1 .5 Bag

Manifolds - Dual

Type 83 Manifolds - Dual Union Body



3581

Type 84 Manifolds - Dual Stem Body

MODEL	SIZE & CONNECTION	ITEM \	VEIGHT	
		lbs.	kg.	
Package Type: Bull	(
3584-1810	1" CTS x ½" CTS	6	2.7	
Package Type: Poly	Bag			
3584B-1810	1" CTS x ½" CTS	6	2.7	3584

Manifolds - Dual (cont'd)

Type 80 Manifold Dual Side Mounting Kits

MODEL	SIZE & CONNECTION	ITEM V	VEIGHT	
		lbs.	kg.	
Package Type: Bul	ĸ			
3580-18	For 35 Series	1.5	.69	
Package Type: Poly	/ Bag			
3580B-18	For 35 Series	1.5	.69	

Type 82 Manifold Divider Plugs

kg.
14
14



3586

Type 85 Manifold Return Ends

MODEL	SIZE & CONNECTION	ITEM V	VEIGHT	
		lbs.	kg.	
Package Type: Bulk				n 🗌
3585-18	1" CTS	2.3	1.0	
Package Type: Poly	Bag			H
3585B-18	1" CTS	2.3	1.0	
	ald Label Dista	-		

Type 86 Manifold Label Plates

SIZE & CONNECTION MODEL **ITEM WEIGHT** lhs kn

		100.	ng.	
Package Type:	Bulk			
3586-Red	Red - For 35 and Metric	0.2	.09	
Package Type:	Poly Bag			
3586B-Red	Red - For 35 and Metric	0.2	.09	

Type 87 Manifold Label Plates

MODEL	SIZE & CONNECTION	ITEM	WEIGHT		
		lbs.	kg.		
Package Type	: Bulk				
3587-Blue	Blue - For 35 and Metric	0.2	.09		
Package Type	: Poly Bag				
3587B-Blue	Blue - For 35 and Metric	0.2	.09		3587

Type 88 Manifold Valve Repair Kits

MODEL	SIZE & CONNECTION	ITEM WEIGHT		
		lbs.	kg.	
4Package Type: E	Bulk			
3588-10	1⁄2" Spool	0.7	.32	
Package Type: Po	oly Bag			
3588B-10	1⁄2" Spool	0.7	.32	

Type 80-MT Manifold Tool

MODEL	SIZE & CONNECTION	ITEM \	WEIGHT	
		lbs.	kg.	
4Package Typ	e: Poly Bag			
3580-MT	Easy Removal of Outlets	.12	.05	3580-MT



3588



A Watts Water Technologies Company

USA: 815 Chestnut St., No. Andover, MA 01845-6098; www.watts.com Canada: 5435 North Service Rd., Burlington, ONT. L7L 5H7; www.wattscanada.ca

9001-2000 CERTIFIED