

FloProTMMD

Gas Flow and Pressure Measurement System

Take the guesswork out of YOUR work

- Displays Real Time Data, Gas Pressure, Flow & BTUs
- No Need to Do The Math-It Does All Calculations
- Replaces The Need for Flowmeter, Manometer & Calculator
- Compatible with Natural Gas (NG) & Propane (LPG)




Go.dormont.com/flopromd

Dormont[®]
A WATTS Brand



Connect with Confidence®



Pressure Reading in "w.c.



Flow readings in Cubic Feet per Hour (CFH)



Heat Energy Capacity in BTU/Hr

User Friendly Features

- Ideal for servicing, diagnostics, and routine maintenance
- Easy installation with common, off-the-shelf tools

Verification and Data Collection

- Gas flow, capacity and pressure data are easily displayed and uploaded to FloPro™-MD app
- FloPro-MD app is easily downloadable to iOS or Android devices
- Proper installation or repair can be verified via a .csv data file that can be imported into excel and a report generated for your customer

Applications

Commercial Kitchen appliances, Boilers, Tankless Water Heaters, Furnaces, Dryers, Kitchen Appliances, standby power generators. Light commercial boilers and water heaters, rooftop units

Operating Range

- Natural Gas (NG) equipment: 15,000 to 325,000 BTU/Hr
- Propane (LPG) equipment: 15,000 to 500,000 BTU/Hr

Benefits

- Free app available from the Google Play™ or Apple® App Store® online stores.
- Compatible with Natural Gas (NG) and Propane (LPG) commercial kitchen appliances and equipment at specified flow rates
- Easily view real time and recorded data via user-friendly app
- Automatically converts gas flow rate (CFH) to capacity (BTU/hr)

Features and Functions

Measures/Displays the Following:

- Gas Flow Rate in Cubic Feet/Hour (CFH)
- Gas Flow Capacity in BTU/Hour
- Gas pressure measurement in inches water column (" w.c.)
- Corrosion-resistant aluminum construction with black finish
- Annunciator LEDs communicate device status
- Standard 3/4" Female NPT connections

Interface & Communications: Android™ and iOS™ mobile operating systems via Bluetooth Low Energy

ORDERING CODE	DESCRIPTION	FLOPRO-MD WITH POWER SUPPLIES	PACKAGING
68004852	Dormont FloPro-MD 3/4" FNPT Standard Hard Case KIT	MODEL FPMD75FF 3/4" FNPT (IN) x 3/4" FNPT (OUT) AC-DC Power Supply Battery Pack Power Supply w/Clip 4-AA Batteries	Hard Case

Google Play and Android are trademarks of Google LLC. Apple and App Store are trademarks of Apple Inc. iOS is a trademark of Cisco.

