

Engineering Specification

Job Name _____

Contractor _____

Job Location _____

Approval _____

Engineer _____

Contractor's P.O. No. _____

Approval _____

Representative _____

CO-200-XHR5

Floor Cleanout with Heavy Duty Round Top

Specification

Watts CO-200-XHR5 epoxy coated cast iron floor cleanout with 5-1/8" (130) round adjustable heavy duty nickel bronze (standard) top, and no hub (MJ) connection.

Call customer service if you need assistance with technical details.

Pipe Size	
Suffix	Description
2	2"(51) Pipe Size
3	3"(76) Pipe Size
4	4"(102) Pipe Size

Outlet Type	
Suffix	Description
NH	No Hub (MJ)
P	Push On

Cover	
Suffix	Description
XHR5-1	5"(127) Dia. Nickel Bronze
XHR5-4	5"(127) Dia. Ductile Iron

Options	
Suffix	Description
-6	Vandal Proof
-13	Galvanized Body
-34G	ABS Plug with Neoprene Gasket
-113M	Special Epoxy from 3M Range

Optional Body Material	
Suffix	Description
-60	PVC Body w/Socket Outlet
-61	ABS Body w.Socket Outlet

Suffix	Load Rating
XHR5-1	*XHD
XHR5-4	*XHD




Chart A			
Pipe Size	Std. No Hub	P Push On	60/61 PVC/ABS
2"(51)	3"(76)	4"(102)	4"(102)
3"(76)	3"(76)	4"(102)	3 3/4"(95)
4"(102)	3"(76)	4"(102)	3 3/4"(95)

NOTICE

The load classifications are in accordance with the American National Standards A112.21.1M ASME Ratings are as follows:
XHD - Safe Live Load 7500-10,000 lbs. (3375-4500 kg)
These categories are given as a guide only.
Please consult factory.

NOTICE

The information contained herein is not intended to replace the full product installation and safety information available or the experience of a trained product installer. You are required to thoroughly read all installation instructions and product safety information before beginning the installation of this product.

Watts product specifications in U.S. customary units and metric are approximate and are provided for reference only. For precise measurements, please contact Watts Technical Service. Watts reserves the right to change or modify product design, construction, specifications, or materials without prior notice and without incurring any obligation to make such changes and modifications on Watts products previously or subsequently sold.



USA: T: (800) 338-2581 • Watts.com

Canada: T: (888) 208-8927 • Watts.ca

Latin America: T: (52) 55-4122-0138 • Watts.com

ES-WD-CO-200-XHR5-CAN 2518

© 2025 Watts

