

Engineering Specification

Job Name _____

Contractor _____

Job Location _____

Approval _____

Engineer _____

Contractor's P.O. No. _____

Approval _____

Representative _____

LEAD FREE*

Series

LFFBV-3-PRxPEX

2-Piece, Full Port, Lead Free* Brass Ball Valves with Integral Press x PEX End Connections

Designed for use in ProPress® Piping Systems

Sizes: 1/2" – 1"

Series LFFBV-3-PRxPEX are two-piece, lead free, full port, ball valves with press x PEX connections that are designed for use in plumbing, heating, and potable water applications. It features a lead-free brass body, adjustable packing gland, and bottom-loaded blowout proof stem. These valves facilitate easy transition from copper tubing to PEX tubing. It has integral ASTM-B88 compliant press end connections on one end with ASTM F-1087 compliant PEX connections on the other. The LFFBV-3-PRxPEX is rated to 160 psi at 73°F (11.0 bar at 22.8°C)

The Series LFFBV-3-PRxPEX features Lead Free* construction to comply with low lead installation requirements.

Features

- Lead Free* brass body
- Tested and Certified to NSF/ANSI 61 Annex G 1/2" – 1"
- Designed for types K, L, and M hard copper tubing 1/2" - 1" and soft copper tubing 1/2" – 1"
- Press X PEX connections
- Press connection rated to 250psi CWP up to 250°F (13.8 bar to 121°C)
- PEX connection is rated for 160psi at 73°F
- Bottom loaded, blowout proof stem
- PTFE seats, seals and thrust washers

Applications

- Lead free and potable water installations
- Commercial, Residential, Industrial plumbing
- Hydronics

ProPress® is a registered trademark of Viega N.A.



LFFBV-3-PRxPEX

Specification

Approved valve to be 2-piece, full port, forged body of Lead Free* brass. Certified to NSF/ANSI 61 Annex G by UL for potable water applications. Lead Free* brass ball and PTFE seats, seal, and thrust washer required. Press fitting rated to 250psi CWP up to 250°F (13.8 bar to 121°C) and press ends must comply to ASTM-B88. PEX fitting is rated for 160psi at 73°F. The valve shall be constructed using Lead Free* brass. Lead Free* brass ball valves shall comply with state codes and standards, where applicable, requiring reduced lead content. Valve shall be a Watts Series LFFBV-3-PRxPEX.

Approvals

NSF/ANSI 372 - Lead content

NSF/ANSI 61 - Health effects



NOTICE


The information contained herein is not intended to replace the full product installation and safety information available or the experience of a trained product installer. You are required to thoroughly read all installation instructions and product safety information before beginning the installation of this product.

***The wetted surface of this product contacted by consumable water contains less than 0.25% of lead by weight.**

Watts product specifications in U.S. customary units and metric are approximate and are provided for reference only. For precise measurements, please contact Watts Technical Service. Watts reserves the right to change or modify product design, construction, specifications, or materials without prior notice and without incurring any obligation to make such changes and modifications on Watts products previously or subsequently sold.


Small Size Valves 1/2" to 1"

Materials



Call customer service if you need assistance with technical details.

N POS	PART NAME	MATERIAL	N PCS
1	Body	Brass	1
2	Stem	Brass	1
3	Nut	Steel	1
4	Packing Nut	Brass	1
5	Packing Gland	PTFE	2
6	Thrust Washer	PTFE	1
7	Ball	Brass	1
8	Ball Seat	PTFE	2
9	Adapter	Brass	1
10	O-Ring	EPDM	2
11	Handle	Steel	1



Dimensions-Weights

ORDERING CODE	SIZE		DIMENSIONS											WEIGHT	
	PFT	ØP	Q		ØH		L		H		R		Lbs	kgs	
	in	mm	in	mm	in	mm	in	mm	in	mm	in	mm			
88009055	1/2	9/16	14.5	1 1/8	28.0	1 3/16	30.0	3 1/8	79.0	1 11/16	42.2	3 3/4	95.0	0.46	0.21
88009056	3/4	3/4	19.0	1 3/16	30.0	1 1/2	37.5	3 3/8	86.2	1 15/16	48.7	3 3/4	95.0	0.67	0.31
88009057	1	1	25.0	1 3/16	30.0	1 7/8	47.0	3 3/16	97.5	2 5/16	58.5	4 15/16	110.0	1.09	0.49

ACCESSORIES					
Ordering Code	Stem Extension Description	Ordering Code	Locking Handle Description	Ordering Code	Replacement Handle Description
88005505	1/2" - 3/4" HK SXI-Press-M2	0789520	Locking Handle KIT For 1/2" LFFBV-3-PRESS ball valves	0789527	Replacement Handle KIT For 1/2" - 3/4" LFFBV-3-PRESS ball valves
88005505	1/2" - 3/4" HK SXI-Press-M2	0789525	Locking Handle KIT For 3/4" LFFBV-3-PRESS ball valves	0789527	Replacement Handle KIT For 1/2" - 3/4" LFFBV-3-PRESS ball valves
88005507	1" HK SXI-Press-M2	0789521	Locking Handle KIT 1" LFFBV-3-PRESS ball valves	0789528	Replacement Handle KIT 1" LFFBV-3-PRESS ball valves

