Engineering Specification

Job Name ————	Contractor —
oob (Name	Oditidotoi
Job Location ————————————————————————————————————	Approval ————————————————————————————————————
Engineer ————	Contractor's P.O. No.
Approval ————	Representative ————

Hand Showers

Part Nos. 141 827N, 141 827WS* 141 879N, 141 879WS*

Specifications

Description Standard Hand Shower with 24" Glide Rail, Type 8 (*WaterSense® Type 8WS), or 30"


Glide Rail Type N (*WaterSense Type NWS)

Finish See drawing and table

Agency/Spec Approval ... IAPMO cUPC

ASME A112.18.1 CSA B125.1

*WaterSense



Maximum Flow 2.5 gpm (9.5L/min) MAX at 80 psi

1.8 gpm (6.8L/min) MAX at 80 psi (*WaterSense)


Minimum Flow 1.8 gpm (6.8L/min) MIN at 45psi

1.4 gpm (5.1L/min) MIN at 45psi (*WaterSense)

Shipping Weight 141 827N, 141 827WS: 2.6 lb (1.18 kg)

141 879N, 141 879WS: 3.05 lb (1.38 kg)





Call customer support if you need assistance with technical details.

Part Nos. 141 827N, 141 827WS*

ITEM	MODEL	DESCRIPTION	QTY
1	141161AN	Hand Sprayer, Push Button, CP Plastic, 2.50 GPM	1
2	141161BN	Hose, Stainless Steel, 60 Inches	1
**3	141163DN	Glide Rail, 24", SS, Adjustable Cradle	1
4	141320N	Supply Elbow CP Plastic Cover, Brass ½" NPT	1
*	141161AWS	Hand Sprayer, Push Button, CP Plastic, 1.80 GPM, WS	1

Part Nos. 141 879N, 141 879WS*

		<u> </u>	
ITEM	MODEL	DESCRIPTION	QTY
1	141161AN	Hand Sprayer, Push Button, CP Plastic, 2.50 GPM	1
2	141161BN	Hose, Stainless Steel, 60 Inches	1
**3	141731N	Glide Rail, 30", SS, Adjustable Cradle	1
4	141320N	Supply Elbow CP Plastic Cover, Brass ½" NPT	1
*	141161AWS	Hand Sprayer, Push Button, CP Plastic, 1.80 GPM, WS	1

^{**}Warning: Never use this product as a grab bar or for support. Personal injury may result if this product is misused.

Powers product specifications in U.S. customary units and metric are approximate and are provided for reference only. For precise measurements, please contact Powers Technical Service. Powers reserves the right to change or modify product design, construction, specifications, or materials without prior notice and without incurring any obligation to make such changes and modifications on Powers products previously or subsequently sold.

A WATTS Brand

USA: Tel: (888) 432-8932 • PowersControls.com

Canada: Tel: (888) 208-8927 • PowersControls.ca

Latin America: Tel: (52) 55-4122-0138 • PowersControls.com

