For Fire Protection Applications

Job Name	Contractor
Job Location	Approval
Engineer	Contractor's P.O. No.
Approval	Representative

Series 411

Swing Check Valve with Resilient Disc Seat

Sizes: 2" - 10" (50mm - 250mm)

Series 411 Swing Check Valves are UL Listed and FM approved in sizes 2" – 10" (50 – 250mm). Valves feature a full port, flanged cast iron body with a Buna-N resilient disc seat designed for use on fire mains and sprinkler systems. The valve operates automatically by opening on a hinge arm with flow and closing when flow stops or is reversed.

Features

- ASTM A126 Class B Cast Iron Body
- Buna-N disc ring
- Complies with ANSI B16.10 and ANSI B16.1
- Full Port Design
- Eye bolt ring 4" 10" (100-250mm)
- Pressure rated 175psi (12.1 bar) CWP
- Replaceable seat and disc repairable in-line.

Specifications

Swing check valve to be manufactured using ASTM A126 Class B Cast Iron with Buna-N resilient disc seat and comply with MSS-SP-71. Valve to be pressure rated to 175psi (12.1 bar) CWP with flanged ends that comply with ANSI B16.10 and ANSI B16.1 Class 125 standards. Series 411 shall comply with state codes and standards, where applicable, requiring reduced lead content. Valve shall have a full port design, and be in-line repairable. Valve to be Watts Series 411 Swing Check Valve.

Standards

Face-to-face: The dimensions of the valves comply with the American Standard for face-to-face dimensions (ANSI B16.10) for Class 125 cast iron flanged valves.

End Flanges: The dimensions and drilling of end flanges conform to the American cast iron flange standard, Class 125 (ANSI B16.1). The flanges are flat faced with smooth finish.



411

Approvals

2"-10" (50mm - 250mm)






Valves comply with MSS-SP-71 Standards




Parts - Materials


NO.	PARTS	MATERIAL	ASTM DESIGNATION				
1	Body	Cast Iron	A126 CL. B				
2	Seat Ring	Cast Bronze	B62				
3	Disc	Ductile Iron	A536 60-40-18				
4	Disc Ring	Buna-N	D-2000				
5	Hinge	Ductile Iron	A536 60-40-18				
6	Washer	Cast Bronze	B62				
7	Hinge Bolt	Brass	B16				
8	0-Ring	Buna-N	D-2000				
9	Hinge Pin	SS 304	A276				
_10	Bushing	Brass Tube	B16				
11	Plug	Bronze	B62				
12	Nut	Steel	A307				
13	Gasket	Compressed Fiber	_				
_14	Bolt	Steel	A307				
15	Cover	Cast Iron	A126 CL. B				
_16	Eye Bolt	Steel	A307				



Pressure - Temperature

Maximum Pressure: 175psi (12.1 bar) CWP Maximum Temperature: 180°F (82°C)





Dimensions - Weights

SI	IZE	DIMENSIONS										WEI	GHT			
			L	[)	С		bolt holes size bolt hole		bolt holes Qty.	Т		Н			
in.	mm	in.	mm	in.	mm	in.	mm	in.	mm		in.	mm	in.	mm	lbs.	Kgs.
2	50	8	203	6	152	43/4	121	3/4	19	4	5/8	16	47/16	112	28	13
21/2	65	81/2	216	7	180	51/2	140	3/4	19	4	11/16	18	43/4	120	37	17
3	75	91/2	241	71/2	191	6	152	3/4	19	4	3/4	19	51/2	140	47	22
4	100	11½	292	9	229	71/2	191	3/4	19	8	¹⁵ / ₁₆	24	65/16	161	82	37
6	150	14	356	11	279	91/2	241	7/8	22	8	1	25	87/16	214	157	71
8	200	19½	495	13½	343	11¾	299	7/8	22	8	11//8	29	101/16	268	303	138
10	250	241/2	622	16	406	141/4	362	1	25	12	13/16	30	137/16	342	471	214

It is illegal to use this product in any plumbing system providing water for human consumption, such as drinking or dishwashing, in the United States. Before installing standard material product, consult your local water authority, building and plumbing codes.





USA: Tel: (978) 688-1811 • Fax: (978) 794-1848 • www.watts.com **Canada:** Tel: (905) 332-4090 • Fax: (905) 332-7068 • www.watts.ca