

## Engineering Specification

Job Name \_\_\_\_\_

Contractor \_\_\_\_\_

Job Location \_\_\_\_\_

Approval \_\_\_\_\_

Engineer \_\_\_\_\_

Contractor's P.O. No. \_\_\_\_\_

Approval \_\_\_\_\_

Representative \_\_\_\_\_

# CA-550

## Service Sink Carrier

### Specification

Watts CA-550 floor mounted service sink carrier with heavy gauge steel uprights with integral welded feet, epoxy coated cast iron fitting, no hub waste and vent connections (specify size), epoxy coated cast iron faceplate, adjustable ABS nipple with integral test cap and neoprene gasket, plated hardware and chrome cap nuts.

Call customer service if you need assistance with technical details.

| Model No.   | Min. Pipe Space to Finished Wall | Front of Faceplate to Back of Fitting | Top of Fitting to Center of Coupling | Center of Coupling to Bottom of Fitting | Waste/Vent                  |
|-------------|----------------------------------|---------------------------------------|--------------------------------------|-----------------------------------------|-----------------------------|
| CA-550-3    | 5 5/8"(143)                      | 5 1/4"(133)                           | 3 3/4"(95)                           | 14 1/2"(368)                            | 3"(76) Waste, 2"(51) Vent   |
| CA-550-4-V2 | 7 1/2"(191)                      | 6 7/8"(175)                           | 5 1/2"(140)                          | 20"(508)                                | 4"(102) Waste, 2"(51) Vent  |
| CA-550-4-V4 | 7 1/2"(191)                      | 6 7/8"(175)                           | 4 1/2"(114)                          | 20"(508)                                | 4"(102) Waste, 4"(102) Vent |




### NOTICE

Anchor Legs to concrete floor with minimum 1/2"(13) lag bolts (by others).

### NOTICE

The information contained herein is not intended to replace the full product installation and safety information available or the experience of a trained product installer. You are required to thoroughly read all installation instructions and product safety information before beginning the installation of this product.



Watts product specifications in U.S. customary units and metric are approximate and are provided for reference only. For precise measurements, please contact Watts Technical Service. Watts reserves the right to change or modify product design, construction, specifications, or materials without prior notice and without incurring any obligation to make such changes and modifications on Watts products previously or subsequently sold.



USA: T: (800) 338-2581 • Watts.com

Canada: T: (888) 208-8927 • Watts.ca

Latin America: T: (52) 55-4122-0138 • Watts.com

ES-WD-CA-550 2507

© 2025 Watts

