ES-WD-FD-100-AS

Engineering Specification

Job Name	Contractor
Job Location	Approval
Engineer	Contractor's P.O. No.
Approval	Representative

FD-100-AS Floor Drain with Angle Strainer Specification

Watts FD-100-AS epoxy coated cast iron floor drain with anchor flange, reversible clamping collar with primary and secondary weepholes, adjustable nickel bronze angle strainer, and no hub (standard) outlet

Call customer service if you need assistance with technical details.

Pipe Sizing			
Suffix	Description		
2	2"(51) Pipe Size		
3	3"(76) Pipe Size		
4	4 4"(102) Pipe Size		
6	6"(152) Pipe Size (NH Only)		
	Outlet Type		
Suffix	Description		
NH	No Hub (MJ)		
P	Push On		
T	Threaded Outlet		

Optional Body Material		
Suffix	Description	
-60	PVC Body w/Socket Outlet	
-61	ABS Body w/Socket Outlet	

Inside Caulk

χ

Options		
Suffix	Description	
-5	Sediment Bucket	
-6	Vandal Proof	
-7	Trap Primer Tapping	Γ
-8	Backwater Valve	
	(2, 3, 4" Only)	
-13	Galvanized Body	
-15	Strainer Extension (DD-50)	
-S0	Side Outlet	





Chart B					
Pipe Size	Std. No Hub	P Push On	T Female Thread	X Inside Caulk	60/61 PVC/ABS
2"(51)	3 5/8"(92)	4 1/4"(108)	4 1/4"(108)	4 1/2"(114)	4"(102)
3"(76)	3 5/8"(92)	4 1/4"(108)	4 1/4"(108)	4 1/2"(114)	4"(102)
4"(102)	3 5/8"(92)	4 1/4"(108)	4 1/4"(108)	4 1/2"(114)	4"(102)
6"(152)	3 1/2"(89)	-	-	-	-

NOTICE

The load classifications are in accordance with the American National Standards ASME A112.36.2M-91(R2012) ASME Ratings are as follows:

MD - Safe Live Load 2000-4999 lbs. (900-2250 kg) The above categories are given as a guide only. Please consult factory.

Watts product specifications in U.S. customary units and metric are approximate and are provided for reference only. For precise measurements, please contact Watts Technical Service. Watts reserves the right to change or modify product design, construction, specifications, or materials without prior notice and without incurring any obligation to make such changes and modifications on Watts products previously or subsequently sold.



USA: T: (800) 338-2581 • Watts.com Canada: T: (888) 208-8927 • Watts.ca Latin America: T: (52) 55-4122-0138 • Watts.com

The information contained herein is not intended to replace the

full product installation and safety information available or the experience of a trained product installer. You are required to

thoroughly read all installation instructions and product safety information before beginning the installation of this product.

NOTICE