

Engineering Specification

Job Name _____

Contractor _____

Job Location _____

Approval _____

Engineer _____

Contractor's P.O. No. _____

Approval _____

Representative _____

Tag _____

FD-1200-L

Floor Drain with Square Heavy Duty Stainless Steel Strainer

Specification

Watts FD-1200-L on-grade epoxy coated cast iron floor drain with anchor flange, weepholes, adjustable heavy duty square heel proof stainless steel strainer, and no hub (standard) outlet.


Pipe Sizing		
Suffix	Description	
2	2"(51) Pipe Size	<input type="checkbox"/>
3	3"(76) Pipe Size	<input type="checkbox"/>
4	4"(102) Pipe Size	<input type="checkbox"/>

Outlet Type		
Suffix	Description	
NH	No Hub (MJ)	<input type="checkbox"/>
P	Push On	<input type="checkbox"/>
X	Inside Caulk	<input type="checkbox"/>

Strainer		
Suffix	Description	
L5	5" x 5"(127x127) Stainless Steel	<input type="checkbox"/>
L6	6" x 6"(152x152) Stainless Steel	<input type="checkbox"/>
L8	8" x 8"(203x203) Stainless Steel	<input type="checkbox"/>

Optional Body Material		
Suffix	Description	
-60	PVC Body w/Socket Outlet	<input type="checkbox"/>
-61	ABS Body w/Socket Outlet	<input type="checkbox"/>

Options		
Suffix	Description	
-5	Sediment Bucket	<input type="checkbox"/>
-6	Vandal Proof	<input type="checkbox"/>
-7	Trap Primer Tapping	<input type="checkbox"/>
-8	Backwater Valve	<input type="checkbox"/>
-13	Galvanized Body	<input type="checkbox"/>
-15	Strainer Extension (DD-50)	<input type="checkbox"/>
-28	304SS Body & Collar	<input type="checkbox"/>
-F4-50	4" Round Cast Iron Funnel	<input type="checkbox"/>
-F4-1	4" Round Nickel Bronze Funnel	<input type="checkbox"/>
-F4-3	4" Round SS Funnel	<input type="checkbox"/>
-F6-1	6" Round Nickel Bronze Funnel	<input type="checkbox"/>
-G-50	4x9" Oval Cast Iron Funnel	<input type="checkbox"/>
-G-1	4x9" Oval Nickel Bronze Funnel	<input type="checkbox"/>
-G-3	4x9" Oval SS Funnel	<input type="checkbox"/>



Strainer Size				
Strainer Size	Min.	Max.	Load Rating	Free Area
5"x5"(127x127)	1 1/2"(38)	2 5/16"(59)	XHD	9
6"x6"(152x152)	1 1/2"(38)	2 5/16"(59)	XHD	12
8"x8"(203x203)	1 1/2"(38)	2 3/4"(70)	XHD	26

Chart A				
Pipe Size	Std. No Hub	P Push On	60/61 PVC/ABS	
2"(51)	4 1/2"(114)	5 1/2"(140)	4"(102)	
3"(76)	4 1/2"(114)	5 1/2"(140)	4"(102)	
4"(102)	4 3/4"(121)	5 1/2"(140)	4"(102)	

NOTICE

The load classifications are in accordance with the American National Standard ASME A112.21.1M ASME Ratings are as follows:
XHD - Safe Live Load 7500-10000 lbs.(3375-4500 kg)
The above categories are given as a guide only. Please consult factory.

Watts product specifications in U.S. customary units and metric are approximate and are provided for reference only. For precise measurements, please contact Watts Technical Service. Watts reserves the right to change or modify product design, construction, specifications, or materials without prior notice and without incurring any obligation to make such changes and modifications on Watts products previously or subsequently sold.

NOTICE

The information contained herein is not intended to replace the full product installation and safety information available or the experience of a trained product installer. You are required to thoroughly read all installation instructions and product safety information before beginning the installation of this product.



USA: T: (800) 338-2581 • Watts.com

Canada: T: (888) 208-8927 • Watts.ca

Latin America: T: (52) 55-4122-0138 • Watts.com

ES-WD-FD-1200-L 2239

© 2022 Watts