

Engineering Specification


Job Name _____
 Job Location _____
 Engineer _____
 Approval _____

Contractor _____
 Approval _____
 Contractor's P.O. No. _____
 Representative _____

FD-200-H Floor Drain with Elastomeric Flange Specification

Watts FD-200-H on-grade epoxy coated cast iron floor drain with anchor flange, weepholes, adjustable heel proof nickel bronze strainer with wide flange, and no hub (standard) outlet. FD-200-H drains are specified for installation with rubberized sheet flooring. The wide flange provides a surface for the flooring to be secured and waterproofed at the drain.

Call customer service if you need assistance with technical details.



| Pipe Sizing | | |
|-------------|-------------------|--------------------------|
| Suffix | Description | |
| 2 | 2"(51) Pipe Size | <input type="checkbox"/> |
| 3 | 3"(76) Pipe Size | <input type="checkbox"/> |
| 4 | 4"(102) Pipe Size | <input type="checkbox"/> |

| Outlet Type | | |
|-------------|--------------|--------------------------|
| Suffix | Description | |
| NH | No Hub (MJ) | <input type="checkbox"/> |
| P | Push On | <input type="checkbox"/> |
| X | Inside Caulk | <input type="checkbox"/> |

| Optional Body Material | | |
|------------------------|--------------------------|--------------------------|
| Suffix | Description | |
| -60 | PVC Body w/Socket Outlet | <input type="checkbox"/> |
| -61 | ABS Body w/Socket Outlet | <input type="checkbox"/> |

| Options | | |
|---------|-----------------------------------|--------------------------|
| Suffix | Description | |
| -5 | Sediment Bucket | <input type="checkbox"/> |
| -6 | Vandal Proof | <input type="checkbox"/> |
| -7 | Trap Primer Tapping | <input type="checkbox"/> |
| -8 | Backwater Valve (2, 3, 4" Only) | <input type="checkbox"/> |
| -13 | Galvanized Body | <input type="checkbox"/> |
| -15 | Strainer Extension (DD-50) | <input type="checkbox"/> |
| -F4-50 | 4" Round Cast Iron Funnel | <input type="checkbox"/> |
| -F4-1 | 4" Round Nickel Bronze Funnel | <input type="checkbox"/> |
| -F6-1 | 6" Round Nickel Bronze Funnel | <input type="checkbox"/> |
| -G-50 | 4" x 9" Oval Cast Iron Funnel | <input type="checkbox"/> |
| -G-1 | 4" x 9" Oval Nickel Bronze Funnel | <input type="checkbox"/> |

Chart B

| Pipe Size | No Hub | P Push On | 60/61 PVC/ABS |
|-----------|-------------|-------------|---------------|
| 2"(51) | 4 1/2"(114) | 5 1/2"(140) | 4"(102) |
| 3"(76) | 4 1/2"(114) | 5 1/2"(140) | 4"(102) |
| 4"(102) | 4 3/4"(121) | 5 1/2"(140) | 4"(102) |

Strainer Size

| Str. Dia. | Min. | Max. | Load Rating | Free Area Sq. In. |
|-----------|--------|------------|-------------|-------------------|
| 6"(152) | 1"(25) | 2 1/4"(57) | MD | 9 |

NOTICE

The information contained herein is not intended to replace the full product installation and safety information available or the experience of a trained product installer. You are required to thoroughly read all installation instructions and product safety information before beginning the installation of this product.

NOTICE

The load classifications are in accordance with the American National Standard ASME A112.21.1M ASME Ratings are as follows:
 MD - Safe Live Load 2000-4999 lbs. (900-2250 kg)
 The above categories are given as a guide only. Please consult factory.

Watts product specifications in U.S. customary units and metric are approximate and are provided for reference only. For precise measurements, please contact Watts Technical Service. Watts reserves the right to change or modify product design, construction, specifications, or materials without prior notice and without incurring any obligation to make such changes and modifications on Watts products previously or subsequently sold.

