

For PEX Piping Systems

Job Name _____

Contractor _____

Job Location _____

Approval _____

Engineer _____

Contractor's P.O. No. _____

Approval _____

Representative _____

Series FBV-PEX-M1

2-Piece, Full Port, Brass Ball Valves with PEX Ends

Sizes: 1/2" - 1"

Series FBV-PEX-M1 2-Piece, Full Port, Brass Ball Valve with PEX Ends are designed for use in PEX piping systems. Forged brass body and adapter manufactured per the ASTM F1807 standard. They feature brass PEX end tailpieces designed for easy crimping into a PEX piping system.

Features

- 2-piece, full port design
- UNS C37700 Forged brass body
- PEX end designed to ASTM F1807
- Valve rated to 400 WOG
- Crimp connection rated to 160psi at 73°F (23°C)
- Designed specifically for use in PEX piping systems



Specification

Approved valve to be 2-piece, full port, UNS C37700 forged brass body, chrome plated brass ball, virgin PTFE seats and stem packing, and NBR stem O-ring. Ball valve rated to 400 WOG and PEX end must comply with ASTM F1807 standard. Crimp joint rated at 160psi at 73°F (23°C). Valve shall be a Watts Series FBV-PEX-M1.

Pressure – Temperature

Ball Valve Rating: 400 WOG

Crimp Connection Rating: 160psi at 73°F (23°C) (refer to PEX piping manufacturer's guidelines)




Materials

ITEM	QTY	DESCRIPTION	MATERIAL
1	1	Handle	Zinc-plated Steel w/Vinyl Handle Insulator
2	1	Stem Packing	PTFE
3	1	Stem	Forged brass
4	1	Handle Nut	Brass
5	1	Body	Forged brass, UNS C37700
6	2	Stem O-Ring	NBR
7	1	Ball	Chrome-Plated Forged brass
8	2	Seat	PTFE
9	1	Adapter	Forged brass, UNS C37700

NOTICE

The information contained herein is not intended to replace the full product installation and safety information available or the experience of a trained product installer. You are required to thoroughly read all installation instructions and product safety information before beginning the installation of this product.

Dimensions – Weights



Dimensions – Weights

SIZE		DIMENSIONS						WEIGHT	
		H		L		L1			
<i>in.</i>	<i>in.</i>	<i>mm</i>	<i>in.</i>	<i>mm</i>	<i>in.</i>	<i>mm</i>	<i>lbs.</i>	<i>kgs</i>	
1/2	1 1/2	38	2 1/2	64	3 3/8	81	0.3	0.14	
3/4	1 5/8	40	2 5/8	67	3 3/8	81	0.34	0.15	
1	2	50	3 1/4	82	4 1/8	106	0.61	0.28	

