

Engineering Specification

Job Name _____
 Job Location _____
 Engineer _____
 Approval _____

Contractor _____
 Approval _____
 Contractor's P.O. No. _____
 Representative _____

OI-K Large Capacity Oil Interceptor Specification


Watts OI-K Series recessed or floor mounted epoxy coated steel oil interceptor with gasketed epoxy coated steel skid-proof cover secured with hex head center bolt(s), double wall deep seal trap 2" IPS oil draw-off connection and 2" no hub dual vent connections, internal stainless steel flow control plate, and no hub (standard) inlet and outlet connections.



Call customer service if you need assistance with technical details.

Flow Rate		Options	
Suffix	Description	Suffix	Description
75	75 GPM	-B	Sediment Bucket
100	100 GPM	-E	Extension
150	150 GPM	-FC	Flange & Clamp Device
200	200 GPM	-HD	Heavy Duty (10,000 lb.) Traffic Cover*
250	250 GPM	-O	Inlet & Outlet (other than Standard Size)
300	300 GPM	-SS	Stainless Steel
400	400 GPM	-THD	Threaded Connections
500	500 GPM		

*HD Option Requires Minimum 3" Extension



Model No.	Flow Rate GPM	A Inlet/Outlet	C Top to Center	D Length	E Width	F Height	G Base to Center	H	J	K
OI-75-K	75	4"(102)	4-1/2"(114)	39-3/4"(1010)	30-3/4"(781)	23"(584)	9-1/2"(241)	21-3/4"(552)	8"(203)	7"(178)
OI-100-K	100	4"(102)	4-1/2"(114)	39-3/4"(1010)	30-3/4"(781)	33"(838)	19-1/2"(495)	21-3/4"(552)	8"(203)	7"(178)
OI-150-K	150	4"(102)	4-1/2"(114)	39-3/4"(1010)	30-3/4"(781)	43"(1092)	29-1/2"(749)	21-3/4"(552)	8"(203)	7"(178)
OI-200-K	200	4"(102)	6-1/2"(165)	52"(1321)	34"(864)	43"(1092)	18-1/2"(470)	41"(1041)	8"(203)	7"(178)
OI-250-K	250	4"(102)	6-1/2"(165)	52"(1321)	34"(864)	46"(1168)	30-1/2"(775)	45"(1143)	8"(203)	7"(178)
OI-300-K	300	6"(152)	10"(254)	76"(1930)	48"(1219)	48"(1219)	28"(711)	48"(1219)	12"(305)	10"(254)
OI-400-K	400	6"(152)	10"(254)	83"(2108)	55"(1397)	52"(1321)	32"(813)	52"(1321)	12"(305)	10"(254)
OI-500-K	500	6"(152)	10"(254)	91"(2311)	60"(1524)	63"(1600)	43"(1092)	63"(1600)	12"(305)	10"(254)

NOTICE

The information contained herein is not intended to replace the full product installation and safety information available or the experience of a trained product installer. You are required to thoroughly read all installation instructions and product safety information before beginning the installation of this product.

Watts product specifications in U.S. customary units and metric are approximate and are provided for reference only. For precise measurements, please contact Watts Technical Service. Watts reserves the right to change or modify product design, construction, specifications, or materials without prior notice and without incurring any obligation to make such changes and modifications on Watts products previously or subsequently sold.



USA: T: (800) 338-2581 • Watts.com
Canada: T: (888) 208-8927 • Watts.ca
Latin America: T: (52) 55-4122-0138 • Watts.com

