

## Engineering Specification

Job Name \_\_\_\_\_

Contractor \_\_\_\_\_

Job Location \_\_\_\_\_

Approval \_\_\_\_\_

Engineer \_\_\_\_\_

Contractor's P.O. No. \_\_\_\_\_

Approval \_\_\_\_\_

Representative \_\_\_\_\_

# SS Series

## Stainless Steel Shock Arrestors

### Specification

Watts SS Series pre-charged all stainless steel shock arrestor with stainless steel bellows, and male IPS threaded connection.

### Operating Pressure:

Designed to operate on all domestic and commercial lines up to 150 psi working pressure, 250 psi static pressure.

### Temperature Range:

33°F to 300°F (1°C to 149°C)

### Installation

May be installed in new or existing plumbing systems with a standard pipe tee vertically, horizontally, or at any angle. SS Series are factory air charged and permanently sealed. They may be installed in concealed locations without access panels and are not rechargeable in the field.


Call customer service if you need assistance with technical details.

| CONNECTION SIZE |           |                          |      |
|-----------------|-----------|--------------------------|------|
| MODEL NO.       | ORDER NO. | DESCRIPTION              | Qty. |
| SS-AA           | 8201139   | 3/4"(19) Connection Size |      |
| SS-BB           | 8201140   | 1"(25) Connection Size   |      |
| SS-CC           | 8201141   | 1"(25) Connection Size   |      |
| SS-DD           | 8201142   | 1"(25) Connection Size   |      |
| SS-EE           | 8201143   | 1"(25) Connection Size   |      |

### NOTICE

The information contained herein is not intended to replace the full product installation and safety information available or the experience of a trained product installer. You are required to thoroughly read all installation instructions and product safety information before beginning the installation of this product.

Watts product specifications in U.S. customary units and metric are approximate and are provided for reference only. For precise measurements, please contact Watts Technical Service. Watts reserves the right to change or modify product design, construction, specifications, or materials without prior notice and without incurring any obligation to make such changes and modifications on Watts products previously or subsequently sold.



| TECHNICAL DATA |             |            |              |             |            |
|----------------|-------------|------------|--------------|-------------|------------|
| DESCRIPTION    | SS-AA       | SS-BB      | SS-CC        | SS-DD       | SS-EE      |
| Fixture Unit   | 1-11        | 12-32      | 33-60        | 61-113      | 114-154    |
| "A" Connection | 3/4"(10)    | 1"(25)     | 1"(25)       | 1"(25)      | 1"(25)     |
| "B" Connection | 3 3/16"(81) | 4"(102)    | 4 5/16"(110) | 5 1/4"(133) | 7"(178)    |
| "C" Diameter   | 3 1/4"(83)  | 3 1/4"(83) | 3 1/4"(83)   | 3 1/4"(83)  | 3 1/4"(83) |

### Approvals



**Note:** Complies with PDI WH201



**Note:** Complies with ASSE 1010



**USA:** T: (800) 338-2581 • Watts.com

**Canada:** T: (888) 208-8927 • Watts.ca

**Latin America:** T: (52) 55-4122-0138 • Watts.com

ES-WD-SS Series 2631

© 2026 Watts