

Engineering Specification

Job Name _____
 Job Location _____
 Engineer _____
 Approval _____

Contractor _____
 Approval _____
 Contractor's P.O. No. _____
 Representative _____

SS Series Stainless Steel Shock Arrestors Specification

Watts SS Series pre-charged all stainless steel shock arrestor with stainless steel bellows, and male IPS threaded connection.

Operating Pressure:

Designed to operate on all domestic and commercial lines up to 150 psi working pressure, 250 psi static pressure.


Temperature Range:

33°F to 300°F (1°C to 149°C)

Installation

May be installed in new or existing plumbing systems with a standard pipe tee vertically, horizontally, or at any angle. SS Series are factory air charged and permanently sealed. They may be installed in concealed locations without access panels and are not rechargeable in the field.

Call customer service if you need assistance with technical details.



Connection Size			
Model No.	Order No.	Description	Qty.
SS-AA	8201139	3/4"(19) Connection Size	<input type="checkbox"/>
SS-BB	8201140	1"(25) Connection Size	<input type="checkbox"/>
SS-CC	8201141	1"(25) Connection Size	<input type="checkbox"/>
SS-DD	8201142	1"(25) Connection Size	<input type="checkbox"/>
SS-EE	8201143	1"(25) Connection Size	<input type="checkbox"/>

Technical Data

Description	SS-AA	SS-BB	SS-CC	SS-DD	SS-EE
Fixture Unit	1-11	12-32	33-60	61-113	114-154
"A" Connection	3/4"(19)	1"(25)	1"(25)	1"(25)	1"(25)
"B" Height	3 3/16"(81)	4"(102)	4 5/16"(110)	5 1/4"(133)	7"(178)
"C" Diameter	3 1/4"(83)	3 1/4"(83)	3 1/4"(83)	3 1/4"(83)	3 1/4"(83)

Approvals



Note: Complies with PDI WH201



Note: Complies with ASSE 1010

NOTICE

The information contained herein is not intended to replace the full product installation and safety information available or the experience of a trained product installer. You are required to thoroughly read all installation instructions and product safety information before beginning the installation of this product.

Watts product specifications in U.S. customary units and metric are approximate and are provided for reference only. For precise measurements, please contact Watts Technical Service. Watts reserves the right to change or modify product design, construction, specifications, or materials without prior notice and without incurring any obligation to make such changes and modifications on Watts products previously or subsequently sold.

