

## Engineering Specification

Job Name \_\_\_\_\_

Contractor \_\_\_\_\_

Job Location \_\_\_\_\_

Approval \_\_\_\_\_

Engineer \_\_\_\_\_

Contractor's P.O. No. \_\_\_\_\_

Approval \_\_\_\_\_

Representative \_\_\_\_\_


# GI-K

## Large Capacity Grease Interceptor

### Specification

Watts GI-K recessed or floor mounted epoxy coated steel grease interceptor with gasketed epoxy coated steel skid-proof cover secured with hex head center bolt(s), double wall deep seshal trap, integral stainless steel flow control plate, and no hub (standard) connections.

Call customer service if you need assistance with technical details.



Flow Rate	
Suffix	Description
75	75 GPM
100	100 GPM
150	150 GPM
200	200 GPM
250	250 GPM
300	300 GPM
400	400 GPM
500	500 GPM

Options	
Suffix	Description
-B	Sediment Bucket
-E	Extension
-FC	Flange & Clamp Device
-HD	Heavy Duty (10,000 lb.) Traffic Cover*
-O	Inlet & Outlet other than Standard Size
-SS	Stainless Steel
-THD	Threaded Connections

\*HD Option Requires Minimum 3"Extension

Model No.	Flow Rate GPM	Grease Capacity Lbs.	A Inlet & Outlet	B Base to Center	C Top to Center	D Length	E Width	F Height
GI-75-K	75 GPM	150	4"(102)	18-½"(470)	4-½"(114)	39-¾"(1010)	30-¾"(781)	23"(584)
GI-100-K	100 GPM	200	4"(102)	28-½"(724)	4-½"(114)	39-¾"(1010)	30-¾"(781)	33"(838)
GI-150-K	150 GPM	300	4"(102)	38-½"(978)	4-½"(114)	39-¾"(1010)	30-¾"(781)	43"(1092)
GI-200-K	200 GPM	400	4"(102)	36-½"(927)	6-½"(165)	52"(1321)	34"(864)	43"(1092)
GI-250-K	250 GPM	500	4"(102)	39-½"(1003)	6-½"(165)	52"(1321)	34"(864)	46"(1168)
GI-300-K	300 GPM	600	6"(152)	38"(965)	10"(254)	76"(1930)	48"(1219)	48"(1219)
GI-400-K	400 GPM	800	6"(152)	42"(1067)	10"(254)	83"(2108)	55"(1397)	52"(1321)
GI-500-K	500 GPM	1000	6"(152)	53"(1346)	10"(254)	91"(2311)	60"(1524)	63"(1600)

### NOTICE

The information contained herein is not intended to replace the full product installation and safety information available or the experience of a trained product installer. You are required to thoroughly read all installation instructions and product safety information before beginning the installation of this product.

Watts product specifications in U.S. customary units and metric are approximate and are provided for reference only. For precise measurements, please contact Watts Technical Service. Watts reserves the right to change or modify product design, construction, specifications, or materials without prior notice and without incurring any obligation to make such changes and modifications on Watts products previously or subsequently sold.



USA: T: (800) 338-2581 • Watts.com

Canada: T: (888) 208-8927 • Watts.ca

Latin America: T: (52) 55-4122-0138 • Watts.com

ES-WD-GI-K 2601

© 2026 Watts