



GL Series

Tag: _____


PDI Certified Grease Interceptor

PROLINE

SPECIFICATION: Watts ProLine GL Series PDI Certified low-rough-in recessed or floor mounted epoxy coated steel grease interceptor with external flow control fitting and no hub connection.



Options	
-E	Extension <input type="checkbox"/>
-THD	Threaded Connections <input type="checkbox"/>



Model	Flow Rate		Capacity		Pipe Size A				Length D		Width E		Height F	
	GPM	LPM	lbs.	kg	in	mm	in	mm	in	mm	in	mm	in	mm
GL-20	20	76	40	18	3	76	4-1/4	108	34-7/8	864	22-7/8	581	11-3/4	298
GL-35	35	133	70	32	4	100	4-1/2	114	40-7/8	1016	32-7/8	835	11-7/8	302
GL-50*	50	190	100	45	4	100	5-1/2	140	55	1397	33	838	14	356

*Not PDI Certified

Job Name _____ Contractor _____

Job Location _____ Contractor's P.O. No. _____

Engineer _____ Representative _____

WATTS Drainage reserves the right to modify or change product design or construction without prior notice and without incurring any obligation to make similar changes and modifications to products previously or subsequently sold. See your WATTS Drainage representative for any clarification. Dimensions are subject to manufacturing tolerances.



Specification Drainage Products

USA: 100 Watts Road, Spindale, NC, 28160-2298; TEL: 828-288-2179 TOLL-FREE: 1-800-338-2581 www.watts.com