

Engineering Specification

Job Name _____

Contractor _____

Job Location _____

Approval _____

Engineer _____

Contractor's P.O. No. _____

Approval _____

Representative _____

OI Oil Interceptor Specification


Watts OI Series recessed or floor mounted epoxy coated steel oil interceptor with gasketed epoxy coated steel skid-proof cover secured with hex head center bolt(s), double wall deep seal trap, draw-off connection and dual vent connections, integral stainless steel flow control plate, and no hub (standard) connections.



Call customer service if you need assistance with technical details.

Flow Rate		Options	
Suffix	Description	Suffix	Description
10	10 GPM <input type="checkbox"/>	-B	Sediment Bucket <input type="checkbox"/>
15	15 GPM <input type="checkbox"/>	-E	Extension <input type="checkbox"/>
20	20 GPM <input type="checkbox"/>	-FC	Flange & Clamp Device <input type="checkbox"/>
25	25 GPM <input type="checkbox"/>	-HD	Heavy Duty (10,000 lb.) Traffic Cover* <input type="checkbox"/>
35	35 GPM <input type="checkbox"/>	-O	Inlet & Outlet (other than Standard Size) <input type="checkbox"/>
50	50 GPM <input type="checkbox"/>	-SS	Stainless Steel <input type="checkbox"/>
		-THD	Threaded Connections <input type="checkbox"/>

*HD Option Requires Minimum 3" Extension



Model Number	Flow Rate GPM	A Inlet/Outlet	C Top to Center	D Length	E Width	F Height	G Base to Center	H	J	K
OI-10	10	3"(76)	4"(102)	22-1/4"(565)	16-3/4"(425)	11-1/2"(192)	3-1/2"(89)	11-1/2"(192)	5"(127)	4"(102)
OI-15	15	3"(76)	4"(102)	22-1/4"(565)	16-3/4"(425)	14-1/2"(368)	5-1/2"(140)	11-1/2"(192)	5"(127)	4"(102)
OI-20	20	3"(76)	4"(102)	27-1/4"(692)	19-1/4"(489)	16-1/2"(419)	6-1/2"(165)	14-1/4"(362)	6"(152)	5"(127)
OI-25	25	3"(76)	4"(102)	27-1/4"(692)	19-1/4"(489)	18-1/4"(464)	9-1/2"(241)	14-1/4"(362)	6"(152)	5"(127)
OI-35	35	4"(102)	4"(102)	33-3/4"(857)	20-3/4"(527)	18"(457)	9-1/2"(241)	18-1/2"(470)	7"(178)	6"(152)
OI-50	50	4"(102)	4"(102)	33-3/4"(857)	20-3/4"(527)	21-1/2"(546)	13"(330)	18-1/2"(470)	7"(178)	6"(152)

NOTICE

The information contained herein is not intended to replace the full product installation and safety information available or the experience of a trained product installer. You are required to thoroughly read all installation instructions and product safety information before beginning the installation of this product.

Watts product specifications in U.S. customary units and metric are approximate and are provided for reference only. For precise measurements, please contact Watts Technical Service. Watts reserves the right to change or modify product design, construction, specifications, or materials without prior notice and without incurring any obligation to make such changes and modifications on Watts products previously or subsequently sold.



USA: T: (800) 338-2581 • Watts.com

Canada: T: (888) 208-8927 • Watts.ca

Latin America: T: (52) 55-4122-0138 • Watts.com

