

For Agricultural and Industrial Applications

Job Name _____

Contractor _____

Job Location _____

Approval _____

Engineer _____

Contractor's P.O. No. _____

Approval _____

Representative _____

APEX Reservoir Valve

Sizes: 1¼", 1½", 2"

Large Acetyl sleeve valve. High volume flow valve for reservoirs and large header tanks. (For pump fed tanks use BigAl® or PumpBuddy® Valves)



Application

- Large Storage Tanks/Reservoirs

Models

RES114 US – 1 ¼" NPT (32mm)

RES112 US – 1 ½" NPT (40mm)

RES2 US – 2" NPT (50mm)

Specifications

Working Pressure: 0 – 120psi (0 – 800kPa)

Supplied with two 6" floats and one Float Connector



Flow Rates: 135gpm @ 58psi

Maximum Water Temperature: 140°F (60°C)

Minimum Water Temperature: 34°F (1°C)

NOTICE

The information contained herein is not intended to replace the full product installation and safety information available or the experience of a trained product installer. You are required to thoroughly read all installation instructions and product safety information before beginning the installation of this product.



Watts product specifications in U.S. customary units and metric are approximate and are provided for reference only. For precise measurements, please contact Watts Technical Service. Watts reserves the right to change or modify product design, construction, specifications, or materials without prior notice and without incurring any obligation to make such changes and modifications on Watts products previously or subsequently sold.



USA: T: (978) 689-6066 • F: (978) 975-8350 • Watts.com
Canada: T: (905) 332-4090 • F: (905) 332-7068 • Watts.ca
Latin America: T: (52) 81-1001-8600 • Watts.com