

Engineering Specification

Job Name _____ Contractor _____

Job Location _____ Approval _____

Engineer _____ Contractor's P.O. No. _____

Approval _____ Representative _____

OI Oil Interceptor Specification


Watts OI Series recessed or floor mounted epoxy coated steel oil interceptor with gasketed epoxy coated steel skid-proof cover secured with hex head center bolt(s), double wall deep seal trap, draw-off connection and dual vent connections, integral stainless steel flow control plate, and no hub (standard) connections.



Call customer service if you need assistance with technical details.

Flow Rate		Options	
Suffix	Description	Suffix	Description
10	10 GPM	-B	Sediment Bucket
15	15 GPM	-E	Extension
20	20 GPM	-FC	Flange & Clamp Device
25	25 GPM	-HD	Heavy Duty (10,000 lb.) Traffic Cover*
35	35 GPM	-O	Inlet & Outlet (other than Standard Size)
50	50 GPM	-SS	Stainless Steel
		-THD	Threaded Connections

*HD Option Requires Minimum 3" Extension



Model No.	Flow Rate GPM	A Inlet/Outlet	C Top to Center	D Length	E Width	F Height	G Base to Center	H	J	K
OI-10	10 GPM	3"(76)	4"(102)	22-¼"(565)	16-¾"(425)	11-½"(192)	3-½"(89)	11-½"(192)	5"(127)	4"(102)
OI-15	15 GPM	3"(76)	4"(102)	22-¼"(565)	16-¾"(425)	14-½"(368)	5-½"(140)	11-½"(192)	5"(127)	4"(102)
OI-20	20 GPM	3"(76)	4"(102)	27-¼"(692)	19-¼"(489)	16-½"(419)	6-½"(165)	14-¼"(362)	6"(152)	5"(127)
OI-25	25 GPM	3"(76)	4"(102)	27-¼"(692)	19-¼"(489)	18-¼"(464)	9-½"(241)	14-¼"(362)	6"(152)	5"(127)
OI-35	35 GPM	4"(102)	4"(102)	33-¾"(857)	20-¾"(527)	18"(457)	9-½"(241)	18-½"(192)	7"(178)	6"(152)
OI-50	50 GPM	4"(102)	4"(102)	33-¾"(857)	20-¾"(527)	21-½"(546)	13"(330)	18-½"(192)	7"(178)	6"(152)

NOTICE

The information contained herein is not intended to replace the full product installation and safety information available or the experience of a trained product installer. You are required to thoroughly read all installation instructions and product safety information before beginning the installation of this product.

Watts product specifications in U.S. customary units and metric are approximate and are provided for reference only. For precise measurements, please contact Watts Technical Service. Watts reserves the right to change or modify product design, construction, specifications, or materials without prior notice and without incurring any obligation to make such changes and modifications on Watts products previously or subsequently sold.



USA: T: (800) 338-2581 • Watts.com

Canada: T: (888) 208-8927 • Watts.ca

Latin America: T: (52) 55-4122-0138 • Watts.com

